

CHEMICAL METERING PUMPS

Microprocessor Based, High Performance

PHP-200B Series
Starts at

\$850



PHP-202B-P with included foot and injection valves, \$850, shown smaller than actual size.

- ✓ Continuous Stroke-Length Adjustment Measured
- ✓ Direct Calibration and Built-In Warning
- ✓ Adjustable Backpressure Control
- ✓ Totalized Output in U.S. Gallons or Liters
- ✓ Bleed Valve Standard
- ✓ Control Options: Manual or Analog
- ✓ Relay Output Option
- ✓ Available in Polypropylene, PTFE, or Stainless Steel Liquid Ends

The PHP-200B Series consists of diaphragm-type, solenoid-driven, microprocessor-based metering pumps with maximum capacities to 4.5 GPH and maximum backpressures to 253 psig. The housing is constructed of fiberglass-reinforced PPE plastic, with a NEMA 4X (IP66) enclosure rating to protect against corrosion, dust, and water. A removable hood covers the faceplate. The drive unit houses a short-stroke solenoid with a maximum stroke length of 1.25 mm (0.05"). It is equipped with a noise-suppressing mechanism for quiet operation and has only one moving part, the armature. The diaphragm is constructed of fabric-reinforced EPDM elastomer with a plastic core and PTFE facing. It is chemically resistant against virtually all process fluids and can be used over a wide temperature range. Suction and discharge ports are equipped with double-ball check valves for maximum repeatability. Feed rate is determined by stroke length and stroke rate. Stroke length is manually adjustable from 1 to 100% in increments of 1% via the stroke length knob. Two control modes are available for the PHP-200B Series: manual or analog control.

Capacities and Specifications

Model Number	Capacity at Maximum Backpressure [†]			Capacity at ½ Max Backpressure [†]		Suction/Discharge Line OD x ID (-P, -T)*	Pre-Primed Suction Lift (ft) [†]	Shipping Wt (lb)
	psi	US GPH (LPH)	cm ³ /Stroke	USG PH (LPH)	cm ³ /Stroke			
PHP-201B/ PHP-211B	145	0.19 (0.719)	0.09	0.21 (0.82)	0.076	¼ x ⅜"	16.4	8.6 (3.9)
PHP-202B/ PHP-212B	253	0.29 (1.10)	0.13	0.37 (1.40)	0.13	¼ x ⅜"	16.4	8.6 (3.9)
PHP-203B/ PHP-213B	253	0.55 (2.08)	0.24	0.66 (2.50)	0.24	¼ x ⅜"	16.4	8.8 (4.0)
PHP-204B/ PHP-214B	145	1.10 (4.16)	0.45	1.32 (5.00)	0.46	½ x ⅜"	16.4	9.0 (4.1)
PHP-205B/ PHP-215B	253	1.10 (4.16)	0.38	1.29 (4.90)	0.45	½ x ⅜"	13.1	10.8 (4.9)
PHP-206B/ PHP-216B	101	2.90 (10.58)	1.02	3.46 (13.10)	1.21	½ x ⅜"	9.8	12.8 (5.8)
PHP-207B/ PHP-217B	58	4.50 (17.0)	1.58	5.04 (19.10)	1.77	½ x ⅜"	9.8	12.8 (5.8)

Comes complete with foot and injection valves, 1.8 m (6') of contact cable for pulse input, and level connector, and operators manual. Polypropylene models are supplied with 3 m (10') or 1.5 m (5') of polyethylene tubing.

[†] Capacities and suction lifts are for waterlike fluids. Higher-specific-gravity fluids reduce suction lift, while higher-viscosity fluids reduce capacity.

* "S" pumps have ¼ FNPT connections. See ordering information on page L-20.



PHP-202B-P, \$850, front view without cover.



PHP-202B-P, \$850, complete with included foot and injection valves, 1.8 m (6') contact cable for pulse input, level connector, and operator's manual, shown smaller than actual size.



Recommended Reference Book:
Chemical Engineering,
CM-4226, \$60.
See Section Y
For Additional Books



The PHP-210B Series has all the features of the PHP-200B Series, as well as current input. This allows the stroking rate to be controlled by standard process signals. Multiple functions can be programmed through the front keypad, including step-up or step-down ratios and the predetermining counter mode, which allows a preset number of strokes to be counted.

SPECIFICATIONS

Maximum Stroke Length: 1.25 mm (0.05")

Materials of Construction:

Housing: Fiberglass-reinforced PPE

Diaphragm: PTFE-faced EPDM with plastic core

Liquid-End Options: Polypropylene (P), PTFE (T), 316 SS (S)

Seal: FKM for P models, PTFE for T and S models

Enclosure Rating: NEMA 4X (IP66)

Power Supply: 100 to 230 Vac, 1 phase, 50/60 Hz $\pm 10\%$

Repeatability of Metering: $\pm 2\%$ under constant conditions and at minimum 30% stroke length

Ambient Temperature Range: -10 to 45°C (14 to 113°F)

Max Fluid Operating Temperature: 50°C (122°F)

Power Cord: 2 m (6')

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)							
Pulse Frequency Input Models				Frequency/Current Input Models			
	Price				Price		
Model Number	Polypropylene	PTFE	316 SS	Model Number	Polypropylene	PTFE	316 SS
PHP-201B-[*]	\$850	\$1450	\$1700	PHP-211B-[*]	\$925	\$1500	\$1750
PHP-202B-[*]	850	1450	1700	PHP-212B-[*]	925	1500	1750
PHP-203B-[*]	850	1450	1700	PHP-213B-[*]	925	1500	1750
PHP-204B-[*]	875	1550	1950	PHP-214B-[*]	950	1600	2000
PHP-205B-[*]	1150	1750	2100	PHP-215B-[*]	1200	1800	2150
PHP-206B-[*]	1150	1750	2100	PHP-216B-[*]	1200	1800	2150
PHP-207B-[*]	1150	1750	2100	PHP-217B-[*]	1200	1800	2150

* Insert "P" for polypropylene, "T" for PTFE or "S" for 316 SS.

Comes complete with foot and injection valves, 1.8 m (6') contact cable for pulse input, level connector, and operator's manual.

Ordering Examples: PHP-211B-P, frequency/current input, 0.19 GPH max polypropylene pump, \$925.

PHP-202B-P, frequency input, 0.19 GPH max polypropylene pump, \$850.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters