

CHEMICAL METERING PUMPS

See page 541
for accessories

PHP-601
Starts
£151



- ✓ Flow Rates from 1.5 to 18.3 Litres per Hour
- ✓ Simple Operation
- ✓ Easily Mounted

VERSATILITY OF DESIGN

The PHP-600 Series pumps have been designed to meet the ever-changing needs of industry. To accommodate diverse applications, the pumps can be easily mounted anywhere in your plant with a broad, flat base and mounting holes for tank, shelf or floor mounting (horizontal). The rear of the pump housing also provides mounting holes to facilitate vertical mounting; wall, tank or machine. With the pump valve assembly and unit controls both located on the front of the pump, there is never a problem with installation or flow adjustments.

SIMPLE OPERATION

The PHP-600 Series pumps are equipped with a single control for pump output. The external Flow Rate Control (potentiometer) on the face of the pump allows you to adjust the percentage of flow from 0 to 100% of the pump's rated capacity. This feature eliminates the need to worry about stroke lengths and power settings. An LED indicator lights up each time a stroke begins. This allows the user to assess the stroke rate from a distance.

HIGH QUALITY MATERIALS


The PHP-600 Series pumps have been manufactured with the highest level of mechanical precision from materials chosen for their inherent ability to resist the effects of most aggressive chemicals. When you select a PHP-600 Series pump you are eliminating the time consuming

effort involved in picking the right material for your application. The PHP-600 Series pumps are supplied with the highest quality material as standard equipment, not optional. The diaphragm uses one-piece construction of PTFE, which unlike conventional laminated diaphragms will stand up to the test of time and wear. Ball valves are constructed in glass. The pump head, and O-rings are all made of FKM, PTFE or PVDF, which offer unsurpassed resistance to the chemicals in your industry.

RUGGED DESIGN

The PHP-600 Series pumps are completely sealed during assembly and offer IP65 protection against splashes and spills providing excellent protection even in hostile environments. The fibre-reinforced polypropylene housing stands up to most aggressive chemicals while offering superior strength under tough industrial conditions.

PHP-601, £151, shown smaller than actual size.



Comes complete with discharge and suction valves installed, 7 m polyethylene tubing, and operator's manual.

RELIABILITY THROUGH SIMPLICITY


The PHP-600 Series positive displacement solenoid driven pumps use a minimum number of moving parts, therefore reducing the chance of mechanical failure. Part wear and oiling associated with motor driven pumps (ball-bearings, gear drives and cams) are not present in these pumps. The PHP-600 Series pumps are more accurate than standard pumps with the positive displacement design ensuring each stroke is identical to the strokes before and after it, thus keeping the flow rate constant.

THE PHP-600 SERIES PUMPS

A wide range of the PHP-600 Series pumps with different dosing capacities is available for your specific dosing needs. Each pump is supplied with discharge and suction valves. Polyethylene tubing, injection fittings, ceramic weights and replacement parts are also available.

SPECIFICATIONS

Power Supply: 110/115V 50/60 Hz
220/240V 50/60 Hz (optional)
Dimensions: 165 H x 194 W x 121 mm D
Weight: Approx. 3 kg
Pump Casing:
Fibre-reinforced polypropylene
Max. Absorbed: Approx. 200W
Power Protection: IP65
Environment: From 0 to 50°C;
max RH 95% non-condensing
Fittings: Polyethylene 5 x 8 mm tubing,
10 mm gas pipeline injection fitting
Pump Head: Pump head in PVDF,
diaphragm and valve seats in PTFE
glass ball Valves and O-rings in FKM
Self-Priming: Max self-priming
height 1.5 m



PHP-601, £151,
shown smaller
than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Max Capacity		Rated Pressure		Strokes per minute
		LPH	US GPH	PSI	BAR	
Small Diaphragm						
PHP-601	£151	1.5	0.4	188.5	13.0	120
PHP-602	151	2.9	0.8	116.0	8.0	120
PHP-603	157	5.0	1.3	101.5	7.0	120
Large Diaphragm						
PHP-604	£171	7.6	2.0	43.5	3.0	120
PHP-605	174	10.8	2.9	43.5	3.0	120
PHP-606	178	15.2	4.0	14.5	1.0	120
PHP-607	200	18.3	4.8	7.3	0.5	120

Accessories (see page 541 for additional information)

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Model No.	Price	Description
PHP-600-PHK	£47.00	PVDF pumphead, PTFE coated O-ring and 6 screws and washers
PHP-600-DVA	16.75	Spare discharge valve assembly, complete with a FKM O-ring, glass valve ball, the valve spacer and seat, head nipple and the tube nut to secure the assembled parts
PHP-600-SVA	16.75	Spare suction valve assembly, complete with a FKM O-ring, glass valve ball, the valve spacer and seat, head nipple and the tube nut to secure the assembled parts
PHP-600-IVA	15.50	Injection valve assembly, complete with an injection nipple, PTFE coated spring, glass valve ball and a valve assembly
PHP-600-FVA	13.50	Foot valve assembly contains a filter with a filter holder, and a valve assembly
PHP-600-CW	16.75	4 x ceramic weight
CM-4226	40.00	Reference Book: Chemical Engineering

Comes complete with discharge and suction valves installed, 7 m polyethylene tubing, and complete operator's manual.

Add "220VAC" to model number for 220/240V operation, no additional charge.

Ordering ExampleS: PHP-601, chemical metering pump, £151. PHP-605, chemical metering pump, and PHP-600-IVA, injection valve assembly, £174 + 15.50 = £189.50.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters