

OMEGA-FLO® 4-WAY SOLENOID VALVES FOR PNEUMATICS

1/4" NPT

SV-1801A
Starts at
£128



- Ideal for Double Acting Cylinders
- Manual Override Standard
- 120 Vac Standard (DC Optional)
- Low Power

OMEGA's Model SV-1801A 4-way solenoid valve is an internally piloted poppet valve with epoxy-encapsulated coil, low power consumption, and high cycling rate. It features a high-quality plastic body with molded-in threaded bushings. Manual override is standard. Seal material is Buna-N. Temperature range is from -10 to 60°C (14 to 140°F). The valve is ideal for use with compressed air to actuate medium-sized cylinders and actuators. Electrical connection is by conduit plug.



SV1801A, £128, shown actual size.

SPECIFICATIONS

Mounting Position: Any (preferably with solenoid systems upright)

Max Ambient Temp: 54° C (130° F)

Voltage Tolerance: ±10%

Power Consumption in Warm State:

AC: 3.5 Va/2 W

DC: 2 W

Opening Time (msec): Approx 50

Closing Time (msec): Approx 30

Cycling Rate: 100 to 500 cpm (depending on operating pressure)

Duty Cycle: Continuous (100%)

FM Approvals: Nonincendiary for hazardous locations Class I Div. 2 Group A, B, C, D; Class II Div. 2 Group F, G; Class III Div. 1 and 2, Operating Temperature T4A

OPTION (NO ADDITIONAL CHARGE)

ORDERING SUFFIX	DESCRIPTION
-24VDC	24 Vdc operation

To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	PORT CONNECTION (NPT)	Cv ¹	PRESSURE RANGE (psi)	ORIFICE DIAMETER	WEIGHT (kg (lb))	BODY MATERIAL
SV-1801A	£128	1/4"	0.97	15 to 140	1/4"	0.40 (0.88)	Plastic

¹ A pressure difference of at least 15 psi is required to ensure operation.

Comes with complete operator's manual.

Ordering Example: SV-1801A, plastic valve, 0.97 Cv, 1/4" NPT connection, £128.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
CM-4449	£50	Reference Book: Valve Selection Handbook





UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters