


FITTINGS AND ACCESSORIES


TUBE FITTINGS

Hose Barb Union

	Straights (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
	FT-HS-2	\$5.50	1/16" x 1/16" Hose Barb	
	FT-HS-3	5.50	3/32" x 3/32" Hose Barb	
	FT-HS-4	5.50	1/8" x 1/8" Hose Barb	
	Tees (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
	FT-HT-2	\$6.30	1/16" x 1/16" x 1/16" Hose Barb	
	FT-HT-3	6.30	3/32" x 3/32" x 3/32" Hose Barb	
	FT-HT-4	6.30	1/8" x 1/8" x 1/8" Hose Barb	
	Elbows (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
FT-HE-2	\$6.30	1/16" x 1/16" Hose Barb		
FT-HE-3	6.30	3/32" x 3/32" Hose Barb		
FT-HE-4	6.30	1/8" x 1/8" Hose Barb		


Material : Polypropylene standard; Nylon available on request.

Panel Mount Hose Barb Union

 <p>Panel Thickness 0.040" to 1/4"</p>	Straights (Supplied 10/PK)				
	TUBING ID	METRIC MM	MODEL NUMBER	PRICE	PANEL OPENING
	1/8" x 1/8"	3.2 x 3.2	FT-BHU 22-02	\$20.30	1/2"
	1/4" x 1/4"	6.4 x 6.4	FT-BHU 22-04	23.80	1/2"
	3/8" x 3/8"	9.5 x 9.5	FT-BHU 22-06	23.80	1/2"

Material: Delrin acetal. Nut: Nickel-plated brass.


Hose Barb x 10-32 Thread

	Straights (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
	FT-MS-2	\$3.80	1/16" Hose Barb x 10-32 Thread	
	FT-MS-3	3.80	3/32" Hose Barb x 10-32 Thread	
	FT-MS-4	3.80	1/8" Hose Barb x 10-32 Thread	
	Tees (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
	FT-MT-2	\$8.60	1/16" x 1/16" Hose Barb x 10-32 Thread	
	FT-MT-3	8.60	3/32" x 3/32" Hose Barb x 10-32 Thread	
	FT-MT-4	8.60	1/8" x 1/8" Hose Barb X 10-32 Thread	
	Elbows (Supplied 10/PK)			
	MODEL NUMBER	PRICE	DESCRIPTION	
FT-ME-2	\$8.60	1/16" Hose Barb x 10-32 Thread		
FT-ME-3	8.60	3/32" Hose Barb x 10-32 Thread		
FT-ME-4	8.60	1/8" Hose Barb x 10-32 Thread		
Miscellaneous (Supplied 10/PK)				
MODEL NUMBER	PRICE	DESCRIPTION		
FT-MP	\$3.80	10-32 Plug		
FT-N32	3.80	10-32 x 10-32 Nipple		

OMEGA's tube fittings solve many small tubing problems. Made of Polypropylene, they provide chemical compatibility. Sizes for 1/16", 3/32" and 1/8" plastic tubing.


Chemical Resistant Material. Polypropylene fittings provide excellent chemical resistance. This strong material is much lighter than brass, attractive in appearance and reasonably priced. Other materials or colors are available on request.

OMEGA's Panel Mount Hose Barb Union connects tubing through panels up to 1/4" thick. Delrin acetal is strong and chemical resistant. Applications include vacuum, pressure lines, fluids and gases.



Tapered 10-32 Threads

OMEGA's threaded fittings feature a tapered 10-32 thread that requires no gasket for a reliable seal. Fittings will seal even in slightly off-sized holes. The tapered thread also allows the fitting to be directionally oriented without a gasket.



Shrouded 1/16" Hose Barb eliminates breakage...

The patented shrouded design eliminates the most common problem of small fittings – barb breakage. The shroud completely supports the tubing, reducing stress on the fragile hose barb. It solves the problem of breakage without buying expensive metal tube fittings. Patented.

Specifications

Working Pressure: 100 psi (7.0 bar)

Operating Temperature:

0° to 110°C, (32 to 230°F)

Materials: Polypropylene

These specifications do not apply to panel mount hose barb unions.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters