


CONSTANT WATTAGE HEAT CABLE

CWM Series Starts at
\$200
 25' Length



- ✓ Constant Output
- ✓ Cut to Any Length
- ✓ Lower Installation Costs
- ✓ Flexible

OMEGALUX® CWM (constant wattage medium temperature) heating cable is ideal for pipe tracing situations that require higher temperatures for process maintenance as well as freeze protection. No matter what length of cable is needed, the wattage (or heat) produced by each foot of cable remains unchanged.

Standard Construction

- A. Bus Wires.** Twin 12 AWG copper bus wires provide reliable, consistent electrical current.
- B. Bus Wire Insulation.** 11 mil FEP jacket protects and electrically insulates bus wires.
- C. Inner Sheath.** This insulation jacket holds the 2 bus wires together and provides the wrapping surface for the nichrome heating wire.
- D. Nichrome Wire.** The nichrome resistance heating wire is the heating component of the cable.
- E. Jacket.** Flame-retardant insulation jacket is made from FEP material, which protects heating cable and ensures long service life. This material is also highly corrosion resistant.
- F. Metal Braid.** Plated copper braid covering the jacket provides a positive ground path.
- G. Optional Fluoropolymer Overjacket.** FEP jacket provides protection from most aqueous and chemically corrosive solutions. Add suffix “-CT” to model number.

SPECIFICATIONS

- Wattage:** 4, 8, 10 and 12 W/ft
- Power:** 120V, 240V and 480V
- Bus Wires:** 12 AWG copper
- Bus Wire Insulation:** Each bus wire is insulated with an 11 mil FEP jacket.
- Approximate Cable Size:** 8 x 5 mm (5/16 x 1/8"); CT only: 26 x 6 mm (1 1/2 x 1/4")



- Minimum Bend Radius:** 6 times minor diameter
- Maximum Intermittent Exposure Temperature/Power-Off:** 200/392°C
- Steam Cleaning:** CWM can withstand 200°C (392°F), 150 psig steam purging of process piping when not energized
- Third-Party Approvals:** See page 47
- Circuit Breaker Selection:** To determine the circuit breaker size required, divide the W/ft (at operating voltage) by the operating voltage;

multiply the result times the total installed cable length in feet; multiply this result times 1.2 to get the minimum circuit breaker size



Caution and Warning!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)									
Output		Tinned Copper Braid (-C)			FEP Overcoat (-CT) and Tinned Copper Overbraid			Module Length mm (in)	Max Circuit Length m (ft)
Watts/Foot	Volts	Model Number	Price/ft	Weight kg (lb)/1000'	Model Number	Price/ft	Weight kg (lb)/1000'		
4	120	CWM4-1C	\$8	43.5 (96)	CWM4-1CT	\$9	49.9 (110)	457 (18)	106.6 (350)
4	240	CWM4-2C	8	43.5 (96)	CWM4-2CT	9	49.9 (110)	762 (30)	213.3 (700)
8	120	CWM8-1C	\$8	43.5 (96)	CWM8-1CT	\$9	49.9 (110)	457 (18)	74.6 (245)
8	240	CWM8-2C	8	43.5 (96)	CWM8-2CT	9	49.9 (110)	610 (24)	144.7 (475)
12	120	CWM12-1C	\$8	43.5 (96)	CWM12-1CT	\$9	49.9 (110)	305 (12)	60.9 (200)
12	240	CWM12-2C	8	43.5 (96)	CWM12-2CT	9	49.9 (110)	610 (24)	121.9 (400)
12	480	CWM12-4C	8	43.5 (96)	CWM12-4CT	9	49.9 (110)	762 (30)	243.8 (800)

Minimum length of heating cable is 25 ft. See Pages 50 to 53 for heat cable accessories and controls.
 Ordering Example: CWM12-1C, 120 Vac heating cable, 12 W/ft, 100-ft length, \$900.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters