


# ELECTRIC STUD HEATERS

CBH Series  
Starts at  
**\$950**



CBH-1815/120, \$950, shown smaller than actual size.

- ✓ Reliable, Premium Quality
- ✓ Steel Sheath
- ✓ 1150 to 8000 W
- ✓ 120, 240 Vac
- ✓ 18" (46 cm), to 60" (152 cm) Lengths



CBH Series heaters are constructed of rugged metal sheathed tubular elements homogeneously combined with a metal sleeve that has been accurately dimensioned to provide a proper clearance and ease of inserting into standard drill hole sizes so large bolts or studs may be rapidly expanded and tightened with a wrench, providing "shrink fit tightness" when cool

Useful in assembly of large compressors, presses, turbines, die blocks, cylinders, engine heads, pressure vessels, etc. Quick heat-up is important to avoid heat drain-away of surrounding metal. CBH heaters are generally used in sets to permit uniform tightening of mating parts.

## SPECIFICATIONS

**Sheath Material:** Steel

**Max Sheath Temperature:** 1600°F

**Power:** 120 or 240 Vac

**Terminal:** Standard octagon box with handle

### CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.

## MOST POPULAR MODELS HIGHLIGHTED!

### To Order (Specify Model Number)

Watts	Dimensions: Inches (cm)						Model No.	Price	Weight lb (kg)
	A Lgth.	B Htd. Lgth.	C Htd. Dia.	D Cold End	E Cold End	Max. Stud Hole Dia. †			
1150	18 (46)	12 (30)	.553 (1.4)	1 1/4 (3)	6 1/4 (17)	.616 (1.6)	CBH-1815/120	\$950	5 (2)
1500	24 (61)	18 (46)	.553 (1.4)	1 1/4 (3)	6 1/4 (17)	.616 (1.6)	CBH-2415/120	1050	5 (2)
2250	30 (76)	24 (61)	.553 (1.4)	1 1/4 (3)	6 1/4 (17)	.616 (1.6)	CBH-3025/*	1100	5 (2)
2600	36 (91)	30 (76)	.553 (1.4)	1 1/4 (3)	6 1/4 (17)	.616 (1.6)	CBH-3625/*	1100	5 (2)
1200	18 (46)	12 (30)	.660 (1.7)	1 1/4 (3)	6 1/4 (17)	.735 (1.9)	CBH-1816/120	1050	6 (3)
1700	24 (61)	18 (46)	.660 (1.7)	1 1/4 (3)	6 1/4 (17)	.735 (1.9)	CBH-2416/120	1050	6 (3)
2300	30 (76)	24 (61)	.660 (1.7)	1 1/4 (3)	6 1/4 (17)	.735 (1.9)	CBH-3026/120	1100	6 (3)
2800	36 (91)	30 (76)	.660 (1.7)	1 1/4 (3)	6 1/4 (17)	.735 (1.9)	CBH-3626/120	1150	6 (3)
1700	18 (46)	12 (30)	.730 (1.9)	1 1/4 (3)	6 1/4 (17)	.860 (2.2)	CBH-1827/120	1100	5 (2)
2500	24 (61)	18 (46)	.730 (1.9)	1 1/4 (3)	6 1/4 (17)	.860 (2.2)	CBH-2427/120	1150	5 (2)
4200	36 (91)	30 (76)	.730 (1.9)	1 1/4 (3)	6 1/4 (17)	.860 (2.2)	CBH-3647/120	1300	6 (3)
6000	48 (122)	42 (107)	.730 (1.9)	1 1/4 (3)	6 1/4 (17)	.860 (2.2)	CBH-4867/**	1400	6 (3)
7500	60 (152)	54 (137)	.730 (1.9)	1 1/4 (3)	6 1/4 (17)	.860 (2.2)	CBH-6177/240	1550	7 (3)
2700	24 (61)	18 (46)	.855 (2.2)	1 1/4 (3)	6 1/4 (17)	.985 (2.5)	CBH-2438/240	1250	7 (3)
3600	30 (76)	24 (61)	.855 (2.2)	1 1/4 (3)	6 1/4 (17)	.985 (2.5)	CBH-3048/120	1300	8 (4)
5300	42 (107)	36 (91)	.855 (2.2)	1 1/4 (3)	6 1/4 (17)	.985 (2.5)	CBH-4258/**	1400	8 (4)
6500	48 (122)	42 (107)	.855 (2.2)	1 1/4 (3)	6 1/4 (17)	.985 (2.5)	CBH-4868/240	1450	9 (4)
6000	42 (107)	36 (91)	.980 (2.5)	1 1/4 (3)	6 1/4 (17)	1.110 (2.8)	CBH-4269/**	1800	9 (4)
8000	54 (137)	48 (122)	.980 (2.5)	1 1/4 (3)	6 1/4 (17)	1.110 (2.8)	CBH-6189/240	2150	9 (4)

† Hole diameter should be held as close to heater diameter as possible for maximum heat transfer and heater life.

\* Designate voltage, Insert 120 for 120 Vac or 240 for 240 Vac.

Those model numbers containing /120, /240, or /480 are available only in that voltage.

Ordering Examples: CBH-3025/240, 2252 Watt, 240 Vac stud heater, \$1100.

CBH-1815/120, 1150 Watt, 120 Vac stud heaters, \$950.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters