



ONE-PIECE BAND HEATERS

4 & 6 cm (1½ & 2½") Wide DB & DBW Series

- ✓ Rugged, Reliable, Heavy Duty
- ✓ 13 to 32 cm (5 to 12½") Barrel Diameter
- ✓ Barrel Temperatures Up to 482°C (900°F)

APPLICATIONS

- ✓ Heating barrels of plastic injection molding machines and extruders
- ✓ Die and die holder heating of plastic extruders and blow molding machines
- ✓ Any application requiring heat applied to a cylindrical surface
- ✓ Burn-out ovens
- ✓ Heated kettles
- ✓ Fluidized beds
- ✓ Heat treating pipes
- ✓ Autoclaves



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Watts	W/In ²	Barrel Dia. cm (in)	Model No.	Price	Wt. kg (lbs.)
DB- 4 cm (1½"), 240/480 volts**					
770	33	13 (5)	DB-050772	\$61	0.7 (1.50)
1000	42	14 (5½)	DB-054102	63	0.8 (1.75)
750	27	15 (6)	DB-060752	66	0.9 (2.00)
1000	33	17 (6½)	DB-064102	68	0.9 (2.00)
1000	30	18 (7)	DB-070102	71	0.9 (2.00)
1250	35	19 (7½)	DB-074122	73	0.9 (2.00)
1200	32	20 (8)	DB-080122	75	0.9 (2.00)
1600	40	22 (8½)	DB-084162	78	1.1 (2.50)
1500	35	23 (9)	DB-090152	81	1.1 (2.50)
1700	38	24 (9½)	DB-094172	84	1.4 (3.00)
1800	38	25 (10)	DB-100182	87	1.4 (3.00)
1200	24	27 (10½)	DB-104122	91	1.4 (3.00)
2100	39	29 (11½)	DB-114212	100	1.4 (3.00)
1500	25	32 (12½)	DB-124152	110	1.4 (3.00)
DBW- 6 cm (2½"), 240/480 volts**					
1525	30	17 (6½)	DBW-064152	92	1.7 (3.75)
1800	31	19 (7½)	DBW-074182	102	1.7 (3.75)
2000	35	20 (8)	DBW-080202	107	1.7 (3.75)
2250	34	22 (8½)	DBW-084222	112	1.7 (3.75)
2500	35	23 (9)	DBW-090252	117	1.7 (3.75)
2800	36	25 (10)	DBW-100282	126	1.7 (3.75)
2950	36	27 (10½)	DBW-104292	131	1.7 (3.75)
3250	36	29 (11½)	DBW-114322	141	1.8 (4.00)

** The two 240V strip heating elements must be wired in series for 480V.
 Note: Watt densities are based on heated area of contact surface only.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
MS-1001	\$120	Reference Book: Heating, Ventilating, Air Conditioning: Analysis and Design

FEATURES

Ten times the life—only slightly higher cost. This economical long life heavy duty band heater has a ⅜" thick chrome steel (stainless) sheath, which offers ten times the life of a mica band heater at only a slightly higher cost than mica, and considerably lower than ceramic band and aluminum shoe designs.

Flexible one-piece construction for easy installation and removal.

The unheated section between heated halves functions as a hinge and permits repeated opening and closing for moving heaters from one application to another. The heavy duty spring loaded clamping bolt pulls the heater tight to the work and maintains tightness by compensating for expansion.

Heavy duty – uses a pair of formed 240V OMEGALUX® PT series strip heaters.

Spring loaded – for tight fit with Inconel-x spring and nickel-plated clamping bolts and nuts— maintains tightness.

Uniform high temperature capability. Highly compacted refractory insulation assures efficient heat transfer, therefore lower resistance wire temperatures.

SPECIFICATIONS

Power: 240/480V**

Wattage: 750 to 3250 watts

Sheath Material: Chrome Steel

Maximum Sheath Temperature: 649°C (1200°F)

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters