

## CORROSION RESISTANT OVER-THE-SIDE IMMERSION HEATERS

TPR Series Starts at  
**\$488**



### TPR—Round Cross Section Elements

- ✓ Fluoropolymer Coated Stainless Steel Elements
- ✓ 20 W/in<sup>2</sup>
- ✓ 1 to 8 kW
- ✓ 120, 240 and 480V, 1 Phase
- ✓ Moisture Resistant Terminal Enclosure

### FEATURES



- ✓ Moisture Resistant Terminal Enclosure
- ✓ Standard Polypropylene Guard
- ✓ Side Mounted Construction with PVC Mounting Flange
- ✓ Overtemperature Protection Integral Manual Reset Cutout [116°C (240°F)]
- ✓ Low Profile, Light Weight

#### 1. Corrosion Resistant:

Thermoplastic fluoropolymer coated stainless steel sheath for long life in almost all types of corrosive solutions for operating temperatures up to 212°F. Pin hole free, durable coating, 100% tested at factory.

#### 2. Overtemperature Shutoff:

Standard on all units. A manual reset cutout will deactivate the heater in the event of an overtemperature condition (rated 25 amps up to 277 volts). A visual minimum level indication is also provided on the heater guard.




**3. Low Profile:** Single and three phase heaters have flat profiles which permit maximum work area and minimum interference with plating process. Heater projects less than 2" away from the side of the tank.

*Continued on page 114*

### CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



**MOST POPULAR MODEL HIGHLIGHTED!**

### To Order (Specify Model Number)

Watts	Volts	Dimensions: cm (in)		Model No.	Price	Weight kg (lb)
		A	B			
1000	120	33 (13)	15 (6)	<b>TPR-101</b>	<b>\$488</b>	2 (4)
1000	240	33 (13)	15 (6)	TPR-102	488	2 (4)
2000	240	53 (21)	30 (12)	TPR-202	579	2 (5)
2000	480	53 (21)	30 (12)	<b>TPR-204</b>	<b>597</b>	2 (5)
3000	240	66 (26)	43 (17)	TPR-302	733	3 (6)
3000	480	66 (26)	43 (17)	TPR-304	733	3 (6)
4000	240	79 (31)	56 (22)	TPR-402	940	3 (7)
4000	480	79 (31)	56 (22)	TPR-404	940	3 (7)
6000	240	107 (42)	84 (33)	TPR-602	1173	5 (10)
6000	480	107 (42)	84 (33)	TPR-604	1173	5 (10)
8000	240	135 (53)	112 (44)	TPR-802	1577	5 (12)
8000	480	135 (53)	112 (44)	TPR-804	1577	5 (12)

Ordering Example: TPR-202 single phase, round cross section element immersion heater, 2000 W, 240V, \$579.

## CORROSION RESISTANT OVER-THE-SIDE IMMERSION HEATERS

TPF Series  
Starts at  
**\$915**





### TPF—Flat Elements

- ✓ Fluoropolymer Coated Stainless Steel Thinblade Elements
- ✓ 20 W/in<sup>2</sup>
- ✓ 3 to 10 kW
- ✓ 240 and 480V, 3 Phase
- ✓ Moisture Resistant Terminal Enclosure

### FEATURES

- ✓ Moisture Resistant Terminal Enclosure
- ✓ Standard Polypropylene Guard
- ✓ Side Mounted Construction with PVC Mounting Flange
- ✓ Overtemperature Protection Integral Manual Reset Cutout (240°F)
- ✓ Low Profile, Light Weight


4. **Vapor Tight Terminal:** Enclosure of PVC material with left or right hand conduit entry.
5. **Mounting Bracket:** Made of PVC material with conveniently located mounting slots.
6. **Polypropylene Guard:** Standard on all units. It protects the heater from work in process in heating tank. Guard easily disassembles for ease of cleaning heating elements.
7. **Grounded Construction:** With metal sheath heating elements to allow for proper grounding safety.



8. **Low Watt Density:** 20 watts per square inch heat output suitable for almost all corrosive solutions.
9. **Light Weight:** Simple design permits easy installation and removal for cleaning.

### CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



**MOST POPULAR MODEL HIGHLIGHTED!**

### To Order (Specify Model Number)

Watts	Volts	Dimensions: cm (in)		Model No.	Price	Weight kg (lb)
		A	B			
3000	240	51 (20)	28 (11)	<b>TPF-302</b>	<b>\$915</b>	4 (8)
3000	480	51 (20)	28 (11)	<b>TPF-304<sup>1</sup></b>	<b>795</b>	4 (8)
4000	240	58 (23)	36 (14)	<b>TPF-402</b>	<b>1017</b>	4 (9)
4000	480	58 (23)	36 (14)	<b>TPF-404<sup>1</sup></b>	<b>1017</b>	4 (9)
6000	240	76 (30)	53 (21)	<b>TPF-602</b>	<b>1315</b>	5 (11)
6000	480	76 (30)	53 (21)	<b>TPF-604<sup>1</sup></b>	<b>1315</b>	5 (11)
8000	240	94 (37)	71 (28)	<b>TPF-802</b>	<b>1574</b>	5 (12)
8000	480	94 (37)	71 (28)	<b>TPF-804<sup>1</sup></b>	<b>1574</b>	5 (12)
10000	240	112 (44)	89 (35)	<b>TPF-1002</b>	<b>1945</b>	6 (14)
10000	480	112 (44)	89 (35)	<b>TPF-1004<sup>1</sup></b>	<b>1945</b>	6 (14)

<sup>1</sup> Not UL Listed or CSA Certified.

Ordering Example: TPF-404 three phase, flat element immersion heater, 4000 W, 480V, \$1017. It is not UL Listed or CSA Certified.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters