


# STRAIN, PROCESS, AND TEMPERATURE METERS

## WITH OPTIONAL RELAYS AND ANALOG OUTPUT

### DP25B Series



DP25B, shown close to actual size.

#### Inputs

- ✓ Thermocouple
- ✓ RTD
- ✓ Process (DC Voltage and Current)
- ✓ Strain Gage



#### Options

- ✓ Relay Output with Adjustable Deadband
- ✓ Isolated or Non-Isolated Analog Output
- ✓ Totally Programmable Color Display
- ✓ Low-Voltage Power Options

#### Panel Meters/Controllers

The OMEGA® DP25B Series meters have the biggest, brightest display of any 1/8 DIN panel meter. The user can select the display color: **RED**, **AMBER**, or **GREEN**.

Along with the 4-digit, 9-segment display, these low-cost panel meters/controllers provide unparalleled accuracy in signal conditioning. Additional features include microprocessor-based operation; dual 5 A SPDT relays (optional); and isolated or non-isolated analog output in ranges of 0 to 10 Vdc, 0 to 20 mA, or 4 to 20 mA, which can be used for retransmission of the display value or as a proportional control output. The DP25 Series includes models with inputs for process (DC voltage and current), strain gages, thermocouples, and RTDs.

#### Thermocouple and RTD Models

These models combine versatility with ease of programming. The DP25B-TC is selectable for J, K, T, or J DIN thermocouples. The DP25B-RTD accepts 100 Ω Pt (0.00385 curve) RTDs.

#### SPECIFICATIONS

**Display:** 4-digit, 9-segment, 21 mm (0.83") high red, amber or green LED (programmable)

**Analog-to-Digital Technique:** Dual slope

**Internal Resolution:** 15-bit

**Polarity:** Automatic

**Read Rate:** 3/s

**Step Response:** 2 s

**Relay Outputs (Optional):** 2 form "C" (SPDT) relays rated 5 A 250 Vac, programmable for active high/low alarms with latching/non-latching relays

**MONOGRAM SERIES**

**PATENTED**

Covered by U.S. and International patents and pending applications

#### DP25B-TC (Thermocouple)

INPUT TYPE	RANGE		ACCURACY
J	-210 to 760°C	-346 to 1400°F	0.5°C (0.9°F)
K	-270 to 1372°C	-454 to 2500°F	
T	-210 to 400°C	-346 to 752°F	
J DIN	-200 to 900°C	-328 to 1652°F	

**Analog Output (Optional):** 0 to 10 V, 4 to 20 mA or 0 to 20 mA; can be assigned to a display range (scalable) or proportional control output with setpoint #1 when used as a control output

**Power:** 115 Vac or 230 Vac ±10%, 10 to 32 Vdc, 26 to 56 Vdc; 8 W max (DP25B-TC or -RTD), 11 W max (DP25B-E or -S); 240 Vrms overvoltage protection

**Isolation:** Dielectric strength to 2500 V transient per 3 mm spacing based on EN61010 for 260 Vrms or Vdc

**NMR:** 60 dB

**CMR:** 120 dB

**Operating Temperature:** 0 to 50°C (32 to 122°F)

**Storage Temperature:** -40 to 85°C (-40 to 185°F)

**Relative Humidity:** 90% @ 40°C (104°F), non-condensing

**Dimensions:** 48 H x 96 W x 152 mm D

(1.89 x 3.78 x 6.0")

**Panel Cutout:** 45 H x 92 mm W (1.772 x 3.622")

**Weight:** 36 g (1.27 lb)

#### THERMOCOUPLE METER SPECIFICATIONS

**Input:** T/C types J, K, T and J DIN

**Relay Hysteresis:**

Programmable from 0 to 9999

**Accuracy:** ±0.5°C (0.9°F) after 30 min warm-up

**Temperature Coefficient:** ±50 ppm/°C

**Input Resistance:** 100 MΩ



# STRAIN, PROCESS, AND TEMPERATURE METERS

## Process and Strain Models

Because they accept a wide range of DC voltage and current inputs, the DP25-B-E strain meters can handle most process and strain applications. Features include easy front-panel scaling to virtually any engineering units, a remote tare function for weighing applications, and a hardware lockout to prevent unauthorized changes in setup. In addition, the DP25B-E meters feature built-in excitation in 4 user-selectable voltages, which makes them compatible with most transducers and transmitters.



DP25B-TC, \$245, programmed for optional green display, shown larger than actual size.

## DP25B-RTD (RTD)

INPUT TYPE	RANGE	ACCURACY
RTD, 100 Ω Pt, 2-, 3-, 4-wire	-200 to 850°C (-328 to 1562°F)	0.5°C (0.9°F)

## SPECIFICATIONS (RTD Temperature Meter/Controller)

**Input:** RTD 100 Ω Pt (0.00385 curves); 2-, 3- and 4-wire selectable  
**Accuracy:** ±0.5°C (0.9°F) after 30 min warm-up  
**Temperature Coefficient:** ±50 ppm/°C  
**Input Resistance:** 100 MΩ



## Select Your Color!

Program to Display in **RED**, **AMBER**, or **GREEN**.

## PROCESS AND STRAIN METERS DP25B-E (Process)/DP25B-S (Strain)

INPUT TYPE	RANGE	ACCURACY
mV, V, mA	0 to 100 mV, ±50 mV, 0 to 10 V ±5 V, 0 to 20 mA, 4 to 20 mA	0.02% rdg

## SPECIFICATIONS (Process and Strain Meters/Controllers)


**Input Ranges:** 0 to 100 mV, ±50 mV, 0 to 10 V, ±5 V, 0 to 20 mA, 4 to 20 mA  
**Protection:** 240 Vrms max for voltage input ranges; 200 mA for current ranges  
**Input Impedance:** 100 MΩ for 100 mV or ±50 mV range; 1 MΩ for 10 V or ±5 V range; 5 Ω for 20 mA current input  
**Analog-to-Digital Technique:** Dual slope  
**Internal Resolution:** 15-bit  
**Polarity:** Automatic  
**Max Error Strain/Process:** ±0.03% rdg  
**Span Temperature Coefficient:** ±50 ppm/°C  
**Warm-Up to Rated Accuracy:** 30 min  
**Excitation Voltage:** 24 V @ 25 mA or 12 V @ 50 mA; 10 V @ 120 mA or 5 V @ 60 mA

## Totally Programmable Color Displays

The OMEGA® DP25B Series meters and controllers have totally programmable color displays—for **RED**, **AMBER**, or **GREEN**.



**Dimensions: mm (in)**



Please visit [omega.com](http://omega.com) and search panel punches.

**CUSTOM CONFIGURATIONS**

Custom firmware and hardware available in quantity.

**CUSTOM COLORS**

Custom-color bezels and enclosures are available for original equipment manufacturers.

Enhance the appearance of your equipment design with custom colors.

Consult the **OMEGA® OEM GROUP** at 1-856-467-4200




**CE** The following LVD (Low Voltage Directive/Safety) requirements have been met to comply with EN 61010-1, 1993 (Electrical equipment for measurement, control and laboratory use)

- 1. Pollution Degree 2      2. Installation Category II      3. Double Insulation
- DP25/DP26/PHCN-37/ORCN-37/OPCN-37 complies with the following EMC Immunity Standards as tested per EN 50082-2, 1995 (Industrial environment)

Phenomena	Test Specification	Basic Standard
Electrostatic Discharge	+/- 4 kV contact discharge +/- 8 kV air discharge	IEC 1000-4-2 Perf. Criteria B
Radio Frequency electromagnetic field	27 - 1000 MHz 10 V/m 80% AM (1 KHz)	IEC 1000-4-3 Perf. Criteria A
Fast Transients	+/- 2 kV (ac mains) +/- 1 kV (dc, signal I/O) 5/50 ns Tr/Th, 5 KHz repet. Freq.	IEC 1000-4-4 Perf. Criteria B
Radio Frequency conducted	0.15 - 80 MHz 10 V/m 80% AM (1 KHz)	IEC 1000-4-6 Perf. Criteria A
Surges	+/- 2 kV line to earth +/- 1 kV line to line 1.2/50 (8/20) _s Tr/Th	IEC 1000-4-5 Perf. Criteria B
Voltage Dips	30% reduction 10 ms 60% reduction 100 ms	IEC 1000-4-11 Perf. Criteria B
Voltage Interruption	>95% reduction 5000 ms Perf. Criteria C	IEC 1000-4-11

DP25/DP26/PHCN-37/ORCN-37/OPCN-37 comply with the following EMC Emission Standards as tested per EN 50081-1, 1997 (Residential, Commercial and Light Industrial)

Phenomena	Frequency Range	Limits	Basic Standard
Radiated Emission	30 - 230 MHz 230 - 1000 MHz	30 dB_V/m at 10 m 37 dB_V/m at 10 m quasi peak	CISPR 22 Class B
Conducted Emission	0.15-0.5 MHz 0.5-5 MHz 5-30 MHz	66-56 dB_V q_peak 56 dB_V quasi peak 60 dB_V quasi peak	CISPR 22 Class B



**MOST POPULAR MODELS HIGHLIGHTED!**

**To Order (Specify Model Number)**

MODEL NO.	DESCRIPTION
DP25B-TC	Thermocouple
DP25B-RTD	RTD
DP25B-E	Process (DC voltage and current)
DP25B-S	Strain input

**POWER OPTIONS\***

ORDER SUFFIX	POWER
-230	230 Vac
-DC10/32	10 to 32 Vdc
-DC26/56	26 to 56 Vdc

**OUTPUT OPTIONS\***

ORDER SUFFIX	POWER
-A	Analog output
-AI-R	Isolated analog output
-R	Dual 5 A relays
-AR	Analog and relay options

**ACCESSORY**

MODEL NO.	DESCRIPTION
EE-2683	Reference Book: Microcontroller Based Temperature Monitoring and Control

\* Not field installable. For "-AI" option, the "-R" option is required. Comes with complete operator's manual. **Ordering Examples:** DP25B-TC-DC10/32-AR, thermocouple indicator for J, K, T or J DIN input, low-voltage power, analog output and dual 5 A relays. **DP25B-E**, process meter.



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters