

ALL STAINLESS STEEL TRANSDUCER MULTIMEDIA COMPATIBILITY HIGH-PERFORMANCE SILICON TECHNOLOGY



PX309 Series
4 to 20 mA Output
0-1 to 0-10,000 psi
0-70 mbar to 0-690 bar

Starts at
\$225



- ✓ 1, 2, and 5 psi Ranges
- ✓ Rugged, Solid State Design
- ✓ All Stainless Steel
- ✓ High Stability, Low Drift
- ✓ 0.25% Accuracy Typical
- ✓ RoHS Compliant
- ✓ IP65 Protection Class

SPECIFICATIONS

Excitation: 9 to 30 Vdc (reverse polarity and overvoltage protected)

Output: 4 to 20 mA

Accuracy: $\pm 0.25\%$ (includes linearity, hysteresis and repeatability)

Zero Offset: $\pm 2\%$ FSO, ($\pm 4\%$ 1 and 2 psi)

Span Setting: $\pm 2\%$ FSO, ($\pm 4\%$ 1 and 2 psi)

Total Error Band: $\pm 2\%$ (except 1 psi = $\pm 4.5\%$ and 2 psi = $\pm 3\%$) FSO, includes linearity, hysteresis, repeatability, thermal hysteresis and thermal errors

Long-Term Stability (1 Year): $\pm 0.25\%$ typical

Typical Life: 10 million cycles

Operating Temperature: -40 to 85°C (-40 to 185°F)

Compensated Temperature:

>5 psi Range: -20 to 85°C (-4 to 185°F)

≤5 psi Range: 0 to 50°C (-18 to 122°F)

Proof Pressure:

psia and ≤50 psig: 3x capacity or 20 psi, whichever is greater

≥100 psi: 2x capacity

Burst Pressure: 500% capacity or 25 psi, whichever is greater

Response Time: <1 ms

Shock: 50 g, 11 ms half-sine shock

Vibration: ± 20 g


PX309-100GI, \$225, shown smaller than actual size.



Engineered from 1 to 10,000 psi.


New Low Ranges: 1, 2, and 5 psi.

PX329-100GI, \$275, shown smaller than actual size.



Fast Delivery!

PX319-100GI, \$225, shown smaller than actual size.



Included

Wetted Parts: 316 SS for all psia ranges and 1 to 50 psig; 17-4 PH SS for ranges 100 to 10,000 psig

Pressure Port: 1/4-18 MNPT

Electrical Connections:

PX309: 1.5 m (5') 2-conductor cable

PX319: Mini DIN connector with mating connector included

PX329: Twist-lock connector, mating connector sold separately (PT06V-10-6S)

Weight: 155 g (5.4 oz) max

Note: Units 100 psig and above may be subjected to vacuum on the pressure port without damage

For alternative performance specifications, contact Engineering.



Order a snubber to protect your pressure transducer!



PS-4G, \$10, shown actual size.

Snubbers protect sensors from fluid hammers/spikes.




CURRENT OUTPUT
PRESSURE TRANSDUCERS

B



RUGGED, GENERAL PURPOSE TRANSDUCER



NEW, LOW-PRESSURE RANGES HIGHLIGHTED

To Order (Specify Model Number)

RANGE		1.5 m CABLE CONNECTION	PRICE	MINI DIN CONNECTION	PRICE	TWIST-LOCK CONNECTION	PRICE
bar	psi						
ABSOLUTE PRESSURE							
0 to 0.34	0 to 5	PX309-005AI	\$325	PX319-005AI	\$325	PX329-005AI	\$350
0 to 1	0 to 15	PX309-015AI	245	PX319-015AI	245	PX329-015AI	295
0 to 2.1	0 to 30	PX309-030AI	245	PX319-030AI	245	PX329-030AI	295
0 to 3.4	0 to 50	PX309-050AI	245	PX319-050AI	245	PX329-050AI	295
0 to 6.9	0 to 100	PX309-100AI	245	PX319-100AI	245	PX329-100AI	295
0 to 14	0 to 200	PX309-200AI	245	PX319-200AI	245	PX329-200AI	295
0 to 21	0 to 300	PX309-300AI	245	PX319-300AI	245	PX329-300AI	295
GAGE PRESSURE							
0 to 0.07	0 to 1	PX309-001GI	\$345	PX319-001GI	\$345	PX329-001GI	\$370
0 to 0.14	0 to 2	PX309-002GI	325	PX319-002GI	325	PX329-002GI	350
0 to 0.34	0 to 5	PX309-005GI	300	PX319-005GI	300	PX329-005GI	300
0 to 1	0 to 15	PX309-015GI	225	PX319-015GI	225	PX329-015GI	275
0 to 2.1	0 to 30	PX309-030GI	225	PX319-030GI	225	PX329-030GI	275
0 to 3.4	0 to 50	PX309-050GI	225	PX319-050GI	225	PX329-050GI	275
0 to 6.9	0 to 100	PX309-100GI	225	PX319-100GI	225	PX329-100GI	275
0 to 10	0 to 150	PX309-150GI	225	PX319-150GI	225	PX329-150GI	275
0 to 14	0 to 200	PX309-200GI	225	PX319-200GI	225	PX329-200GI	275
0 to 21	0 to 300	PX309-300GI	225	PX319-300GI	225	PX329-300GI	275
0 to 34	0 to 500	PX309-500GI	225	PX319-500GI	225	PX329-500GI	275
0 to 69	0 to 1000	PX309-1KGI	225	PX319-1KGI	225	PX329-1KGI	275
0 to 138	0 to 2000	PX309-2KGI	225	PX319-2KGI	225	PX329-2KGI	275
0 to 207	0 to 3000	PX309-3KGI	225	PX319-3KGI	225	PX329-3KGI	275
0 to 345	0 to 5000	PX309-5KGI	225	PX319-5KGI	225	PX329-5KGI	275
0 to 517	0 to 7500	PX309-7.5KGI	225	PX319-7.5KGI	225	PX329-7.5KGI	275
0 to 690	0 to 10,000	PX309-10KGI	225	PX319-10KGI	225	PX329-10KGI	275

Comes with certificate of conformance to specifications.

Ordering Examples: PX309-100GI, 100 psi gage pressure transducer with 4 to 20 mA output and 1.5 m cable termination, \$225. PX319-015AI, 15 psi absolute pressure transducer with 4 to 20 mA output and mini DIN termination, \$300. PX329-3KGI, 3000 psi gage pressure transducer with 4 to 20 mA output and twist-lock termination, \$275. Mating connector sold separately; order PT06V-10-6S, \$26.50.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
-NIST	\$75.00	5-point NIST-traceable calibration (must be ordered as a suffix with new transducer)
CAL-3	150.00	Recalibration: 5-point NIST traceable
PT06V-10-6S	26.50	Mating twist-lock connector for PX329
CA-39-4PC22-5	90.00	Mating twist-lock connector with 1.5 m (5') cable for PX329
CX5302	15.00	Extra mating mini DIN connector for PX319
ES-2272	190.00	Reference Book: Handbook of Heating, Ventilation, and Air Conditioning



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters