

Economical Pressure Transducer



PXM4100
From
£110
with mV Output

PXM4100 Series
0 to 700 bar
0 to 20 mV, 0 to 10V or
4 to 20mA Outputs

- ✓ 17/4PH Stainless Steel Diaphragm (>10 bar)
- ✓ Micro DIN Connector
- ✓ Gauge and Absolute Models

Specifications

mV Output:-
Excitation: 10 Vdc (15 V max.)
Supply Effects: Ratiometric
Output: 0-20 mV ($\pm 1\%$)
Input/Output Impedance:
 1 k Ω $\pm 30\%$ for SS, 15 k Ω $\pm 30\%$ ceramic
Power requirements: 10 mA
10V Output:-

Excitation: 13 to 30 Vdc
Supply Effects: 11 μ V/V
Output: 0-10 Vdc
Load Driving Capability: 5 Ω
4-20mA Output:-
Excitation: 13 to 36 Vdc
Supply Effects: 3 μ V/V
Output: 4-20 mA, 2 wire
Load Driving Capability:
 1150 Ω @ 36 Vdc

General:-
Zero Offset: $< \pm 1\%$ FSO
Combined Non-linearity/hysteresis: $< \pm 0.25\%$ FSO
Repeatability: $< \pm 0.1\%$ FSO
Long Term Stability:
 $< \pm 0.2\%$ FSO/6 Mths
Operating Temperature Range:
 -20 to +80°C
Storage Temperature Range:
 -40 to +90°C
Thermal Zero Effect: $< \pm 0.03\%$ FSO/°C
Thermal Span Effect: $< \pm 0.04\%$ FSO/°C
Vibration Tolerance: 10g's to 50Hz
Maximum Overpressure: 200% Range
Pressure Connection: 1/4" BSP male
Electrical Connection:
 Micro DIN plug and Socket to DIN43650 or 1m PVC screened cable.
Diaphragm:
 17/4PH >10bar, Ceramic <10 bar
Enclosure Rating: IP65
Weight: 75 g

OMEGA's PXM4100 series pressure transducers have been designed specifically for general-purpose applications where reliable pressure measurement is required. Incorporating the latest strain gauge technology and using unique manufacturing techniques has resulted in a low cost, quality transducer, ideal for OEM applications.

MOST POPULAR MODELS HIGHLIGHTED

How To Order (Specify Model Number)				
RANGE (bar)	MODEL NO.	PRICE mV	PRICE mA or V	COMPATIBLE METERS
		Output	Output	
0 to 1	PXM410[+]-001[*]	£135	£135	i-SERIES™, DP25B
0 to 1.6	PXM410[+]-1.60[*]	135	135	i-SERIES™, DP25B
0 to 2.5	PXM410[+]-2.50[*]	135	135	i-SERIES™, DP25B
0 to 4	PXM410[+]-004[*]	135	135	i-SERIES™, DP25B
0 to 6	PXM410[+]-006[*]	135	135	i-SERIES™, DP25B
0 to 10	PXM410[+]-010[*]	110	135	i-SERIES™, DP25B
0 to 16	PXM410[+]-016[*]	110	135	i-SERIES™, DP25B
0 to 25	PXM410[+]-025[*]	110	135	i-SERIES™, DP25B
0 to 40	PXM410[+]-040[*]	110	135	i-SERIES™, DP25B
0 to 60	PXM410[+]-060[*]	110	135	i-SERIES™, DP25B
0 to 100	PXM410[+]-100[*]	110	135	i-SERIES™, DP25B
0 to 160	PXM410[+]-160[*]	110	135	i-SERIES™, DP25B
0 to 250	PXM410[+]-250[*]	110	135	i-SERIES™, DP25B
0 to 400	PXM410[+]-400[*]	110	135	i-SERIES™, DP25B
0 to 700	PXM410[+]-700G	110	135	i-SERIES™, DP25B

+Insert 0 for 0-20mV, 1 for 0-10V or 3 for 4-20mA Output.
 *Insert G for Gauge, A for Absolute Pressure Ranges
 Supplied standard with Micro DIN plug and Socket.

Ordering Example: PXM4100-010G, Pressure Transducer, 0-10bar Gauge Pressure Range, Micro DIN output connector and 0-20mV Output £110



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters