

HIGH-ACCURACY CURRENT OUTPUT TRANSDUCER

7/16-20 OR 1/4 NPT CONNECTIONS

PX02 Series
4 to 20 mA Output
0-2 to 0-30,000 psi
0-150 mbar to 0-2000 bar



PX02K1-100GI,
NPT connector
style, \$650,
shown smaller
than actual size.



PX02C0-100GI, NPT cable
style, \$670, shown smaller
than actual size.

Starts at
\$650



- ✓ High Accuracy
- ✓ FM Intrinsically Safe
- ✓ 5-Point Calibration Provided
- ✓ All Stainless Steel Construction

- ✓ Hermetically Sealed Design for Harsh Environments
- ✓ Available in Gage, Absolute, Sealed Gage, psi, and Metric Ranges
- ✓ Cable or Connector Models

✓ Optional Pressure Ports to Fit Most Industrial Applications

OMEGA's PX02 is a high-accuracy industrial pressure transmitter. All stainless steel construction and a sealed case make the PX02 suitable for harsh industrial

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

RANGE	7/16-20 MODEL NO.	PRICE	1/4 NPT MODEL NO.	PRICE	COMPATIBLE METERS†	
ABSOLUTE PRESSURE (All Ranges Available in Absolute Pressure)						
0 to 10 psi	0 to 0.69 bar	PX02K1-010AI	\$765	PX02C1-010AI	\$785	DP41-E, DP25B-E
0 to 15 psi	0 to 1.0 bar	PX02K1-015AI	765	PX02C1-015AI	785	DP41-E, DP25B-E
0 to 20 psi	0 to 1.4 bar	PX02K1-020AI	765	PX02C1-020AI	785	DP41-E, DP25B-E
0 to 25 psi	0 to 1.7 bar	PX02K1-025AI	765	PX02C1-025AI	785	DP41-E, DP25B-E
0 to 50 psi	0 to 3.4 bar	PX02K1-050AI	700	PX02C1-050AI	720	DP41-E, DP25B-E
GAGE PRESSURE (All Ranges Also Available in Sealed Gage Pressure)						
0 to 2 psi	0 to 0.14 bar	PX02K1-002GI	\$715	PX02C1-002GI	\$735	DP41-E, DP25B-E
0 to 5 psi	0 to 0.34 bar	PX02K1-005GI	715	PX02C1-005GI	735	DP41-E, DP25B-E
0 to 10 psi	0 to 0.69 bar	PX02K1-010GI	715	PX02C1-010GI	735	DP41-E, DP25B-E
0 to 15 psi	0 to 1.0 bar	PX02K1-015GI	715	PX02C1-015GI	735	DP41-E, DP25B-E
0 to 50 psi	0 to 3.4 bar	PX02K1-050GI	650	PX02C1-050GI	670	DP41-E, DP25B-E
0 to 75 psi	0 to 5.2 bar	PX02K1-075GI	650	PX02C1-075GI	670	DP41-E, DP25B-E
0 to 100 psi	0 to 6.9 bar	PX02K1-100GI	650	PX02C1-100GI	670	DP41-E, DP25B-E
0 to 200 psi	0 to 13.8 bar	PX02K1-200GI	650	PX02C1-200GI	670	DP41-E, DP25B-E
0 to 300 psi	0 to 20.7 bar	PX02K1-300GI	650	PX02C1-300GI	670	DP41-E, DP25B-E
0 to 500 psi	0 to 34.5 bar	PX02K1-500GI	650	PX02C1-500GI	670	DP41-E, DP25B-E
0 to 1000 psi	0 to 68.9 bar	PX02K1-1KGI	650	PX02C1-1KGI	670	DP41-E, DP25B-E
0 to 1500 psi	0 to 103 bar	PX02K1-1.5KGI	650	PX02C1-1.5KGI	670	DP41-E, DP25B-E
0 to 2000 psi	0 to 138 bar	PX02K1-2KGI	650	PX02C1-2KGI	670	DP41-E, DP25B-E
0 to 3500 psi	0 to 241 bar	PX02K1-3.5KGI	650	PX02C1-3.5KGI	670	DP41-E, DP25B-E
0 to 5000 psi	0 to 345 bar	PX02K1-5KGI	650	PX02C1-5KGI	670	DP41-E, DP25B-E
0 to 7500 psi	0 to 517 bar	PX02K1-7.5KGI	650	PX02C1-7.5KGI	670	DP41-E, DP25B-E
0 to 10,000 psi**	0 to 689 bar	PX02S1-10KGI	750	not available		DP41-E, DP25B-E*
0 to 20,000 psi**	0 to 1379 bar	PX02S1-20KGI	750	not available		DP41-E, DP25B-E*
0 to 30,000 psi**	0 to 2068 bar	PX02S1-30KGI	750	not available		DP41-E, DP25B-E*

Comes with 5-point calibration.

* 4-digit meter, counts in increments of 10. ** 1/4 HP tube fitting. † See section D for compatible meters.

To order absolute pressure, replace "G" in model number with "A" and add \$50.

To order sealed gage units, replace "G" in model number with "S" (no extra charge).

Ordering Examples: PX02K1-1KGI, 1000 psi gage transducer with 4 to 20 mA output, twist lock connector and 7/16-20 female pressure connection, \$650. PT06F-10-6S, mating connector (not included), \$26.50. PX02C0-010GI, 10 psi gage transducer with 4 to 20 mA output, 3 m (10') cable and 1/4 NPT male pressure connection, \$735.

HIGH-ACCURACY ALL STAINLESS STEEL TRANSDUCER

environments. It is a true high-accuracy industrial device with FM/CSA Intrinsic Safety approvals standard. A broad temperature-compensated range of 16 to 71°C (60 to 160°F) and a high operating range to 121°C (250°F) make this transducer very stable for applications with fluctuating temperatures.

The PX02 is available in gage, absolute, or sealed models, as well as in psi or metric ranges. NPT and 1/16-20 O-ring seal fittings are available for industrial and hydraulic applications.

SPECIFICATIONS

4 to 20 mA Output

Excitation: 10 to 40 Vdc

Output: 4 to 20 mA ±10% adj

Zero Balance: 4 mA +10% -2% adj

Linearity: ±0.15% FSO

Hysteresis: ±0.1% FSO

Repeatability: ±0.05% FSO

Sensing Element: 4-active-arm bridge, using thick-film strain gages in a hermetically sealed chamber (except gage units)

Operating Temp Range: -46 to 121°C (-50 to 250°F)

Compensated Temp Range: 16 to 71°C (60 to 160°F)

Thermal Effects:
Span: 0.005% FSO/°F
Zero: 0.005% FSO/°F

Proof Pressure: 150% of rated pressure

Burst Pressure: 300% of rated pressure

Wetted Parts: 17-4 PH stainless steel

Pressure Port: Ranges <10000 psi: 1/16-20 UNF female
Also available: 1/4-18 NPT M/F ranges
10,000-30,000 psi = 1/8-18, 1/4" HP tube

Electrical Connection: PTIH-10-6P or equal. Also available: 3 m (10') 2-conductor cable; explosion-proof amplifier housing

Mating Connector: PT06F10-6S (not included), metric ranges available

Weight: 388 g (13.7 oz)

CUSTOM CONFIGURATIONS

SERIES PX02	PRESSURE PORT [1]	ELECTRICAL CONNECTION [2]	RANGE (psi) [3]	UNITS [4]	OUTPUT [5]	OPTIONS [6]
Models < 10,000 psi			002*	S,G,A	V = mV/V output base price all ranges	OL = Overload stops +\$65 (when available)
C = 1/4-18 NPT-M +\$20			005*	S,G,A		
D = 1/4-18 NPT-F, no charge			010	S,G,A	5T = 0 to 5 Vdc output +\$155 all ranges	OX = Cleaned for oxygen service +\$75 plus 2 weeks
J = 1/16-20 UNF-M +\$20			015	S,G,A		
K = 1/16-20 UNF-F, no charge			020	S,G,A	5Z = Isolated 0 to 5 Vdc output +\$190 all ranges	See page B-12 for additional options, including extended temperature ranges.
Models ≥10,000 psi			025	S,G,A		
S = 1/4 HP tube fitting no charge			050	S,G,A	10T= 0 to 10 Vdc output +\$155 all ranges	
			075	S,G,A		
			100	S,G,A	I = 4 to 20 mA output +\$175 all ranges	
			150	S,G,A		
	0 = 3 m (10') cable (std) +\$2/ft over 3 m (10')		200	S,G,A		
	1 = PTIH-10-6P connector (or equal, no charge). Mating connector (not included), order PT06F-10-6S \$26.50		250	S,G,A		
	5 = Lightning-protected amplifier box (no charge) (4 to 20 mA models only)		300	S,G,A		
	6 = DIN connector		500	S,G,A		
			750	S,G,A		
			1K	S,G,A		
			1.5K	S,G,A		
			2K	S,G,A		
			3K	S,G,A		
			3.5K	S,G,A		
			5K	S,G,A		
			7.5K	S,G,A		
			10K†	S,G,A		
			20K†	S,G,A		
			30K†	S,G,A		


* 2 and 5 psi ranges available only on amplified output.

† Supplied with 1/4 HP tube fitting.


Ordering Examples: PX02C1-100GI, 100 psi gage pressure transducer with 1/4-18 NPT male fitting, PTIH-10-6P, connector, and 4 to 20 mA output, \$475 + 175 + 19 = \$670. PT06F-10-6S, mating connector (not included), \$26.50. PX02K0-1KS5Z, 1000 psi sealed gage pressure transducer with 1/16-20 UNF female fitting, 3 m (10') cable and isolated 0 to 5 output, \$475 + 190 = \$665. PX02J1-015A5T, 15 psi absolute pressure transducer with 1/16-20 UNF male fitting, PTIH-10-6P, connector, and a 0 to 5 Vdc output, \$540 + 155 + 19 = \$714. PT06F-10-6S, mating connector (not included), \$26.50. PX02K1-025GV-FM, 25 psi gage pressure transducer with 1/16-20 UNF female fitting, PTIH-10-6P, connector, mV/V output and FM Hazardous Locations rating, \$540 + 150 = \$690.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4355	\$80	Reference Book: Automated Continuous Process Control



"C" and "D" Fittings



CURRENT OUTPUT
PRESSURE TRANSDUCERS

B

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters