



1/8 DIN Digital Panel Meters For DC Voltage and Current Inputs

Panel Punches Available, Visit omega.com/panelpunches

DP63600
Starts at
\$254



DP63600-DC, \$254, shown smaller than actual size.



- ✓ Universal DC Input
- ✓ Green Display or Red Sunlight-Readable Display
- ✓ 5-Digit, 14.2 mm (0.56") LED
- ✓ 4 V (300 Vdc Max) and 5 Current (2A dc Max) Ranges
- ✓ 3 Resistance Ranges—10 KΩ Max
- ✓ Field-Upgradeable Option Cards
- ✓ AC and DC Powered Versions
- ✓ NEMA 4X (IP65)

The DP63600 Series panel meters offer many features and performance capabilities suitable for a wide range of industrial applications. These meters accept universal DC voltage/current inputs. The optional plug-in output cards allow the opportunity to configure the meter for present applications, while providing easy upgrades for future needs.

The meters employ a bright, 14.2 mm (0.56") LED display. The unit is available with a red sunlight readable or a standard green LED. The intensity of display can be adjusted from dark room to sunlight readable, making it ideal for viewing in variable light applications.

The meters provide a max and min reading memory with programmable capture time. The capture time is used to prevent detection of false max or min readings which may occur during start-up or unusual process events.

The meters have 4 setpoint outputs, implemented on plug-in option cards. The plug-in cards provide dual form "C" relays (5A), quad form "A" (3A), or either quad-sinking or quad-sourcing open collector logic outputs. The setpoint alarms can be configured to suit a variety of control and alarm requirements. Communication and bus capabilities are also available as option cards; these include RS232, RS485, and MODBUS®.

Specifications

Display: 5-digit, 14.2 mm (0.56") red sunlight readable or standard green LEDs, (-19999 to 99999)

Power:

AC Versions:

AC Power: 85 to 250 Vac, 50/60 Hz, 15 VA

Isolation: 2300 Vrms for 1 minute to all inputs and outputs

DC Power: 11 to 36 Vdc, 11 W (derate operating temperature to 40°C if operating <15 Vdc and 3 plug-in option cards are installed)

AC Power: 24 Vac, ± 10%, 50/60 Hz, 15 VA

Isolation: 500 Vrms for 1 minute to all inputs and outputs (50V working)

Keypad: 3 programmable function keys, 5 keys total

A/D Converter: 16-bit resolution

Update Rates:

A/D Conversion Rate: 20 readings/s

Step Response: 200 ms max to within 99% of final readout value (digital filter and internal zero correction disabled), 700 ms max (digital filter disabled, internal zero correction enabled)

Display Update Rate: 1 to 20 updates/s

Setpoint Output On/Off Delay Time: 0 to 3275 seconds

Analog Output Update Rate: 0 to 10s

Max/Min Capture Delay Time: 0 to 3275 s

Memory: Non-volatile EEPROM retains all programmable parameters and display values

Environmental Conditions:

Operating Temperature Range: 0 to 50°C (32 to 122°F) [0 to 45°C (32 to 113°F) with all 3 plug-in cards installed]

Storage Temperature Range: -40 to 60°C (-40 to 140°F)

Operating and Storage Humidity: 0 to 85% max RH non-condensing

Altitude: Up to 2000 m (6562')

Connections: High-compression, cage-clamp terminal block

Construction: This unit is rated for NEMA 4X (IP65) outdoor use, IP20 touch-safe, Installation Category II, Pollution Degree 2, 1-piece bezel/case, flame-resistant, synthetic rubber keypad—panel gasket and mounting clip included

Weight: 295 g (10.4 oz)

Excitation Power

Transmitter Power: 24 Vdc, ±5%, regulated, 50 mA max

Reference Voltage: 2 Vdc, ±2%

Compliance: 1 kΩ load min (2 mA max)

Temperature Coefficient: 40 ppm/°C max

Reference Current: 1.75 mAdc, ±2%

Compliance: 10 kΩ load max

Temperature Coefficient: 40 ppm/°C max

Output Modules: For complete specifications, see LDP63100 Series, page M-100

DC Inputs


Input Range	Accuracy (18 to 28°C)	Accuracy (0 to 50°C)	Impedance/ Compliance	Max Continuous Overload	Resolution
±200 µAdc	0.03% of rdg + 0.03 µA	0.12% of rdg + 0.04 µA	1.11 kΩ	15 mA	10 nA
±2 mAdc	0.03% of rdg + 0.3 µA	0.12% of rdg + 0.4 µA	111 Ω	50 mA	0.1 µA
±20 mAdc	0.03% of rdg + 3 µA	0.12% of rdg + 4 µA	11.1 Ω	150 mA	1 µA
±200 mAdc	0.05% of rdg + 30 µA	0.15% of rdg + 40 µA	1.1 Ω	500 mA	10 µA
±2 Adc	0.5% of rdg + 0.3 mA	0.7% of rdg + 0.4 mA	0.1 Ω	3 A	0.1 mA
±200 mVdc	0.03% of rdg + 30 mV	0.12% of rdg + 40 mV	1.066 MΩ	100V	10 µV
±2 Vdc	0.03% of rdg + 0.3 mV	0.12% of rdg + 0.4 mV	1.066 MΩ	300V	0.1 mV
±20 Vdc	0.03% of rdg + 3 mV	0.12% of rdg + 4 mV	1.066 MΩ	300V	1 mV
±300 Vdc	0.05% of rdg + 30 mV	0.15% of rdg + 40 mV	1.066 MΩ	300V	10 mV
100 Ω	0.05% of rdg + 30 MΩ	0.2% of rdg + 40 MΩ	0.175V	30V	0.01 Ω
1000 Ω	0.05% of rdg + 0.3 Ω	0.2% of rdg + 0.4 Ω	1.75V	30V	0.1 Ω
10 kΩ	0.05% of rdg + 1 Ω	0.2% of rdg + 1.5 Ω	17.5V	30V	1 Ω

* After 20 minute warm-up. Accuracy is specified in two ways: Accuracy over an 18 to 28°C and 10 to 75% RH environment; and accuracy over a 0 to 50°C and 0 to 85% RH (non-condensing environment). Accuracy over the 0 to 50°C range includes the temperature coefficient effect of the meter.

Note: Recommended minimum clearance (behind the panel) for mounting clip installation is 53.4 (2.1) H x 127 (5) W.



Dimensions: mm (in)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description (Display Meter Only, No Outputs)
DP63600-DC	\$254	Universal DC inputs, red display, 85 to 250 Vac, 50/60 Hz
DP63600-DC-LV	282	Universal DC inputs, red display, 11 to 36 Vdc, 24 Vac
DP63600-DC-GN	269	Universal DC inputs, green display, 85 to 250 Vac, 50/60 Hz
DP63600-DC-GN-LV	297	Universal DC inputs, green display, 11 to 36 Vdc, 24 Vac

Optional Plug-in Output Cards (Field Installable)

Model No.	Price	Description
Setpoint Alarms (Only 1 Alarm Card Can Be Installed Into Base Meter)		
LDP6-CDS10	\$37	Dual setpoint relay output card
LDP6-CDS20	37	Quad setpoint relay output card
LDP6-CDS30	37	Quad setpoint sinking open collector output card
LDP6-CDS40	37	Quad setpoint sourcing open collector output card
Analog Output		
LDP6-CDL10	\$74	Analog output card
Communications (Only 1 Communications Card Can Be Installed Into Base Meter)*		
LDP6-CDC10	\$48	RS485 serial communications output card with terminal block
LDP6-CDC1C	48	Extended RS485 serial communications output card with dual RJ11 connector
LDP6-CDC20	48	RS232 serial communications output card with terminal block
LDP6-CDC2C	48	Extended RS232 serial communications output card with 9-Pin D connector
LDP6-CDC40	58	MODBUS communications card
LDP6-CDC4C	58	Extended MODBUS communications card with dual RJ11 connector

Accessory

Model No.	Price	Description
DPP-5	\$525	1/8 DIN panel punch

* Free software available at omega.com/dp63600-dc

Comes complete with operator's manual.

Note: Adding option cards—meters can be fitted with up to 3 optional plug-in cards, however, only 1 card from each function type can be installed at a time. The function types include setpoint alarms, analog output and communications. The cards can be installed initially or at a later date. Each optional plug-in card is shipped with installation and programming instructions.

Ordering Examples: DP63600-DC-GN, universal DC inputs, green display, 85 to 250 Vac, 50/60 Hz, and LDP6-CDL10 analog output card, \$269 + 74 = \$343.

DP63600-DC, universal DC inputs, red display, 85 to 250 Vac, 50/60 Hz, \$254.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters