


# Digital Video Camera

Works With **All** OMEGASCOPE™ IR Thermometers!

DV-CAM  
£50



## PATENTED

Patents issued and pending on many aspects of this device including but not limited to laser circle and distance measurement.

- ✓ 35 mm Colour LCD Display
- ✓ 32 MB Compact Flash Memory Card (Included)
- ✓ USB Port
- ✓ Built-In Microphone and Speaker
- ✓ Digital Video Camcorder
- ✓ Digital Still Camera
- ✓ Digital Voice Recorder
- ✓ Export to TV
- ✓ Display/Software Bundle
- ✓ Supports Windows 98SE/ME/2000/XP
- ✓ DV Cam Manager
- ✓ Microsoft® NetMeeting
- ✓ VideoLive Mail
- ✓ Ulead® DVD MovieFactory™ SE Basic
- ✓ Photo Express™
- ✓ Photo Explorer™
- ✓ 10 Second Self-Timer
- ✓ Power Saving/Auto Power-Off if Idle for Over 60 Seconds

Reference Table		
Memory (MB)	Still Pictures (1280 x 1024)	AVI Movies (min)
Built-in SDRAM	12	1.5
32 MB	80	6 to 9
64 MB	160	12 to 18
128 MB	320	24 to 36



OS534E-DM, £486, sold separately. See page 235.

DV-CAM, £50, sold separately, shown smaller than actual size.

Device Can Be Removed and Used Independently!

DV-CAM Accessory Works With All OMEGA OS Series IR Thermometers!



Laptop computer not included.

## Specifications

**Digital Video Camcorder:**  
QVGA (320 x 240 pixels)/10 fps

**Digital Still Camera:**  
2M (1600 x 1200 pixels)  
SXGA (1280 x 1024 pixels)  
VGA (640 x 480 pixels)

**PC Camera:**  
VGA (640 x 480 pixels)/10 fps  
QVGA (320 x 240 pixels)/24 fps

**Digital Voice Recorder:**  
About 4 min/1 MB memory  
**A/V out:** Supports NTSC/PAL colour TV system

**Battery:** Two "AA" (included)

## Dimensions:

84 H x 41 W x 68 mm L

## System Requirements:

Windows 98SE/ME/2000/XP;  
Pentium II, 266 MHz (or equivalent) processor or higher (Pentium III recommended); Direct x 8.0 or above  
32 MB of RAM (64 MB recommended);  
video card with 4 MB of RAM for minimum 16-bit (high colour) display

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
DV-CAM	£50.00	Digital/video camera with mounting hardware
32MB-FC	16.75	Replacement 32 MB compact flash memory card

Comes with operator's manual 32 MB flash memory card, software bundle, USB cable, 1/4" mini-stereo jack to RCA audio/video cable adaptor, mini-tripod, and detachable strap.

**Note:** Mini-tripod to be used only with video camera, not with infrared thermometer.

**Ordering Example:** DV-CAM, digital/video camera, plus OS534E-DM, handheld infrared thermometer with built-in Laser Circle to Dot Switchable™ feature, thermocouple input and distance measuring feature, plus 32MB-FC, replacement 32 MB compact flash memory card, £50 + £486 + £16.75 = **£552.75**

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

**www.omega.co.uk**



## UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters