



Rugged, Weatherproof, Wall Mounted Temperature Sensor

Pt100 Class A Sensor in NEMA 4X (IP65) Enclosure

EWSE Series




- ✓ Designed for Indoor and Outdoor Use
- ✓ Screw Terminal Block for 4-Wire Pt100 Connection
- ✓ Optional Built in 4 to 20 mA Transmitter
- ✓ Rugged Sensor and Protection Tube Design
- ✓ Supplied with NEMA 4X (IP68) Cable Gland or Electrical Connection

OMEGA's new air temperature sensors offer the perfect solution for temperature monitoring outdoors or in demanding environments.

A rugged 6 mm-diameter sheathed RTD probe is housed in the center of a 14 mm (0.551") outer protection tube which is drilled to improve airflow around the sensor. A 4-terminal connector block or 4 to 20 mA transmitter are housed in a tough aluminum alloy enclosure rated to NEMA 4X (IP65).

A cable gland is fitted on the left hand side of the enclosure, suitable for cables from 2.5 to 6.5 mm (0.098 to 0.25") diameter.



EWSE-PT100 with customer supplied connection installed shown actual size.

Specifications

Dimensions:

Box: 80 W x 75 H x 58 mm D (3 x 2.9 x 2.3")

Sensor: 75 mm long x 14 mm OD (2.9 x 0.55")

Cable Entry: NEMA 4X (IP68) gland for 2.5 to 6.5 mm (0.098 x 0.25") OD cable

EWSE-PT100:

Sensor Type: Thin film Pt100 class A 4 wire

Ambient Temperature Range:

-50 to 100°C (-58 to 212°F)

Electrical Connection:

Screw terminal block

EWSE-PT100-TX:

Ambient Temperature Range: -40 to 85°C (-40 to 185°F) at 10 to 90% RH non condensing

Standard Transmitter Scaling:

4 mA -25°C (-13°F), 20 mA at 75°C

Electrical Connection: Screw terminals, 2-wire

Power Supply: 10 to 30 Vdc, loop powered

Maximum Output Load: [(V supply-10)/20] kΩ eg 700Ω @ 24V



To Order Visit omega.com/ewse for Pricing and Details	
Model No.	Description
EWSE-PT100	External air temperature assembly, 4-wire RTD
EWSE-PT100-TX	External air temperature assembly with 2-wire 4 to 20 mA transmitter
TX-SCALED	Factory scaling charge for non-standard temperature range on 4 to 20mA output models
TX4-100	Multi-conductor hook-up wire, 30.5 m (100') spool

Other probe lengths available on request. Contact sales to discuss your specific requirements.

Ordering Example: EWSE-PT100, air temperature sensor.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters