

# 2-WAY STEAM SOLENOID VALVES

**DIRECT LIFT, NORMALLY CLOSED,  
BRASS VALVE BODY, EPDM SEALS**

## SV230 Series

Starts at  
**\$97**




- ✓ Rated Up to 145°C (293°F) Steam
- ✓ Rugged NEMA 4 (IP65) Housing
- ✓ Mounts in Any Position
- ✓ Rated for Continuous Duty

### TYPICAL APPLICATIONS


- ✓ Heating and Cooling
- ✓ Commercial Dish Washing Equipment
- ✓ Car Washing Equipment
- ✓ Food Processing
- ✓ Commercial Laundry Equipment
- ✓ Bottle Washing
- ✓ Sterilizing Equipment

The SV230 Series valves are designed for low-pressure steam applications in which the valve must operate when the pressure drop across the valve falls into the 0 to 5 psi range. These valves are able to control steam up to 45 psi at 145°C (293°F). All seals are made of ethylene propylene for compatibility with steam over a wide temperature range and for trouble-free, bubble-tight service.

The SV231 through SV235 are direct-lift valves, which combine the features of a direct-acting valve with those of a pilot-operated valve. Because of a flexible link between the solenoid plunger and the diaphragm, the direct-lift valve functions as a direct-acting valve at low pressures and as a pilot-operated valve at high pressures. It is sometimes referred to as a zero delta pressure valve or a hung diaphragm valve.



SV231, \$97, shown actual size.





SV234, \$180, shown actual size.

# DIRECT LIFT, NORMALLY CLOSED, BRASS VALVE BODY, STEAM SOLENOID VALVES, EPDM SEALS

## SPECIFICATIONS

**Operation:** Direct lift  
**Wetted Parts:** Brass, stainless steel, copper and seal  
**Medium:** Liquid or gases  
**Max Static Pressure:** 5 times max psid  
**Ambient Temp:** -9 to 50°C (15 to 122°F)  
**Mounting:** Pipe mounting, any direction  
**Power:** 22 W, 120 Vac, 50 to 60 Hz, Class H



**MOST POPULAR MODEL HIGHLIGHTED!**

## To Order (Specify Model Number)

MODEL NO.	PRICE	NPT FITTING	ORIFICE	C <sub>v</sub>	SEAL	DIFF PRES (psid)		TEMP		RESPONSE TIME	
						MIN	MAX	°C	(°F)	OPEN	CLOSE
SV231	\$97	1/4	13/64"	0.76	EPDM	0	40	141	285	4 to 8 ms	4 to 8 ms
SV232	160	3/8	5/8"	4.4	EPDM	0	45	145	293	30 to 100 ms	350 to 900 ms
SV233	170	1/2	5/8"	4.4	EPDM	0	45	145	293	30 to 100 ms	350 to 900 ms
SV234	180	3/4	5/8"	5.5	EPDM	0	45	145	293	30 to 100 ms	350 to 900 ms
SV235	325	1	1"	11.7	EPDM	0	45	145	293	30 to 100 ms	350 to 900 ms

Comes complete with operator's manual.

**Note:** Some solenoid valves are available with 24 Vdc coils. Five piece minimum order. UL approval is not available with 24 Vdc coils. Specifications effected; pressure ratings may decrease; coil wattage ratings may increase. Consult Engineering.

**Ordering Examples:** SV232, 2-way direct-lift steam valve, NC with a brass body and 3/8 NPT fitting with EPDM seal, \$160.

SV235, 2-way direct-lift steam valve, NC with a brass body and a 1 NPT fitting and EPDM seals, \$325.

Recommended Reference Book: Plantwide Process Control, CM-4333, \$155.  
See Section Y For Additional Books.



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters