


Heavy Duty Industrial Grade Thermocouple Wire Shielded Extension Cables



For Your Most Demanding Applications!



OMEGA® extension cables are designed for use in connecting a thermocouple probe to a readout or indicator. Made from extension grade thermocouple wire, J, K and E wire types are rated from 0 to 105°C (32 to 221°F) for the insulation. The range type T extension wire is rated from -60° to 100°C (-76 to 212°F). Used for a wide variety of applications, these cables are our standard construction PVC or PFA wire with a metal overbraid of tinned copper or stainless steel, and an overall outer jacket of PVC or PFA.

This construction add durability and assures long term abrasion resistance.

Use with OMEGA's Patented Low Noise Connectors

The thermocouple connector with a ground strap to work with shielded wire.

Shown smaller than actual size.



See pages G-5 to G-11

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Polyvinyl Coated Wire with Tinned Copper Overbraid

Model Number	Price/1000'	Calibration	Nominal Size mm (inches)	AWG No.*
EXPP-J-14-TCB-P	\$970	J Iron-Constantan	5.1 x 7.4 (0.20 x 0.29)	14 Solid
EXPP-J-16-TCB-P	720		4.8 x 6.7 (0.19 x 0.26)	16 Solid
EXPP-J-16S-TCB-P	880		4.8 x 6.9 (0.19 x 0.27)	16 Stranded
EXPP-J-20-TCB-P	500		4.1 x 5.5 (0.16 x 0.22)	20 Solid
EXPP-J-20S-TCB-P	640		4.1 x 5.6 (0.16 x 0.22)	20 Stranded
EXPP-J-24S-TCB-P	560		4.0 x 5.1 (0.16 x 0.20)	24 Stranded
EXPP-T-14-TCB-P	995	T Copper Constantan	5.1 x 7.4 (0.20 x 0.29)	14 Solid
EXPP-T-16-TCB-P	740		4.8 x 6.7 (0.19 x 0.26)	16 Solid
EXPP-T-20-TCB-P	510		4.1 x 5.5 (0.16 x 0.22)	20 Solid
EXPP-T-20S-TCB-P	660		4.1 x 5.6 (0.16 x 0.22)	20 Stranded
EXPP-K-14-TCB-P	1270	K CHROMEQA®-ALOMEGA®	5.1 x 7.4 (0.20 x 0.29)	14 Solid
EXPP-K-16-TCB-P	900		4.8 x 6.7 (0.19 x 0.26)	16 Solid
EXPP-K-16S-TCB-P	1145		4.8 x 6.9 (0.19 x 0.27)	16 Stranded
EXPP-K-20-TCB-P	550		4.1 x 5.5 (0.16 x 0.22)	20 Solid
EXPP-K-20S-TCB-P	740		4.1 x 5.6 (0.16 x 0.22)	20 Stranded
EXPP-K-24S-TCB-P	640		4.0 x 5.1 (0.16 x 0.20)	24 Stranded
EXPP-E-16-TCB-P	1095	E CHROMEQA®-Constantan	4.8 x 6.7 (0.19 x 0.26)	16 Solid
EXPP-E-20-TCB-P	580		4.1 x 5.5 (0.16 x 0.22)	20 Solid
EXPP-E-24S-TCB-P	620		4.0 x 5.1 (0.16 x 0.20)	24 Stranded

* See page H-8 for complete AWG dimensions

Ordering Example: EXPP-J-20S-TCB-P-1000, 1000' (300 m) of type J (Iron-Constantan), polyvinyl coated extension grade wire, 20 gage, \$640.

PFA Coated Wire with 304SS Overbraid

Model Number	Price/1000'	Calibration	Nominal Size mm (Inches)	AWG No.*
EXTT-J-16-SB-T	\$1385	J Iron-Constantan	3.3 x 5.1 (0.13 x 0.20)	16 Solid
EXTT-J-20-SB-T	935		2.9 x 4.3 (0.12 x 0.17)	20 Solid
EXTT-J-24-SB-T	750		2.5 x 3.3 (0.10 x 0.13)	24 Solid
EXTT-T-16-SB-T	1370	T Copper Constantan	3.3 x 5.1 (0.13 x 0.20)	16 Solid
EXTT-T-20-SB-T	925		2.9 x 4.3 (0.12 x 0.17)	20 Solid
EXTT-T-24-SB-T	750		2.5 x 3.3 (0.10 x 0.13)	24 Solid
EXTT-K-16-SB-T	1620	K CHROMEQA®-ALOMEGA®	3.3 x 5.1 (0.13 x 0.20)	16 Solid
EXTT-K-20-SB-T	1045		2.9 x 4.3 (0.12 x 0.17)	20 Solid
EXTT-K-24-SB-T	800		2.5 x 3.3 (0.10 x 0.13)	24 Solid
EXTT-E-16-SB-T	1620	E CHROMEQA®-Constantan	3.3 x 5.1 (0.13 x 0.20)	26 Solid
EXTT-E-20-SB-T	1045		2.9 x 4.3 (0.12 x 0.17)	20 Solid
EXTT-E-24-SB-T	905		2.5 x 3.3 (0.10 x 0.13)	24 Solid

* See page H-8 for complete AWG dimensions Ordering Example: EXTT-K-20-SB-T-1000, 1000' (300 m) of type K (CHROMEQA®-ALOMEGA®), PFA coated extension grade wire, 20 gage, with stainless steel overbraid, \$1045 To order quantities other than 1000', consult Sales.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters