

# Economical Handheld Digital Tachometer with RS232C Software\*

- ✓ 5 Digits LCD Display
- ✓ Light Reflex Measurement Technology
- ✓ Range 10.00 to 99,999 RPM
- ✓ Measuring Distance 50 to 300 mm
- ✓ Event Counter with Elapsed Time (HH:MM)
- ✓ HHT-1502 Optional Contact Adaptor
- ✓ Max/Min/Hold: True Average
- ✓ Auto Range RPM
- ✓ RS232 Interface for Model HHT-1501
- ✓ Contact RPM and Circumferential Velocity (HHT-1502CA)

HHT-1500 Series Starts at

£131



The HHT-1500 Series is an accurate economical, non-contact optical digital tachometer. All units come complete with reflective tape and carrying case. An optional contact adaptor, HHT-1502CA is easy to attach and converts the unit to mechanical measurement. Users affix a tape on the shaft to be measured. The tachometer measures the time between reflected pulses of light and calculates the RPM.

## Specifications

### Speed (Optical)

|         | Range          | Resolution     | Accuracy       |
|---------|----------------|----------------|----------------|
| RPM     | 10.00 ~ 99999  | 0.01/0.1/1     | 0.04% ± 2 dgts |
| rps(Hz) | 0.200 ~ 2000.0 | 0.001/0.01/0.1 | 0.04% ± 2 dgts |

### Speed (Contact)

|                                  | Range           | Resolution       | Accuracy       |
|----------------------------------|-----------------|------------------|----------------|
| RPM / ("/" symbolizes "Contact") | 10.00 to 29999  | 0.001/0.01/0.1/1 | 0.04% ± 2 dgts |
| m/min                            | 1.000 to 2999.9 | 0.001/0.01/0.1   | 0.04% ± 2 dgts |
| ft/min                           | 3.00 to 10000   | 0.001/0.01/0.1   | 0.04% ± 2 dgts |
| yard/min                         | 1.00 to 3000    | 0.001/0.01/0.1   | 0.04% ± 2 dgts |

### General Specifications

|                    |  |
|--------------------|--|
| External TTL Input | High > 4.5V (HHT-1501)                             |
| Display            | 5 digits 99999 counts                              |
| Sampling Rate      | 0.7 second (> 60 rpm)<br>> 1 second (10 to 60 rpm) |
| Measuring Distance | 50 to 300 mm (2 to 12")                            |
| Time Base          | 4.0 MHz Quartz Crystal                             |
| Range Selection    | Automatic  |
| Battery            | Four 1.5 V "AA" (included)                         |
| Auto Power-Off     | 30 minutes   |
| Operating Temp     | 0 to 50°C (32 to 122°F)                            |
| Size               | 72 mm x 63 mm x 36 mm (6.8 x 2.5 x 1.5")           |
| Weight             | 190 g (6.7 oz.) (including battery)                |

HHT-1500, £131, shown larger than actual size.

### Event Counter

| Range      | Max Input Frequency       |
|------------|---------------------------|
| 0 to 99999 | 10 KHz with 5% duty cycle |

**AVAILABLE FOR FAST DELIVERY!**

\* HHT1501 only. Comes with carrying case, reflective tape, 4 "AA" alkaline batteries and operator's manual.  
**Ordering Example:** HHT-1501, digital tachometer with RS232C cable and software and HHT-1502CA, contact adaptor, £151 + 30 = £181.

| To Order (Specify Model Number) |       |   |
|---------------------------------|-------|---|
| Model No.                       | Price | Description                                       |
| HHT-1500                        | £131  | Digital tachometer                                |
| HHT-1501                        | 131   | Digital tachometer with RS232C cable and software |
| HHT-1502CA                      | 30    | Optional contact adaptor                          |

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters