

PFA Coated Thermocouple Probes

With Standard Size Connectors

We Can PFA Coat Most Thermocouple Probes. Contact Our Sales Department for Availability and Price.



- ✓ Chemically Inert
- ✓ Electrically Insulated
- ✓ Abrasion Resistant
- ✓ Rated to 205°C (400°F)
- ✓ Quick-Disconnect Style
- ✓ 1.5 mm (1/16") or 3.0 mm (1/8") Diameter
- ✓ Grounded Junction
- ✓ 300 mm (12") Probe Standard†
- ✓ 0.010 PFA Coating (Typical)

PFA coated probes are the perfect solution when there is a need to measure the temperature of caustic or corrosive chemical solutions in industrial and laboratory environments. The superior corrosion resistance of PFA allows you to measure the temperature of sulfuric, hydrochloric, nitric, and chromic acids, as well as caustic compounds.


Applications

- ✓ Battery Electrolyte
- ✓ Plating Baths
- ✓ Anodizing Baths
- ✓ Severe Environments

All products shown smaller than actual size.


HDX probe handle not included. Please see omega.com/sdx_hdx_probes of probe handles.

Note: OMEGA can pre-bend PFA coated probes prior to shipping. Consult Sales for this option. Probes ordered from this page are shipped straight.




To Order		
Calibration	Probe Dia.* mm (inch)	Model Number
Iron-Constantan J	1.5 (1/16)	ICSS-116G-12-PFA
	1.5 (1/16)	ICSS-116G-18-PFA
	1.5 (1/16)	ICSS-116G-24-PFA
	6.0 (1/4)	ICSS-14G-12-PFA
	6.0 (1/4)	ICSS-14G-18-PFA
	6.0 (1/4)	ICSS-14G-24-PFA
	3.0 (1/8)	ICSS-18G-12-PFA
	3.0 (1/8)	ICSS-18G-18-PFA
	3.0 (1/8)	ICSS-18G-24-PFA
CHROMEALOMEGA® K	1.5 (1/16)	CASS-116G-12-PFA
	1.5 (1/16)	CASS-116G-18-PFA
	1.5 (1/16)	CASS-116G-24-PFA
	3.0 (1/8)	CASS-18G-12-PFA
	3.0 (1/8)	CASS-18G-18-PFA
	3.0 (1/8)	CASS-18G-24-PFA
Copper-Constantan T	1.5 (1/16)	CPSS-116G-12-PFA
	1.5 (1/16)	CPSS-116G-18-PFA
	1.5 (1/16)	CPSS-116G-24-PFA
	3.0 (1/8)	CPSS-18G-12-PFA
	3.0 (1/8)	CPSS-18G-18-PFA
	3.0 (1/8)	CPSS-18G-24-PFA
CHROMEALOMEGA®-Constantan E	1.5 (1/16)	CXSS-116G-12-PFA
	1.5 (1/16)	CXSS-116G-18-PFA
	1.5 (1/16)	CXSS-116G-24-PFA
	3.0 (1/8)	CXSS-18G-12-PFA
	3.0 (1/8)	CXSS-18G-18-PFA
	3.0 (1/8)	CXSS-18G-24-PFA

Standard size connectors, shown smaller than actual size.



Available in lengths up to 1.2 m (4').

Mating connector, cable clamp and locking clip included.



* Before PFA coating. † Other lengths available, consult Sales department.
Ordering Example: CASS-18G-12-PFA, coated thermocouple probe, Type K, stainless steel sheath, 3 mm (1/8") Dia., grounded, 300 mm (12") long.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters