

1/32 DIN Ramp/Soak Controllers

CN7500 Series



- ✓ Dual 4-Digit LED Display
- ✓ 8 Ramp/Soak Programs, 8 Segments Each
- ✓ Universal Inputs
- ✓ Autotune
- ✓ Dual Control Outputs
- ✓ RS485 Communications Standard
- ✓ Alarm Functions
- ✓ Free Software

The CN7500 Series temperature/process controller's advanced control features can handle the most demanding temperature or process applications. Enclosed in a compact 1/32 DIN housing, the CN7500 has dual, 4-digit LED displays for local indication of process value and setpoint. Control methods include on/off, PID, autotune, and manual tune. PID control is supported with 64 temperature and time (ramp/soak) control actions. The dual-loop output control allows simultaneous heating and cooling. The second output can be configured as an alarm mode using one of the 13 built-in alarm functions.

RS485 communications is standard. Up to 247 communication addresses are available, with transmission speeds of 2400 to 38,400 bps. Other features include universal inputs, selectable temperature units (°C/°F), selectable resolution, quick sampling rate, and security protection.

Specifications

Inputs: Thermocouple, RTD, DC voltage or DC current

Display: Two 4-digit, 7 segment 6.35 mm H (25") LEDs;

PV: red

SV: green

Accuracy: ±0.25% span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, 50/60 Hz

Power Consumption: 5 VA max

Operating Temperature: 0 to 50°C (32 to 122°F)

Memory Backup: Non-volatile memory

Control Output Ratings:

Relay: SPST, 5A @ 250 Vac resistive

Voltage Pulse: 14 V, 10 to -20% (max 40 mA)

Current: 4 to 20 mA

Communication: RS485 MODBUS® A-5-11/RTU communication protocol

Weight: 114 g (4 oz)

Panel Cut-Out: 45 x 22.5 mm (1.772 x 0.886")

Maximum Panel Thickness: 3.40 mm (0.14")

Panel Depth: 99.80 mm (3.86")



Panel punches available, visit omega.com/panelpunches

Inputs

Input Types	Range
K	-200 to 1300°C (-328 to 2372°F)
J	-100 to 1200°C (-148 to 2192°F)
T	-200 to 400°C (-328 to 752°F)
E	0 to 600°C (32 to 1112°F)
N	-200 to 1300°C (-328 to 2372°F)
R	0 to 1700°C (32 to 3092°F)
S	0 to 1700°C (32 to 3092°F)
B	100 to 1800°C (212 to 3272°F)
L	-200 to 850°C (-328 to 1562°F)
U	-200 to 500°C (-328 to 932°F)
Pt100 RTD	-200 to 600°C (-328 to 1112°F)
0 to 50 mV	-999 to 9999
0 to 5 V	-999 to 9999
0 to 10 V	-999 to 9999
0 to 20 mA*	-999 to 9999
4 to 20 mA*	-999 to 9999

* Requires external 250 Ω precision shunt resistor, **OMX-R250** (sold separately).

To Order Visit omega.com/cn7500 for Pricing and Details

Model No.	Description
CN7523	Dual output, DC pulse/relay, RS485*
CN7533	Dual output, relay/relay, RS485*
CN7553	Dual output, 4 to 20 mA/relay, RS485*

Accessories (Field Installable)

Model No.	Description
CNQUENCHARC	Noise suppression RC snubber (2 leads), 110 to 230 Vac
OMX-R250	250 Ω precision resistor
CN7-485-USB-1	RS485 to USB mini-node converter

Comes complete with operator's manual.

* Free CN7-A software download available at omega.com/cn7500

Ordering Example: **CN7523**, dual-output controller, DC pulse and a mechanical relay output, RS485 communications.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters