

# Portable Relative Humidity/Temperature Calibrator



RHCL-2  
£8040



- ✓ RHCL-2 field proven Optical Chilled Mirror (OCM) Technology
- ✓ Completely Self-Sufficient and Portable Humidity Calibration System
- ✓ Highest Accuracy Available for Both RH and Temperature (AT):  
RH Range: 5% to 95%
- ✓ Air Temperature Range: 10°C to 50°C
- ✓ Temperature and RH Controlled Independently
- ✓ Automatic Correction for Mirror Contaminants
- ✓ Certified Measurements Against NIST Traceable Standards

The Omega RHCL-2 is a microprocessor based, programmable humidity calibration system that is at home in the metrology lab or out in the field performing on site NIST traceable humidity calibrations. The RHCL-2 is entirely self-sufficient and does not need compressed air or a water connection to operate, which allows this system to be truly portable. The system offers the highest accuracy available for both relative humidity and ambient temperature. Temperature and relative humidity are controlled independently; therefore, you are not limited to performing calibrations at the surrounding ambient temperature. The RHCL-2 uses an Optical Chilled Mirror (OCM) primary measurement technique for traceability and feedback control. Contributing to ease of use are features such as



RHCL-2, £8040, shown smaller than actual size.

maintenance reducing Automatic Balance Cycle (ABC), an integral ambient temperature probe, and D2 chilled mirror sensor which are located in the sample chamber providing not only superior accuracy but the fastest response.

The RHCL-2 employs a unique control scheme for maintaining precise RH control. The system incorporates volumetric proportional control valves. By independently modulating the "Dry" and "Wet" valves from full-open to full-close, and all points between, any desired humidity can be quickly generated. Additionally, because the RHCL-2 is continuously monitoring the sample chamber conditions via its integral chilled mirror, it is able to instantaneously react to changes in humidity and maintain control stability.

## Specifications

- Range:**  
RH: 5 to 95% RH @ 10 to 50°C  
**Dew/Frost Point:** -40 to 60°C (-40 to 140°F)
- Accuracy:**  
RH: ±0.5% RH @ ±0.2°C  
**Dew/Frost Point:** ±0.2°C nominal
- Slew Rate:** 1.0°C (1.8°F)/sec max, above 0°C
- Repeatability:** ±0.5%
- Outputs:** Analog (0 to 5 Vdc or 4 to 20 mA) and RS232C
- Power Requirements:** 100 to 240 Vac, 50 to 60 Hz, 150 W maximum
- Sample Flow Rate:** 1 liter/min (2.0 SCFH)
- Operating Temperature (Control Unit):** 0 to 50°C (32 to 122°F)
- Weight:** 15.4 kg (34 lb)
- Dimensions:** 52 W x 43.7 D x 21.7 cm H (20% W x 17% D x 8% H)
- Enclosure:** Ultra high-impact copolymer carrying case

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Model No.	Price	Description
RHCL-2	£8040	Portable Rh/Temp calibrator
RHCL-2-SR	37	Seals for sample chamber, qty 20
RHCL-2-CCB	33	Chamber covers without holes, qty 3
RHCL-2-DR5	58	Dessicant 5 lb jar

Comes with complete operator's manual, power cord, cleaning kit and NIST certificate.  
**Ordering Example:** RHCL-2, portable calibrator, RHCL-2-SR, seals, and RHCL-2-DR5, 5 lb jar of dessicant, £8040 + 37 + 58 = £8,135

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



## UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)  
088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters