



Dual Element RTD Pipe Plug Sensors

RTD-NPT Series

- Ideal for Use in Pressure Vessel Applications, 172 bar (2500 psi) Max
- PFA Insulated Lead Wires
- High-Accuracy, 100 Ω, Thin-Film Class "A" DIN Platinum Elements
- 3-Wire Construction for Connecting to Most Handheld Instruments



To Order Visit omega.com/rtd-npt for Pricing and Details

Model Number	Sensing Element	Cable	Thread Size	Max Temp
RTD-NPT-72-E-DUAL-1/4-MTP	100 Ω Class "A" DIN	72" L PFA insulated with MTP connectors	1/4 NPT	230°C (450°F)
RTD-NPT-72-E-DUAL-1/8-MTP	100 Ω Class "A" DIN	72" L PFA insulated with MTP connectors	1/8 NPT	230°C (450°F)
RTD-NPT-72-E-DUAL-1/8-MTP-HT	100 Ω Class "A" DIN	72" L fiberglass insulated with MTP connectors	1/8 NPT	480°C (896°F)
RTD-NPT-72-E-DUAL-1/4-MTP-HT-S	100 Ω Class "A" DIN	72" L SST braided fiberglass insulated with MTP connectors	1/4 NPT	480°C (896°F)

Ordering Examples: *RTD-NPT-72-E-DUAL-1/8-MTP*, dual 100 Ω Class "A" DIN Platinum thin-film elements, 3-wire connections, 1/8 NPT mounting thread, 72" long PFA insulated cables with MTP connectors. *RTD-NPT-72-E-DUAL-1/8-MTP-HT*, dual 100 Ω Class "A" DIN Platinum thin-film elements, 3-wire connections, 1/8 NPT mounting thread, 72" long fiberglass insulated cables with MTP connectors.

Options: Sensors supplied with MTP connectors standard. For OTP connectors add "-OTP" to model number for an additional cost. For NO connectors remove "-MTP" from model number for a subtraction in cost (leads will be stripped). For a 3-pin audio connector, add "-TA3F" to the model number for an additional cost.

Popular Options Include:



CN1A visit omega.com/cn1a



DP461-RTD meter visit omega.com/dp460-t


IDRX/IDRN signal conditioner, visit omega.com/idrn-idrx



DRF-RTD signal conditioner visit omega.com/drft-rtd



How are OMEGA's Model Numbers Constructed?





Ordering Example: *RTD-NPT-72-E-DUAL-OTP-HT-S*, two 100 Ω class "A" DIN, 72" fiberglass insulated, 1/4 NPT, 480°C (896°F), and OTP connector.

Pipe Plug RTD Sensor

RTD-NPT Series

- ✓ Ideal for Use in Pressure Vessel Applications, 172 bar (2500 psi) Max
- ✓ 6 mm (0.24") Diameter, SST Probe
- ✓ Steel Braided, PFA Insulated Lead Wires
- ✓ High-Accuracy, 100 Ω, Class "A" DIN Thin-Film Platinum Element (European Curve)
- ✓ 3-Wire Construction for Connecting to Most Handheld Instruments with Red/Red/White Per ASTM-E-1137



To Order Visit omega.com/rtd-npt for Pricing and Details

Model Number	Sensing Element	Cable	Thread Size	Max Temp
RTD-NPT-72-E-1/4	100 Ω Class "A" DIN	72" L PFA insulated (stripped leads)	1/4 NPT	230°C (450°F)
RTD-NPT-72-E-1/4-MTP	100 Ω Class "A" DIN	72" L PFA insulated	1/4 NPT	230°C (450°F)
RTD-NPT-72-E-1/8-MTP	100 Ω Class "A" DIN	72" L PFA insulated	1/8 NPT	230°C (450°F)
RTD-NPT-72-E-1/4-MTP-HT	100 Ω Class "A" DIN	72" L fiberglass insulated	1/4 NPT	480°C (896°F)
RTD-NPT-72-E-1/8-MTP-HT	100 Ω Class "A" DIN	72" L fiberglass insulated	1/8 NPT	480°C (896°F)

Ordering Examples: RTD-NPT-72-E-1/4-TA3F, 100 Ω Class "A" European curve, single element, with 1/4 NPT mounting thread, 72" long PFA insulated cable with audio connector. RTD-NPT-72-E-1/4-MTP-HT, 100 Ω Class "A" European curve, single element, with 1/4 NPT mounting thread, 72" long fiberglass insulated cable with steel overbraid. RTD-NPT-72-E-1/8-MTP-HT, Class "A" element, European curve, with 1/8 NPT mounting thread, 72" long fiberglass insulated cable with SST braid.

Options Available: Sensors supplied with MTP connectors, add "-OTP" to model number for an additional cost for each heavy-duty connector, add "-TA3F" to model number for an additional cost for each audio connector. For stripped leads (no connector) remove "-MTP" from model number, and subtract from cost.

Popular Options Include:



CN3271-R1 high/low limit controller visit omega.com



DP25B-RTD 1/2 DIN panel meter visit omega.com




SPRTX, 4 to 20 mA transmitter visit omega.com



TX92 transmitter visit omega.com

How are OMEGA's Model Numbers Constructed?



Ordering Example: RTD-NPT-72-E-OTP-HT, 100 Ω Class "A" European curve, with 1/4 NPT, 72" L fiberglass insulated cable, heavy-duty connector.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters