

Economical, High Performance Handheld Thermometers

°C/°F and 0.1°/1° Resolution Models

All Models
\$125



HH-25TC, \$125,
shown smaller
than actual size.

- ✓ Certificate Included Stating NIST-Traceability (No Points)
- ✓ Up to 0.4% of Reading Accuracy
- ✓ HH-25 Models for 0.1° and 1° Display with Type K or T Thermocouples
- ✓ HH-26 Models for °C/°F Display, 1° Resolution with Type J or K Thermocouples
- ✓ Rugged, High-Impact ABS Plastic Case
- ✓ Large 3½ Digit LCD Display

FREE Thermocouple Included!

These models include a free 1 m (40") insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel). **Order a Spare! Model No. SC-GG-(*)-30-36, \$15.**

* Insert thermocouple Type, J,K,T,E.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Specifications

Input Current: 120 nA typical

Repeatability: 0.2°C (0.3°F) typical for 1 week at constant ambient temperature

Temperature Coefficient:

-10 to 18°C and 28 to 50°C; less than ±(0.025% of rdg + 0.1°C)/°C

Operating Temperature: -10 to 50°C and less than 80% RH up to 35°C

Display: 3½ digit LCD, 13 mm H (0.5"), polarity, overrange, oversensor and decimal indication

Conversion Rate: 1.5 readings per second

Maximum Common Mode Voltage: 42V peak to earth

Thermocouple Input:

Miniature T/C connector

Power: 9V alkaline battery (included)

Battery Life, Continuous: 300-hr, alkaline

Battery Indicator: Display indicates "LO BAT" when less than 10% of the life remains

Dimensions: 69 W x 31 D x 160 mm L (2.7 x 1.2 x 6.3")

Weight: 210 g (7.5 oz)



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Resolution	Range	Accuracy
HH-25KF	\$125	0.1°F 1°F	-40 to 199.9°F -120 to 1999°F	±(0.5% rdg + 1.0°F) ±(1.0% rdg + 2.0°F)
HH-25KC	125	0.1°C 1°C	-40 to 199.9°C -120 to 1999°C	±(0.5% rdg + 0.5°C) ±(1.0% rdg + 1.0°C)
HH-26K	125	1°F 1°C	-120 to 1999°F -85 to 1100°C	±(1.0% rdg + 2.0°F) ±(1.0% rdg + 1.0°C)
HH-25TF	125	0.1°F 1°F	-112 to 199.9°F 200 to 752°F	±(0.4% rdg + 1.1°F) ±(1.0% rdg + 2.0°F)
HH-25TC	125	0.1°C 1°C	-80 to 199.9°C 200 to 400°C	±(0.4% rdg + 0.6°C) ±(1.0% rdg + 1.0°C)
HH-26J	125	1°F 1°C	-112 to 1400°F -80 to 760°C	±(1.0% rdg + 2.0°F) ±(1.0% rdg + 1.0°C)

Comes complete with 9V battery, operator's manual, beaded wire thermocouple, and NIST certificate (no data points).

Ordering Example: HH-25KF, handheld thermometer, Type K, resolution 0.1°F/1°F, and KTSS-HH, Type K general purpose meter probe (shown below), \$125 + 29 = **\$154.**

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$31), \$125 + 31 = **\$156.**

Model No.	Price	Description
SC-800	\$10	Carrying case
CAL-3-HH	75	NIST-traceable calibration with points

General purpose meter probes start at \$29. See page L-48.



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters