

# DialTemp™ Surface Thermometers Dual Fahrenheit and Celsius Dials




All Models  
**\$36**

**Operating Instructions**  
This unique, handy little gage is great for use in sensing the temperature of almost any surface. The bimetal sensing element is exposed to allow quick accurate response to surface

temperature, but adequately shielded from damage by a protective cover and heat collector. For the most accurate reading this surface thermometer should be used in still air. Place the gage on the surface where you wish to know the temperature – dial face up with bimetal sensing element against the surface. The magnets will allow placement in any position on a ferrous surface. It can also be used on any other material with a horizontal surface. Allow about a minute for the sensing element to stabilize and then read the temperature. Higher or lower air temperatures surrounding the thermometer or a draft over the surface may slightly affect the temperature indicated.

### Some Typical Applications

Air ducts, boilers, cabinets, drums, engines, enclosures, fire boxes, manifolds, platens, plumbing, piping, refrigerators and many others.



### Specifications

- Head Size:** 5.08 cm (2")
- Height:** 1.27 cm (1/2")
- Weight:** 56.7 g (2 oz) approximately
- Dial:** White background, blue marks and numbers
- Case:** Aluminum with optically clear crystal
- Sensing Element:** Precision calibrated bimetal coil
- Accuracy:** ±2% of full scale
- Response Time:** Approximately 1 minute
- Mounting:** 2 magnets on back

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Model No.	Price	Range
<b>SUR-15</b>	<b>\$36</b>	-20 to 65°C (0 to 150°F)
<b>SUR-25</b>	<b>36</b>	-20 to 120°C (0 to 250°F)
<b>SUR-50</b>	<b>36</b>	-20 to 260°C (0 to 500°F)
<b>SUR-75</b>	<b>36</b>	10 to 400°C (50 to 750°F)

## Accessories and Options

### Mounting Threads and Bushings

- 1/8" NPT – Models Q, G, H
- 1/4" NPT – All models
- 1/2" NPT – All models
- 3/8" NPT – Models Q, G, H
- 3/4" NPT Adaptor Bushing – Models A, R, B, S, X, XR, V, VR, J

**Hex Bushing:** Models A, R, B, S

**Other Threads on Special Order**



**External Mounting Brackets for Models G and H**

External mounting brackets facilitate surface mounting on cabinets, ovens, coolers, flat surfaces.

To order, see page E-19.

### Clip Hanger and Spring Handle—All Models

The C-10 Clip Hanger and T-27 Spring Handles are used on the rims of tanks, kettles, urns, solder pots, beakers or other containers. The Spring Handle can be hand held allowing thermometer insertion in hot or corrosive materials without exposure of the hand. Very handy items. Available from stock.

**Model C-10  
Clip Hangers**

**\$5** Each

**Model T-27  
Spring Handles**

**\$5** Each



Other Options	Price
Pointed stems (for all models), add "-PS"	<b>\$4 each</b>
Pocket case/clip (for 5" or 6" stems only)	<b>5 each</b>
Unbreakable clear plastic crystals, add "-PC"	<b>7 each</b>
Pointer for min and max on 3" models, add "-NMP"	<b>46</b>
Pointer for min and max on 5" models, add "-NMPS"	<b>71</b>
Custom thermometers, dials, ranges, fixtures	<b>Consult Sales</b>
*Silicone filling—models A, R, add "-SF" up to 9"	<b>38</b>
*Silicone filling—models B, S, add "-SF" up to 9"	<b>41</b>
*Silicone filling—models X, XR, add "-SF" up to 9"	<b>50</b>
*Silicone filling—models V, VR, and J, add "-SF" up to 9"	<b>52</b>

\* Models A, R, B, S: over 9" add \$2/add'l inch. Models X, XR, V, VR, J: over 9" add \$3/add'l inch. PFA coating: add \$4/additional inch. **Ordering Example: SUR-75, 10 to 400°C range, \$36.**

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters