


Silicone Rubber Insulated High Temperature Heater Hook-Up Wire



HTRG Series

- ✓ 200°C (392°F) Temperature Rating
- ✓ UL & CSA Certified*
- ✓ Silicone Rubber Insulated with Treated Glass Overbraid
- ✓ Tinned Copper Conductor

Discount Schedule	
50 to 99ft	20%
100 to 199ft	30%
200 to 499ft	40%
500ft and up	60%



Braided silicone rubber insulated high-temperature lead wires are well suited for use as the exposed leads in appliances and lighting fixtures. HTRG Series wire is also used for range top burners and back panels, steam irons, toasters, broiler ovens, gas dryers, kilns, recessed lighting fixtures and similar applications up to 200°C (392°F).

CAUTION AND WARNING!
Fire and electrical shock may result if products are used improperly or installed or used by nonqualified personnel. See inside back cover for additional warnings.

Additional Heater Hook-up Wire is shown in the OMEGALUX Complete Electric Heaters Handbook & Encyclopedia™ and also online at: www.omega.com

MOST POPULAR MODELS HIGHLIGHTED!

ALL MODELS STOCKED FOR FAST DELIVERY!

To Order (Specify Model Number)							
Gauge	Model No.	Price/Foot	Type	Volts	NOM OD, mm ± 1.0 mm (in ± .004")	Approx. Wt. Kg/300m (lb/1000 ft)	Colour
18	HTRG-1CU-618SW	£0.30p	7 x 26	600	3.18 (.125)	5.7 (12.5)	White
18	HTRG-1CU-618SBK	0.30p	7 x 26	600	3.18 (.125)	5.7 (12.5)	Black
16	HTRG-1CU-616SW	0.34p	7 x 24	600	3.40 (.134)	7.5 (16.5)	White
16	HTRG-1CU-616SBK	0.34p	7 x 24	600	3.40 (.134)	7.5 (16.5)	Black
14	HTRG-1CU-614SW	0.44p	7 x 22	600	3.84 (.151)	10.0 (22.0)	White
14	HTRG-1CU-614SBK	0.44p	7 x 22	600	3.84 (.151)	10.0 (22.0)	Black
12	HTRG-1CU-612SW	0.60p	19 x 25	600	4.22 (.166)	14.3 (31.5)	White
12	HTRG-1CU-612SBK	0.60p	19 x 25	600	4.22 (.166)	14.3 (31.5)	Black
10	HTRG-1CU-610SW	0.91p	19 x 23	600	5.59 (.220)	23.1 (51.0)	White
10	HTRG-1CU-610SBK	0.91p	19 x 23	600	5.59 (.220)	23.1 (51.0)	Black

Ordering Example: HTRG-1CU-618SW, a 50ft spool of 18 gauge stranded wire with white jacketing, £0.30p x 50 - 20% = **£12.00**

Standard Conductors: AWG 22-20: Nickel Plated Copper

AWG 18-8: Tinned Copper

Standard Colour: White or Black. Other colours available; contact Sales.

*HTRG Series wire is both UL listed and CSA certified.

See Heater Hook-up Wire Introduction for current carrying capacity and derating.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters