

Non-Reversible Labels

Indicator dot turns black at rated temperature.

MOST POPULAR MODELS HIGHLIGHTED!

✓ **Accuracy ±2.0%**

Single Dot Round Labels (°C/°F)

TL-S labels are designed for low-cost, single-temperature operation. TL-S labels are compact round labels, only 9.5 mm in diameter. They are perfect for use in limited spaces. TL-S labels are supplied in packs of 30 or 50.

Model No. (pk. 30)	°C (°F) Range	Model No.	°C (°F) Range	Model No.	°C (°F) Range	Model No.	°C (°F) Range
TL-S-100	38 (100)	TL-S-190	88 (190)	TL-S-300	149 (300)	TL-S-410	210 (410)
TL-S-105	41 (105)	TL-S-200	93 (200)	TL-S-310	154 (310)	TL-S-420	216 (420)
TL-S-110	43 (110)	TL-S-210	99 (210)	TL-S-320	160 (320)	TL-S-435	224 (435)
TL-S-115	46 (115)	TL-S-220	104 (220)	TL-S-330	166 (330)	TL-S-450	232 (450)
TL-S-120	49 (120)	TL-S-230	110 (230)	TL-S-340	171 (340)	TL-S-465	241 (465)
TL-S-130	54 (130)	TL-S-240	116 (240)	TL-S-350	177 (350)	TL-S-480	249 (480)
TL-S-140	60 (140)	TL-S-250	121 (250)	TL-S-360	182 (360)	TL-S-490	254 (490)
TL-S-150	66 (150)	TL-S-260	127 (260)	TL-S-370	188 (370)	TL-S-500	260 (500)
TL-S-160	71 (160)	TL-S-270	132 (270)	TL-S-380	193 (380)		
TL-S-170	77 (170)	TL-S-280	138 (280)	TL-S-390	199 (390)		
TL-S-180	82 (180)	TL-S-290	143 (290)	TL-S-400	204 (400)		



10 mm

TL-S-100
Shown actual size

Price

pk. of 30 pk. of 50

£4 **£6**

To order pack of 50, add suffix "-50" to Model No.

Ordering Example: TL-S-100-50, Single Dot Round Label, 38°C (100°F), pack of 50, £6.

4 Dot Round Labels (°F only)

TL-C labels feature four temperature ratings in a single, compact, round design. These labels are especially suited for use in areas with limited space. TL-C indicators are supplied 10 or 30 to a pack.

Model No. (pk. 10)	Temperature Range °F	Model No.	Temperature Range °F
TL-C-105	105 110 115 120	TL-C-290	290 300 310 320
TL-C-130	130 140 150 160	TL-C-330	330 340 350 360
TL-C-170	170 180 190 200	TL-C-370	370 380 390 400
TL-C-210	210 220 230 240	TL-C-410	410 420 435 450
TL-C-250	250 260 270 280	TL-C-465	465 480 490 500



15 mm

TL-C-170
Shown actual size

Price

pk. of 10 pk. of 30

£8.70 **£25.50**


To order pack of 30, add suffix "-30" to Model No.

Ordering Example: TL-C-105-30, Four Dot Label, (105 to 120°F), pack of 30, £25.50.

3 Dot Labels (°C/°F)

TL-T labels have three temperature ratings on a single label, which gives the user more information about the maximum temperature of the label. Use these labels to bracket the maximum temperature. TL-T labels are supplied 20 or 40 to a pack.

Model No. (pk. 20)	Temperature Range °C (°F)	Model No.	Temperature Range °C (°F)
TL-T-105	41 (105) 43 (110) 46 (115)	TL-T-300	149 (300) 154 (310) 160 (320)
TL-T-120	49 (120) 54 (130) 60 (140)	TL-T-330	166 (330) 171 (340) 177 (350)
TL-T-150	66 (150) 71 (160) 77 (170)	TL-T-360	182 (360) 188 (370) 193 (380)
TL-T-180	82 (180) 88 (190) 93 (200)	TL-T-390	199 (390) 204 (400) 210 (410)
TL-T-210	99 (210) 104 (220) 110 (230)	TL-T-420	216 (420) 224 (435) 232 (450)
TL-T-240	116 (240) 121 (250) 127 (260)	TL-T-465	241 (465) 249 (480) 254 (490)
TL-T-270	132 (270) 138 (280) 143 (290)		



19 mm

TL-T-420
Shown actual size

Price

pk. of 20 pk. of 40


£11.50 **£22.75**

To order pack of 40, add suffix "-40" to Model No. **Ordering Example: TL-T-120-40, Three Dot Label, 49 to 60°(120 to 140°F), pack of 40, £22.75.**

5 Dot Labels (°C/°F)

TL-F labels have five temperature dots aligned in a straight line. This design tells the user the maximum temperature, with just a quick glance. The TL-F labels are supplied 10 or 30 to a pack.

Model No. (pk. 10)	Temperature Indicating Levels °C (°F)
TL-F-105	41 (105) 43 (110) 46 (115) 49 (120) 54 (130)
TL-F-140	60 (140) 66 (150) 71 (160) 77 (170) 82 (180)
TL-F-190	88 (190) 93 (200) 99 (210) 104 (220) 110 (230)
TL-F-240	116 (240) 121 (250) 127 (260) 132 (270) 138 (280)
TL-F-290	143 (290) 149 (300) 154 (310) 160 (320) 166 (330)
TL-F-340	171 (340) 177 (350) 182 (360) 188 (370) 193 (380)
TL-F-390	199 (390) 204 (400) 210 (410) 216 (420) 224 (435)
TL-F-450	232 (450) 241 (465) 249 (480) 254 (490) 260 (500)



19 mm

TL-F-105
Shown actual size

Price

pk. of 10 pk. of 30

£14.75 **£37.50**

To order package of 30, add suffix "-30" to Model No.

Ordering Example: TL-F-105-30, Five Dot Label, 41 to 54°C (105 to 130°F), pack of 30, £37.50.

Non-Reversible Labels


 **MOST POPULAR MODELS HIGHLIGHTED!**

8-Dot Labels (°C/°F)
TL-E labels are the most cost-effective of the TL Series labels. These labels have 8 different temperature ratings on a single label. They come in packages of 10 or 30.

Model No. (Pkg 10)	Temperature Range °C (°F)							
TL-E-105	41 (105)	43 (110)	46 (115)	49 (120)	54 (130)	60 (140)	66 (150)	71 (160)
TL-E-170	77 (170)	82 (180)	88 (190)	93 (200)	99 (210)	104 (220)	110 (230)	116 (240)
TL-E-250	121 (250)	127 (260)	132 (270)	138 (280)	143 (290)	149 (300)	154 (310)	160 (320)
TL-E-330	166 (330)	171 (340)	177 (350)	182 (360)	188 (370)	193 (380)	199 (390)	204 (400)
TL-E-410	210 (410)	216 (420)	224 (435)	232 (450)	241 (465)	249 (480)	254 (490)	260 (500)

To order package of 30, add suffix “-30” to model number.

Ordering Example: TL-E-170-30, 8-dot labels, 77 to 116°C (170 to 240°F), package of 30, £54.



TL-E-170, £23, shown actual size.

TL-E Series Price

pkg of 10 pkg of 30
£23 **£54**

5-Dot Round Labels (°C)

TL-C5 labels have 5 temperature ratings in °C scales. Ideal for measuring temperatures in small areas such as electronic applications. They are sold in packages of 10 or 30.

Model No. (Pkg 10)	Temperature-Indicating Levels					
TL-C5-105	°C	40	43	46	49	54
TL-C5-140	°C	60	66	71	77	82
TL-C5-190	°C	88	93	99	104	110
TL-C5-240	°C	116	121	127	132	138
TL-C5-290	°C	143	149	154	160	166
TL-C5-340	°C	171	177	182	188	193
TL-C5-390	°C	199	204	210	216	224
TL-C5-450	°C	232	241	249	254	260

To order package of 30, add suffix “-30” to model number.

Ordering Example: TL-C5-105-30, 5-dot round labels, (40 to 54°C), package of 30, £25.50.

15 mm (0.6")



TL-C5-450, £9, shown actual size.

TL-C5 Series Price

pkg of 10 pkg of 30
£9 **£25.50**

Non-Reversible Labels for Low Temperatures

The TL-CC series are used to control and identify problematic temperature conditions that are experienced in transportation of goods, using a low cost method for instance for medical supplies, or to increase food protection in transit to warehouse or depots. Change of state occurs after a short duration not exceeding five minutes, staining of the white paper (to blue/purple) occurs when the specified rating has been exceeded.

Model No.	Price/Pkg of 10	Description °C (°F)
TL-CC/-17C	£12	-17 (+1)
TL-CC/-8C	12	-8 (+18)
TL-CC/-5C	12	-5 (+23)
TL-CC/-2C	12	-2 (+28)
TL-CC/5C	12	+5 (+41)
TL-CC/9C	12	+9 (+48)
TL-CC/17C	12	+17 (+63)
TL-CC/20C	12	+20 (+68)

To order package specify model number

32 mm (1.25")



TL-CC/-17C, £12, shown actual size.

Specifications

Type: Non-reversible indicator, circular, self-adhesive
Size: 32 mm diameter by 6 mm deep (1.25" by 0.23" deep)
Print: 2 colors (blue print onto white background)
Temperature: °F and °C, ±0°C accurate

OMEGALABEL® Labels

OMEGALABEL® irreversible self-adhesive temperature monitors consist of 1 or more heat-sensitive indicators sealed under transparent, heat-resistant windows. The centres of the indicator circles will turn black at the temperature ratings shown on the label. The change to black is irreversible and registers the temperature history of the workpiece. The exposed OMEGALABEL can be made part of the permanent record when it is removed and affixed to a service report. These conveniently applied and easy-to-interpret temperature indicating tabs have many

industrial and military uses, as well as applications in research and development programs. The OMEGALABEL will indicate a specified temperature or sequence of temperatures, with a tolerance of ±2% of the stated temperature rating. The performance of the OMEGALABEL is not affected by transient contact with solvents, gasoline, fuel oil, lubricants, hot water, or steam.

Specifications

Accuracy: Up to 99°C (210°F) is ±1°C (1.8°F); From 100°C (212°F) to 154°C (309°F) is ±1.5°C (2.7°F); From 160°C (320°F) to 280°C (536°F) is ±1% and ±1°C (1.8°F)

Typical Applications

Machinery and Equipment

Bearings, gear boxes, transmission housings, heat exchangers, radiators

Electrical Apparatuses

Generators, transformers, rectifiers, motor casings and bearings, metal or plastic appliances

Electronic Assemblies

Tubes, transformers, transistors, resistors, printed circuits, housings

Aircraft and Rockets

Engine parts, cargo compartments, tyres, brakes, heating systems, rocket chamber walls, blast tubes



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters