

Automatic Melting Point Apparatus

Touch Screen Display



MPS40 shown smaller than actual size.

MPS40 Series




- ✔ **Maximum Temperature 400°C (752°F)**
- ✔ **Utilizes Latest Technology in Digital Imaging**
- ✔ **145 mm (5.7") Color VGA Touch Screen Display**
- ✔ **Unique Split Design Concept**
- ✔ **Integrated Cooling 350 to 50°C (662 to 122°F) in 10 Minutes**

The MPS40 automatic melting point uses the latest technology in digital image processing, to accurately identify the melt of up to 3 samples simultaneously. The unit comes with a 145 mm (5.7") color VGA display, on which the melt can be watched real time, or the melt video will automatically be saved as an AVI file that can be reviewed later, either on the unit or via PC, providing traceability long after the sample has gone. The result can also be overridden if for any reason you don't agree with the result calculated by the image processing algorithm.

The MPS40 is fully programmable via the touch screen display, once the user has set the plateau temperature they can select the ramp rate, between 0.1 and 10°C (0.2 to 18°F) in 0.1°C (0.2°F) increments. During use a library

of preset methods can be built up to streamline the method input for repeat measurements. For materials where the user is unaware of an approximate melting point, and therefore unable to set the plateau temperature, the MPS40 can be used in rapid melt mode. During rapid melt mode a fast scan of the full temperature range is undertaken to provide an approximate melt temperature, then a method will be automatically programmed with the appropriate plateau temperature to allow a more accurate measurement to be carried out.

The MPS40 has an innovative split design concept, the unit can be used as normal or the control side and the melt side can be separated, allowing for the maximum in footprint flexibility. After the samples have been loaded the melt side of the unit can be placed at the back



MPS40, melting point apparatus shown smaller than actual size.

of the bench or even in a fume cupboard to catch any potentially dangerous fumes. Once the unit has been split the control panel side can be used in two orientations, either landscape or portrait to allow the perfect viewing angle whether you are sat or stood at the bench, the screen automatically changes orientation with the unit.

The unit can store up to 200 result files with videos, if required data can be easily transferred from the unit to a flash memory drive or PC via one of the USB connectors.

The unit has been designed to include a number of other useful features such as slots to accommodate pre-prepared samples and a draw to house your unused melting point tubes. Also included in the draw is a handy glass cutter, which can be used to accurately cut tubes in half quickly and cleanly for users who prefer to use half tubes.

All units are supplied with a NIST calibration certificate showing individual serial numbers.

Specifications

Number of Samples: 3 simultaneously

Temperature Range: Ambient to 400°C (752°F)

Temperature Resolution: 0.1°C

Display: 145 mm (5.7") color VGA touch screen

Ramp Rates: 0.1 to 10°C (0.2 to 18°F) in 0.1°C (0.2°F) increments

Temperature Sensor: Pt1000 platinum resistance

Memory: 200 results with video

Cool Down Time: 350 to 50°C (662 to 122°F), 10 minutes

Heat Up Time: 50 to 350°C (122 to 662°F), 6 minutes

Oven Control: Closed loop PID

Flash Memory/PC Interface: USB

Sample Level: 2 to 3 mm in 50 mm, or 100 mm length capillaries

Electrical Supply: 120V/230V, 50 to 60 Hz

Temperature Units: °C, °F, K

Dimensions: 175 H x 210 D x 328 mm W (6.9 x 8.3 x 13")

Net Weight: 3.2 kg (113 oz)

IP Rating: 30

To Order Visit omega.com/mps40 for Pricing and Details

Model No.	Description
MPS40	Melting point apparatus with pack of 100 melting point tubes, closed at both ends
MPS40-TUBESSEALED	Spare glass melting point tubes, closed at both ends, pack of 100

Comes complete with 100 melting point tubes, RS232 cable, USB cable, UK, European and USA power cords, NIST calibration certificate and operator's manual.

Ordering Example: MPS40, melting point apparatus, closed at both ends.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters