



# Sanitary Thermistor Assemblies


## Heavy-Duty with Protection Head

### THS-H-NB9W Series



**3-A Approved  
For Use in  
CIP and Sanitary  
Processes**

3/4" NPT process connection.



White polypropylene screw cover connection head.

- ✓ Heavy-Duty Probe Design With Stepped Probe Stem for Additional Strength
- ✓ 1 1/2" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
- ✓ White Polypropylene Head with Screw Cap Standard
- ✓ 316L SS Wetted Surfaces with 32 µin or Better Finish
- ✓ 10k Thermistor Element (44006) Standard
- ✓ -80 to 150°C (-112 to 302°F) Temperature Range

The OMEGA® THS-H-NB9W Series thermistor probe assemblies are available in standard lengths from 3 to 6", with standard 10 kΩ (44006) thermistor element. These heavy-duty probes have a 3/8" diameter, which steps down to a 3/16" diameter at the probe tip, for fast response and additional strength. Standard features include a 1 1/2" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including element types and curves, probe lengths, protection heads and sanitary fitting styles.

1 1/2"

316L SS 1 1/2" 16 AMP Tri-Grip™ cap standard.

3/8" diameter

Probe length

3/16" diameter

1 1/4"

#### Element Options

Sensor Code	Resistance @ 25°C	Element Series
2K	2252 Ω	44004
3K	3000 Ω	44005
5K	5000 Ω	44007
30K	30,000 Ω	44008

For other thermistor elements, change the model number from "10K" to the desired sensor code as shown in the table above, no additional cost.

THS-10K-H-0300-D1-NB9W shown smaller than actual size.

#### Options

- ✓ Fitting Styles
- ✓ Protection Heads
- ✓ Probe Lengths
- ✓ Thermistor Elements

### To Order Visit [omega.com/th-s-h-nb9w](http://omega.com/th-s-h-nb9w) for Pricing and Details

Model Number	Resistance at 25°C	Element Series	Interchangeability (0 to 70°C)	Sheath Diameter	Probe Length
THS-10K-H-0300-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	3"
THS-10K-H-0400-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	4"
THS-10K-H-0500-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	5"
THS-10K-H-0600-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	6"

For lengths longer than 6", change "0600" in model number to the required length (eg, 12" = 1200, 9 1/4" = 0925) for an additional cost.

To order with NB15 large 316 SS head, change model number suffix from "-NB9W" to "-NB15" for an additional cost.

Ordering Example: THS-10K-H-0400-D1-NB9W, 10,000 Ω thermistor sensor, 1 1/2" 16 A Tri-Grip™ fitting, 4" length, heavy duty probe, NB9W white polypropylene screw cap protection head.



# Sanitary Thermistor Assemblies

## Standard Duty with Protection Head

### THS-S-NB9W Series



**3-A Approved  
For Use in  
CIP and Sanitary  
Processes**

- ✓ Standard Duty 1/4" Probe Diameter
- ✓ 1 1/2" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
- ✓ White Polypropylene Head with Screw Cap Standard
- ✓ 316L SS Wetted Surfaces with 32 µin or Better Finish
- ✓ 10k Thermistor Element (44006) Standard
- ✓ -80 to 150°C (-112 to 302°F) Temperature Range

### Options

- ✓ Fitting Styles
- ✓ Protection Heads
- ✓ Probe Lengths
- ✓ Thermistor Elements

**32 µin  
Finish**


The OMEGA® THS-S-NB9W Series thermistor probe assemblies are available in standard lengths from 3 to 6", with standard 10 kΩ (44006) thermistor element. Standard features include a 1 1/2" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including element types and curves, probe lengths, protection heads and sanitary fitting styles.

### Element Options

Sensor Code	Resistance @ 25°C	Element Series
2K	2252 Ω	44004
3K	3000 Ω	44005
5K	5000 Ω	44007
30K	30,000 Ω	44008

For other thermistor elements, change the model number from "10K" to the desired sensor code as shown in the table above, no additional cost.

3/8" NPT process connection.



White polypropylene screw cover connection head.

316L SS 1 1/2" 16 AMP Tri-Grip™ cap standard.

1 1/2"

Probe length

1/4" diameter.

THS-10K-S-0300-D1-NB9W shown smaller than actual size.

### To Order Visit [omega.com/ths-h-nb9w](http://omega.com/ths-h-nb9w) for Pricing and Details

Model Number	Resistance at 25°C	Element Series	Interchangeability (0 to 70°C)	Sheath Diameter	Probe Length
THS-10K-S-0300-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	3"
THS-10K-S-0400-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	4"
THS-10K-S-0500-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	5"
THS-10K-S-0600-D1-NB9W	10,000 Ω	44006	±0.2°C	1/4"	6"

For lengths longer than 6", change "0600" in model number to the required length (eg, 12" = 1200, 9 1/4" = 0925) for an additional cost.

To order with NB15 large 316 SS protection head, change model number suffix from "-NB9W" to "-NB15" for an additional cost.

Ordering Example: THS-10K-S-0400-D1-NB9W, 10,000 Ω thermistor sensor, 1 1/2" 16 A Tri-Grip™ fitting, 4" length, standard duty probe, NB9W white polypropylene screw cap protection head.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters