

# Thermoelectric Alloy Property Data

| ALLOY or DESIGNATION       | Notes | PERCENT PURITY or composition | RESISTIVITY $\Omega$ cmil/ft (at 0°C) |        | TEMP COEFF. OF RESISTANCE (0-100°C) |        | TENSILE STRENGTH (psi x 1000) |        | ELONGATION (percent) |        | Melting point °C | Density (g/cm <sup>3</sup> ) |
|----------------------------|-------|-------------------------------|---------------------------------------|--------|-------------------------------------|--------|-------------------------------|--------|----------------------|--------|------------------|------------------------------|
|                            |       |                               | Hard                                  | Annl'd | Hard                                | Annl'd | Hard                          | Annl'd | Hard                 | Annl'd |                  |                              |
| <b>Pure Metals</b>         |       |                               |                                       |        |                                     |        |                               |        |                      |        |                  |                              |
| Iron                       |       | 99.9+%                        | 66                                    | 60     | .0062                               | .0065  | 90                            | 34     | 2                    | 40     | 1536             | 7.9                          |
| Nickel                     |       | 99.98%                        | 39                                    | 37     | .0064                               | .0068  | 100                           | 48     | 2                    | 36     | 1452             | 8.9                          |
| Molybdenum                 |       | 99.9+%                        | 42                                    | 31     | .0036                               | .0047  | 250                           | 120    | 2                    | 16     | 2610             | 10.2                         |
| Aluminum (H-P)             |       | 99.99+%                       | 17.4                                  | 15     | .0038                               | .0044  | 16.3                          | 6.8    | 5                    | 60     | 660              | 2.71                         |
| Copper                     |       | 99.98%                        | 9.44                                  | 9.24   | .0041                               | .0043  | 76                            | 32     | 1.5                  | 46     | 1083             | 8.93                         |
| Gold                       |       | 99.999%                       | 13.4                                  | 13.17  | .0039                               | .0040  | 46                            | 19     | 1.5                  | 36     | 1063             | 19.30                        |
| Silver                     |       | 99.99%                        | 9.3                                   | 8.83   | .0038                               | .0041  | 52                            | 24     | 1.5                  | 46     | 960.8            | 10.5                         |
| Tungsten                   |       | 99.99%                        | 42                                    | 33     | .0036                               | .0048  | 285                           | 80     | -                    | 3      | 3410             | 19.3                         |
| Rhenium                    |       | 99.99%                        | -                                     | 117    | -                                   | -      | 360                           | 170    | -                    | 10     | 3170             | 20.0                         |
| Platinum Ref               |       | 99.999+%                      | 61.2                                  | 59.13  | .00386                              | .00393 | 60                            | 24     | 2                    | 38     | 1769             | 21.45                        |
| Rhodium                    |       | 99.99%                        | 33.0                                  | 25.8   | .0029                               | .0046  | 275                           | 120    | 2                    | 16     | 1966             | 12.42                        |
| <b>Platinum</b>            |       |                               |                                       |        |                                     |        |                               |        |                      |        |                  |                              |
| Pt- 6%Rh                   |       | 94%Pt- 6%Rh                   | 101                                   | 95     | .0019                               | .0020  | 85                            | 37     | 1.5                  | 34     | 1810             | 20.51                        |
| Pt-10%Rh                   |       | 90% Pt-10% Rh                 | 114                                   | 111    | .0016                               | .0017  | 95                            | 46     | 1.5                  | 32     | 1830             | 19.95                        |
| Pt-13% Rh                  |       | 87% Pt-13% Rh                 | 119                                   | 114    | .0015                               | .0016  | 105                           | 48     | 1.5                  | 32     | 1840             | 19.55                        |
| Pt-20% Rh                  |       | 80% Pt-20% Rh                 | 124                                   | 116    | .0013                               | .0014  | 140                           | 72     | 1.5                  | 32     | 1870             | 18.65                        |
| Pt-30% Rh                  |       | 70% Pt-30% Rh                 | 116                                   | 112    | .0013                               | .0014  | 160                           | 74     | 1.5                  | 26     | 1910             | 17.52                        |
| Pt-40% Rh                  |       | 60% Pt-40% Rh                 | 108                                   | 101    | .0013                               | .0014  | 190                           | 78     | 1.5                  | 26     | 1920             | 16.54                        |
| <b>Nickel Alloys</b>       |       |                               |                                       |        |                                     |        |                               |        |                      |        |                  |                              |
| Constantan                 |       | 55% Cu-45% Ni                 | 315                                   | 294    | .00003                              | .00002 | 150                           | 80     | 2                    | 32     | 1270             | 8.86                         |
| CHROMEGA® P                |       | 90% Ni-10% Cr                 | -                                     | 425    | .00032                              | .00032 | 165                           | 95     | 2                    | 27     | 1430             | 8.73                         |
| ALOMEGA®                   |       | 95% Ni-2% Mn-2% Al            | -                                     | 177    | .00188                              | .00188 | 170                           | 85     | 2                    | 32     | 1400             | 8.60                         |
| <b>Tungsten Alloys</b>     |       |                               |                                       |        |                                     |        |                               |        |                      |        |                  |                              |
| Tungsten-3% Re             |       | 97% W- 3% Re                  | -                                     | 55     | -                                   | -      | 320                           | 180    | -                    | 10     | 3410             | 19.4                         |
| Tungsten-5% Re             |       | 95% W- 5% Re                  | -                                     | 70     | -                                   | -      | 320                           | 200    | -                    | 10     | 3350             | 19.4                         |
| Tungsten-25% Re            |       | 75% W-25% Re                  | -                                     | 165    | -                                   | -      | 300                           | 210    | -                    | 10     | 3130             | 19.7                         |
| Tungsten-26% Re            |       | 74% W-26% Re                  | -                                     | 170    | -                                   | -      | 300                           | 200    | -                    | 10     | 3120             | 19.7                         |
| <b>Compensating Alloys</b> |       |                               |                                       |        |                                     |        |                               |        |                      |        |                  |                              |
| Alloy #11                  | (1)   | Pt alloys                     | -                                     | 30     | -                                   | .0014  | 105                           | 50     | 2                    | 30     | 1090             | 8.91                         |
| Alloy #200                 |       | Tungsten                      | -                                     | 470    | -                                   | -      | -                             | -      | -                    | -      | 1430             | 8.73                         |
| Alloy #203                 |       | Tungsten- 3% Re               | -                                     | 470    | -                                   | .0003  | -                             | -      | -                    | -      | 1400             | 8.60                         |
| Alloy #205                 |       | Tungsten- 5% Re               | -                                     | 510    | -                                   | -      | -                             | -      | -                    | -      | 1410             | 8.58                         |
| Alloy #225                 |       | Tungsten-25% Re               | -                                     | 180    | -                                   | .0012  | -                             | -      | -                    | -      | 1370             | 8.88                         |
| Alloy #226                 |       | Tungsten-26% Re               | -                                     | 160    | -                                   | -      | -                             | -      | -                    | -      | 1450             | 8.85                         |
| Alloy #260                 |       | Tungsten-26% Re               | -                                     | 750    | -                                   | -      | -                             | -      | -                    | -      | 1520             | 7.42                         |

1. "Percent purity or composition" column refers to matching thermocouple grade alloy.

# Changes in Thermocouple Resistance with Increasing Temperature

| N=Neg<br>P=Pos<br>Thermoelements | Ratio of Resistance at Temperature Indicated to Resistance at 0°C (32°F) |             |               |               |                |                |                 |                 |                 |                 |
|----------------------------------|--|-------------|---------------|---------------|----------------|----------------|-----------------|-----------------|-----------------|-----------------|
|                                  | 0°C (32°F)   | 20°C (68°F) | 200°C (392°F) | 400°C (752°F) | 600°C (1112°F) | 800°C (1472°F) | 1000°C (1832°F) | 1200°C (2192°F) | 1400°C (2552°F) | 1500°C (2732°F) |
| JP                               | 1.00   | 1.13        | 2.46          | 4.72          | 7.84           | 12.0           | 13.07           | ...             | ...             | ...             |
| JN, TN, EN                       | 1.00   | 0.999       | 0.996         | 0.994         | 1.02           | 1.056          | 1.092           | ...             | ...             | ...             |
| TP                               | 1.00   | 1.11        | 1.86          | 2.75          | 3.70           | 4.75           | 5.96            | ...             | ...             | ...             |
| KP, EP                           | 1.00   | 1.01        | 1.09          | 1.19          | 1.25           | 1.30           | 1.37            | 1.43            | ...             | ...             |
| KN                               | 1.00   | 1.05        | 1.43          | 1.64          | 1.82           | 1.98           | 2.15            | 2.32            | ...             | ...             |
| NP                               | 1.00   | 1.01        | 1.02          | 1.07          | 1.08           | 1.08           | 1.10            | ...             | ...             | ...             |
| NN                               | 1.00   | 1.07        | 1.13          | 1.27          | 1.39           | 1.55           | 1.68            | ...             | ...             | ...             |
| RP                               | 1.00   | 1.03        | 1.31          | 1.60          | 1.89           | 2.16           | 2.41            | 2.66            | 2.90            | 3.01            |
| SP                               | 1.00   | 1.03        | 1.33          | 1.65          | 1.95           | 2.23           | 2.50            | 2.76            | 3.01            | 3.13            |
| RN, SN                           | 1.00   | 1.06        | 1.77          | 2.50          | 3.18           | 3.81           | 4.40            | 4.94            | 5.42            | 5.66            |
| BP                               | 1.00   | 1.03        | 1.26          | 1.51          | 1.76           | 1.98           | 2.20            | 2.41            | 2.62            | 2.73            |
| BN                               | 1.00   | 1.03        | 1.40          | 1.78          | 2.14           | 2.47           | 2.78            | 3.08            | 3.37            | 3.51            |

| N=Neg, P=Pos Resistance of Thermocouples, ohms per foot at 20°C ( 68°F) |              |        |       |          |         |        |       |        |        |        |        |        |        |
|---|--------------|--------|-------|----------|---------|--------|-------|--------|--------|--------|--------|--------|--------|
| Awg. No.  | Diameter in. | KN     | KP,EP | TN,JN,EN | TP      | JP     | NP    | NN     | RN, SN | RP     | SP     | BP     | BN     |
| 16  | 0.0508       | 0.0683 | 0.164 | 0.1113   | 0.00402 | 0.0276 | .2230 | .08458 | 0.0247 | 0.0456 | 0.0445 | 0.0447 | 0.0414 |
| 20  | 0.0320       | 0.173  | 0.415 | 0.287    | 0.0102  | 0.0699 | .5664 | .2148  | 0.0624 | 0.1149 | 0.1125 | 0.1130 | 0.1046 |
| 24  | 0.0201       | 0.438  | 1.05  | 0.728    | 0.0257  | 0.1767 | 1.436 | .5445  | 0.1578 | 0.4656 | 0.2847 | 0.2859 | 0.2647 |
| 30  | 0.0100       | 1.77   | 4.25  | 2.94     | 0.1032  | 0.710  | 5.800 | 2.20   | 0.6344 | 2.965  | 1.144  | 1.149  | 1.064  |
| 36  | 0.0050       | 7.08   | 17.0  | 11.8     | 0.4148  | 2.86   | 23.20 | 8.800  | 2.550  | 12.25  | 4.600  | 4.620  | 4.277  |

# Thermocouple Types

**Iron-Constantan (ANSI Symbol J)** The Iron-Constantan "J" curve thermocouple with a positive iron wire and a negative Constantan wire is recommended for reducing atmospheres. The operating range for this alloy combination is 1600°F for the largest wire sizes. Smaller size wires should operate in correspondingly lower temperatures.

**Copper-Constantan (ANSI Symbol T)** The Copper-Constantan "T" curve thermocouple, with a positive copper wire and a negative Constantan wire, is recommended for use in mildly oxidizing and reducing atmospheres up to 750°F. They are suitable for applications where moisture is present. This alloy is recommended for low temperature work since the homogeneity of the component wires can be maintained better than with other base metal wires. Therefore, errors due to inhomogeneity of wires in zones of temperature gradients are greatly reduced.

**CHROME<sup>®</sup>-ALOMEGA<sup>®</sup> (ANSI Symbol K)** The CHROME<sup>®</sup>-ALOMEGA<sup>®</sup> "K" curve thermocouple with a positive CHROME<sup>®</sup> wire and a negative ALOMEGA<sup>®</sup> wire is recommended for use in clean oxidizing atmospheres. The operating range for this alloy is 2300°F for the largest wire sizes. Smaller wire sizes should operate in correspondingly lower temperatures.

**CHROME<sup>®</sup>-Constantan (ANSI Symbol E)** The CHROME<sup>®</sup>-Constantan thermocouple may be used for temperatures up to 1600°F in a vacuum or inert, mildly oxidizing or reducing atmosphere. At sub-zero temperatures, the thermocouple is not subject to corrosion. This thermocouple has the highest emf output of any standard metallic thermocouple.

**Platinum-Rhodium Alloys (ANSI Symbols S, R and B)** Three types of "noble-metal" thermocouples are in common use; they are: 1) a positive wire of 90% platinum and 10% rhodium used with a negative wire of pure platinum, 2) a positive wire of 87% platinum and 13% rhodium used with a negative wire of pure platinum, and 3) a positive wire of 70% platinum and 30% rhodium used with a negative wire of 94% platinum and 6% rhodium. They have a high resistance to oxidation and corrosion. However, hydrogen, carbon and many metal vapors can contaminate a platinum-rhodium thermocouple. The recommended operating range for the platinum-rhodium alloys is 2800°F, although temperatures as high as 3270°F can be measured with the Pt-30% Rh vs. Pt-6% Rh alloy combination.


**Tungsten-Rhenium Alloys** Three types of tungsten-rhenium thermocouples are in common use for measuring temperatures up to 5000°F. These alloys have inherently poor oxidation resistance and should be used in vacuum, hydrogen or inert atmospheres.

# Trade Names of Alloys

| ANSI DESIGNATION | ALLOY (Generic or Trade Names)                                  |
|------------------|---|
| JP               | Iron  |
| JN, EN, or TN    | Constantan, Cupron, Advance                                     |
| KP or EP         | CHROME <sup>®</sup> , Tophel, T <sub>1</sub> , Thermokanthal KP |
| KN               | ALOMEGA <sup>®</sup> , Nial, T <sub>2</sub> , Thermokanthal KN  |
| TP               | Copper  |
| RN or SN         | Pure Platinum   |
| RP               | Platinum 13% Rhodium  |
| SP               | Platinum 10% Rhodium  |

Trade Names: Advance T - Driver Harris Co., CHROME<sup>®</sup> and ALOMEGA<sup>®</sup> - OMEGA Engineering, Inc., Cupron, Nial and Trophei - Wilbur B. Driver Co., Thermokanthal KP and Thermokanthal KN - The Kanthal Corporation.

ANSI LETTER DESIGNATIONS -Currently thermocouple and extension wire is ordered and specified by an ANSI letter designation. Popular generic and trade name examples are CHROME<sup>®</sup>/ALOMEGA<sup>®</sup> -ANSI Type K; Iron/Constantan - ANSI Type J; Copper/Constantan - ANSI Type T CHROME<sup>®</sup>/Constantan -ANSI Type E; Platinum/Platinum 10% Rhodium - ANSI Type S; Platinum/Platinum 13% Rhodium -ANSI Type R. The positive and negative legs are identified by letter suffixes P and N, respectively, as listed in the tables.



## ANSI Symbol

- T Copper vs. Constantan
- E CHROME<sup>®</sup> vs. Constantan
- J Iron vs. Constantan
- K CHROME<sup>®</sup> vs. ALOMEGA<sup>®</sup>
- N\* OMEGALLOY<sup>®</sup> Nicrosil-Nisil
- G\* Tungsten vs. Tungsten 26% Rhenium
- C\* Tungsten 5% Rhenium vs. Tungsten 26% Rhenium
- D\* Tungsten 3% Rhenium vs. Tungsten 25% Rhenium
- R Platinum 13% Rhodium vs. Platinum
- S Platinum 10% Rhodium vs. Platinum
- B Platinum 30% Rhodium vs. Platinum 6% Rhodium

\*Not an ANSI Symbol

## Resistance Vs. Wire Diameter

| AWG No. | Diameter inches | Type K CHROME <sup>®</sup> /ALOMEGA <sup>®</sup> | Type J Iron/Constantan | Type T Copper/Constantan | Type E CHROME <sup>®</sup> /Constantan | Type S Pt/Pt10%Rh | Type R Pt/Pt13%Rh | Type RX/SX Copper Alloy11** | Type C† W5%Re/W26%Re | Type CX Alloy 405 Alloy 426 | Type G† W/W26%Re | Type D† W3%Re/W25%Re | Type BX Copper/Copper* |
|---------|-----------------|--|------------------------|--------------------------|--|-------------------|-------------------|-----------------------------|----------------------|-----------------------------|------------------|----------------------|------------------------|
| 6       | 0.162           | 0.023  | 0.014                  | 0.012                    | 0.027                                  | 0.007             | 0.007             | 0.003                       | 0.009                | 0.014                       | 0.008            | 0.009                | 0.000790               |
| 8       | 0.128           | 0.037  | 0.022                  | 0.019                    | 0.044                                  | 0.011             | 0.011             | 0.004                       | 0.015                | 0.023                       | 0.012            | 0.015                | 0.001256               |
| 10      | 0.102           | 0.058  | 0.034                  | 0.029                    | 0.069                                  | 0.018             | 0.018             | 0.007                       | 0.023                | 0.037                       | 0.020            | 0.022                | 0.001998               |
| 12      | 0.081           | 0.091  | 0.054                  | 0.046                    | 0.109                                  | 0.028             | 0.029             | 0.011                       | 0.037                | 0.058                       | 0.031            | 0.035                | 0.00318                |
| 14      | 0.064           | 0.146  | 0.087                  | 0.074                    | 0.175                                  | 0.045             | 0.047             | 0.018                       | 0.058                | 0.093                       | 0.049            | 0.055                | 0.00505                |
| 16      | 0.051           | 0.230  | 0.137                  | 0.117                    | 0.276                                  | 0.071             | 0.073             | 0.028                       | 0.092                | 0.146                       | 0.078            | 0.088                | 0.00803                |
| 18      | 0.040           | 0.374  | 0.222                  | 0.190                    | 0.448                                  | 0.116             | 0.119             | 0.045                       | 0.148                | 0.238                       | 0.126            | 0.138                | 0.01277                |
| 20      | 0.032           | 0.586  | 0.357                  | 0.298                    | 0.707                                  | 0.185             | 0.190             | 0.071                       | 0.235                | 0.371                       | 0.200            | 0.220                | 0.02030                |
| 24      | 0.0201          | 1.490  | 0.878                  | 0.7526                   | 1.78                                   | 0.464             | 0.478             | 0.180                       | 0.594                | 0.941                       | 0.560            | 0.560                | 0.05134                |
| 26      | 0.0159          | 2.381  | 1.405                  | 1.204                    | 2.836                                  | 0.740             | 0.760             | 0.288                       | 0.945                | 1.503                       | 0.803            | 0.890                | 0.08162                |
| 30      | 0.0100          | 5.984  | 3.551                  | 3.043                    | 7.169                                  | 1.85              | 1.91              | 0.727                       | 2.38                 | 3.800                       | 2.03             | 2.26                 | 0.2064                 |
| 32      | 0.0080          | 9.524  | 5.599                  | 4.758                    | 11.31                                  | 1.96              | 3.04              | 1.136                       | 3.8                  | 5.94                        | 3.22             | 3.60                 | 0.3282                 |
| 34      | 0.0063          | 15.17  | 8.946                  | 7.66                     | 18.09                                  | 4.66              | 4.82              | 1.832                       | 6.04                 | 9.57                        | 5.10             | 5.70                 | 0.5218                 |
| 36      | 0.0050          | 24.08  | 14.20                  | 12.17                    | 28.76                                  | 7.40              | 7.64              | 2.908                       | 9.6                  | 15.20                       | 8.16             | 9.10                 | 0.8296                 |
| 38      | 0.0039          | 38.20  | 23.35                  | 19.99                    | 45.41                                  | 11.6              | 11.95             | 4.780                       | 15.3                 | 24.98                       | 12.9             | 15.3                 | 1.3192                 |
| 40      | 0.00315         | 60.88  | 37.01                  | 31.64                    | 73.57                                  | 18.6              | 19.3              | 7.327                       | 24.4                 | 38.30                       | 20.6             | 23.0                 | 2.098                  |
| 44      | 0.0020          | 149.6  | 88.78                  | 76.09                    | 179.20                                 | 74.0              | 76.5              | 18.18                       | 60.2                 | 95.00                       | 51.1             | 56.9                 | 5.134                  |
| 50      | 0.0010          | 598.4  | 355.1                  | 304.3                    | 716.9                                  | 185               | 191               | 72.7                        | 240                  | 380.0                       | 204              | 227                  | 20.64                  |
| 56      | 0.00049         | 2408   | 1420                   | 1217                     | 2816                                   | 740               | 764               | 302.8                       | 1000                 | 1583                        | 850              | 945                  | 86.38                  |

\*Increase the resistance by 19% for nickel plated, type RTD wire

\*\*Maximum Resistance of reviewed wire

†Not ANSI symbol