

**NEW**

# EASIEST TO PROGRAM, CONNECT & OPERATE **EZ Series™** PLC TEXTPANELS



Series Starts at  
**\$261**

**TESTED AND PROVEN BY  
20,000+ ENGINEERS**

- Easy to Learn, Intuitive Software
- Easy to Operate Menu Driven Messages
- Easy to Connect to Most PLCs
- Easy to Maintain Hardware
- Easy on the Budget
- 7 Models to Choose From
- NEMA 4x Indoor

**EZ Series Textpanels  
are Easy to Operate**



- 2 x 20 or 4 x 20 Ch. Message Display
- 5 User Defined Pushbuttons and LEDs
- Scroll Data Entry Buttons
- Numeric Keypad on "P" Models
- Setpoint Model w/ LED Display

### Hi-Brite VFD Models

EZ Series Textpanels and EZ Series TextPLCs have been enhanced to incorporate a vacuum fluorescent display that has greater visibility as well as a wider viewing angle. At \$296 for EZ-220V and \$362 for EZ-220PV, these Textpanels cost almost 1/4th the price of Allen Bradley Data Liners and offer an excellent value prop-osition.



**EZ Series Textpanels  
have Drivers for Most PLCs**


### Serial Drivers

- Allen-Bradley DF1 Half and Full Duplex (PLC-5, SLC 500, MicroLogix 1000, 1200 and 1500) DH485/AIC/AIC+ for MicroLogix 1000, 1200, 1500, SLC500, 5/01, /02, /03
- Aromat Mewtocol COM
- Control Techniques - Unidrive 2-wire, 4-wire (binary)
- CTC Binary
- GE Fanuc SNPX (90/30, 90/70)
- Idec Computer Link
- Omron Host Link (C200 and C500)
- All Mitsubishi FX Series
- Modicon MODBUS® RTU
- Siemens S7 MPI Adaptor series
- Texas Instruments - T15x5 Series

**EZ Series Textpanels  
Exclusive Features**

### Multi-Color Annunciator LED Lamps

The annunciator lamps on the EZ-220P and EZ-220PV models are configured similar to pushbuttons. Once you have selected the starting address in the PLC, all of the lamp colors will be identified by the bit pairs. The color that the lamp illuminates depends on the bit assignment of the address selected.




### 256 User Programmable Messages

There are two message types which can be displayed: local and PLC. Local messages are displayed on the screen unless the PLC triggers a PLC message, which overrides a local message.



### PLC Message LED Indicator

When a PLC message is triggered, the PLC Message LED will also be illuminated. The PLC message LED will remain on until the user acknowledges the situation by pressing [esc] on the panel.



**Easy as 1-2-3  
Programming Software**

### Step 1

Configure pushbuttons and LED Light indicators

### Step 2

Configure Hi-brite Lamps


### Step 3

Program User-Programmable Messages

**\$44**  
Programming Software

**NEW**

**EZ Multiplexer**  
**\$430**



**SPECIFICATIONS**

- Enclosure:** NEMA 4/4X Indoor
- CPU Type:** 8 bit
- OS:** Dedicated (non-Windows)
- Service Power:** 24 Vdc (20-30 Vdc)  
4 - 8.5 Watts depending on model
- Agency Approval:** UL, CUL, CE
- Operating Temp:** 0 to 45°C  
(32 to 113°F)
- Storage Temp:** -20 to 60°C  
(-4 to 140°F)
- Humidity:** 10 to 95% RH,  
non-condensing
- Withstand Voltage:** 1000 Vdc 1 min.
- Vibration:** 5-55Hz, 2G for 2 hours
- Shock:** 10 G under 12 ms
- Electrical Noise:** NEMA ICS 2-230  
Showering Arc
- No. of Messages:** Up to 256
- LED/LCD Life:** 100,000 hours
- Mounting:** DIN

**DIMENSIONS:**

- EZ220(V)/420:**  
7.418 x 5 x 1.154"
- EZ220L/220P(V)/SP:**  
10.018 x 5 x 1.154"

**VIEWING ANGLE:**

- EZ220(L,P)/420/SP:**  
± 15 degrees horizontal
- EZ220V/EZ220PV:**  
± 60 degrees horizontal

**CHARACTER HEIGHT:**

- EZ220/EZ220P/EZ220V/EZ220PV:**  
5.55 mm
- EZ220L/EZSP:**  
8.06 mm
- EZ420:**  
4.75 mm

**Communication Master Unit**

EZ Multiplexer is a docking station, where you may connect up to 5 of any combination of EZ Series Textpanels. When you select the multi-panel system in the programming software, you can configure panels for one port each.

A write utility is included so you can download changes to one or more panels on the complete system without EZ Series Software.

To Order (Specify Model Number)		MOST POPULAR MODELS HIGHLIGHTED!	
MODEL NO.	PRICE	DESCRIPTION	
<b>EZ-220</b>	<b>\$261</b>	2 line 20 channel LCD Textpanel	
<b>EZ-220L</b>	<b>338</b>	2 line 20 large channel LCD Textpanel	
<b>EZ-420</b>	<b>292</b>	4 line 20 channel LCD Textpanel	
<b>EZ-220P</b>	<b>353</b>	2 line 20 channel LCD Textpanel w/numeric keypad	
<b>EZ-SP</b>	<b>353</b>	Setpoint interface with 8 digit numeric display	
<b>EZ-220V</b>	<b>415</b>	2 Line 20 channel VFD Textpanel	
<b>EZ-220PV</b>	<b>500</b>	2 Line 20 channel VFD Textpanel w/numeric keypad	
SOFTWARE AND ACCESSORIES			
<b>EZ-SERIESEDIT-E</b>	<b>\$44</b>	Programming software for EZ Series Text Enhanced	
<b>EZ-SERIES-PGMCBL</b>	<b>26</b>	RS232 programming cable for EZ Series Text Enhanced	
<b>EZ-SERIES-S-GSK</b>	<b>13</b>	Replacement gasket for EZ-220, EZ-220V, EZ-420	
<b>EZ-SERIES-L-GSK</b>	<b>14</b>	Replacement gasket for EZ-220L, EZ-220PV, EZ-220P	
<b>EZ-BRK-2</b>	<b>54</b>	DIN rail clips for EZ Series Text Enhanced, 4 in package	
<b>EZ-SERIES-STUDS</b>	<b>13</b>	Spare mounting studs (4 studs with nuts included)	
<b>EZ-SERIES-CORE</b>	<b>24</b>	Ferrite core (pack of 2)	
<b>EZ-SERIES-PWRTERM</b>	<b>20</b>	Replacement power terminal strip	
<b>EZ-MULTIDROP</b>	<b>430</b>	Multiplexer for connecting 5 Textpanels to 1 PLC	

**Ordering Examples:** EZ-220, 2 line x 20 character LCD text panel, EZ-SERIESEDIT-E, programming software, EZ-SERIES-PGMCBL, RS-232 programming cable, \$261 + 44 + 26 = \$331.  
EZ-220P, 2 x 20 character LCD text panel with numeric keypad, EZ-SERIESEDIT-E, programming software, EZ-SERIES-PGMCBL, programming cable, \$353 + 44 + 26 = \$423.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters