

# DRF-RTD RTD Input Signal Conditioner



All Models  
**£121**



- ✓ 100 Ω Platinum (Pt) RTD Element, 0.00385 Curve
- ✓ 2- or 3-Wire Configuration
- ✓ 0.2% Accuracy
- ✓ Cable Resistance Compensation Up to 10 Ω
- ✓ Upscale Break Protection
- ✓ Response Time <250 ms
- ✓ Galvanic Isolation Between Input, Output, and Power

DRF-RTD signal conditioners accept 2- or 3-wire 100 Ω platinum RTDs as input and provide an isolated 0 to 10 Vdc or 4 to 20 mA output. Models are available with three different power options; 24 Vdc, 115 Vac, and 230 Vac.

DRF-RTD conditioners are ideally suited for industrial applications. All models mount on a standard 35 mm DIN rail and provide galvanic isolation between input, output, and power up to 3500 Veff (model specific). Module response time is 250 ms or less.

## Specifications

**RTD:** 2- or 3-wire 100 Ω platinum RTD,  $\alpha=0.00385$

**Accuracy:** <0.2% full scale


**Linearity:** <0.1% full scale

**Thermal Drift:** 250 ppm/°C typical

**Response Time:** <250 ms (90% of signal)

**RTD Excitation:** 1 Vdc

**Input Impedance:** Measured with a Wheatstone bridge; bridge to positive through a 100 Ω resistance, bridge to negative through a 10 KΩ resistance



## Range Code Table

Range Code	Range
-25/75C	-25 to 75°C
-50/150C	-50 to 150°C
0/100C	0 to 100°C
0/200C	0 to 200°C
0/300C	0 to 300°C
0/450C	0 to 450°C
0/600C	0 to 600°C

\* Custom ranges can be obtained by adjusting on-board zero and span potentiometers. The minimum range is 0 to 50°C (32 to 122°F), maximum range is 0 to 600°C (32 to 1112°F).

DRF-RTD-24VDC-0/100C-0/10, £121, shown larger than actual size



**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
DRF-RTD-(*)-(**)-(***)	£121	Signal conditioner for 100 Ω Pt RTD
CS-3775	54	Reference Book: Control System Design Guide

\* Specify power: "24VDC" for 24 Vdc power, "115VAC" for 115 Vac power or "230VAC" for 230 Vac power.

\*\* Specify range code from the Range Code Table.

\*\*\* Specify output: "4/20" for 4 to 20 mA output or "0/10" for 0 to 10 Vdc output.

**Ordering Example:** DRF-RTD-24VDC-0/100C-0/10, signal conditioner for an RTD with a 0 to 100°C input range, 0 to 10 Vdc output and 24 Vdc power, £121.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters