OM-CP-HITEMP-150 Extended-Range Submersible

Temperature Data Logger Part of the NOMAD® Family

Starts at

\$499

- ✓ Operating Temperature Range: -40 to 150°C (-40 to 302°F)
- ✓ Submersible to 70 m (230')
- Programmable Start Time
- User Calibration Through Software
- **✓** Real-Time Operation
- Autoclave Verification
- ✓ Pharmaceutical
- Implement HACCP Programs
- Food Preparation and Processing
- ✓ Environmental Studies
- ✓ Well Monitoring
- Dish Washer Testing
- Hostile Environment Monitoring

The OM-CP-HITEMP-150 sub-mersible temperature data logger is a battery-powered, standalone device that can record up to 32, 767 temperatures ranging from -40 to 150°C (-40 to 302°F). It's 51 mm (2") long rigid external probe lets the user take quick, acurate measurements.

The OM-CP-HITEMP-150 is ideal for harsh environments. Its real-time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.



OM-CP-IFC110, \$99, Windows software displays data in graphical or tabular format.

The OM-CP-HITEMP-150 can be started and stopped directly from your computer, and its small size allows it to fit almost anywhere. Data retrieval is simple. Plug it into an empty USB or COM port and the Windows software does the rest. The software converts a PC into a real-time strip chart recorder. Data can be printed in graphic or tabular format and can be exported to a text or

USA

Microsoft Excel file.

Specifications

Temperature Sensor: 100 Ω

Platinum RTD

Temperature Range: -40 to 150°C

(-40 to 302°F)

Temperature Resolution: 0.05°C Calibrated Accuracy: ±0.5°C Start/Time: Software programmable start time and date, up to 6 months in advance

Real-Time Recording: Device may be used with PC to monitor and record data in real time

Memory: 32,767 readings

Reading Interval: 1 reading every 2 seconds to 1 every 12 hours, selectable through software Calibration: Digital calibration is available through software Calibration Date: Automatically

recorded within device

Power: 3.9 V lithium battery (included)
Battery Life: 1 year typical
(1 minute reading rate @ 25°C)
Time Accuracy: ±1 minute per month at 20°C (RS-232 cable not in use)
Computer Interface: PC USB or serial

(interface cable required); 2400

Software:

WIN98/NT/2000/XP/VISTA 32-bit, (VISTA 32-bit version only; VISTA 64-bit is not supported)

OM-CP-HITEMP-150,

\$499, shown larger

than actual size.

Operating Environment:

-40 to 150°C (-40 to 302°F); 0 to 100% RH, non-condensing **Data Format:** Date and time stamped, °C, °F, K, °Ra **Weight:** 225 g (8 oz)

Computer Interface: PC serial,

RS-232C COM or USB **Dimensions (Body):** 28 H x 45 mm Dia. (1.1 x 1.75")

Dimensions (Probe):

51 L x 5 mm Dia.

(2.0 x ¾6")

Construction: 316 SS (food grade)

ALL MODELS AVAILABLE FOR FAST DELIVERY!

ALL MODELO ATAILADEL I ON I AUT DELITENTI		
To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-HITEMP-150	\$499	Extended-range submersible temperature data logger
OM-CP-HITEMP-150-CERT	559	Extended-range submersible temperature data logger with NIST calibration
OM-CP-IFC110	99	Windows software and 1.2 m (4') RS-232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT108	99	Replacement 3.9 V lithium battery

Operator's manual and USB cable are included with the **OM-CP-IFC200** Windows software (software is required to operate the data logger and is sold separately).

Ordering Example: OM-CP-HITEMP150-CERT, extended-range temperature data logger with NIST calibration certificate, OM-CP-IFC200, Windows software and USB cable, \$559 + 119 = \$678.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

www.omega.co.uk



UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY

www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622

www. omega.co.uk Manchester, England 0800-488-488 +44-(0)161-777-6611

FRANCE

www.omega.fr 0800-466-342

BENELUX

www.omega.nl 0800-099-33-44



Sales@omega.co.uk

More than 100,000 Products Available!

Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ehernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters