


OMB-PDQ30

Analog Input Expansion Module for OMB-DAQ-3000 Series and OMB-DAQBOARD-3000 Series



OMB-PDQ30, \$599, shown smaller than actual size

Thermocouple probes sold separately

JMQSS-125U-12, \$26.95

TMQSS-125U-12, \$26.95

KMQSS-125U-12, \$26.95

Starts at
\$599



- ✓ Adds 24 Differential/48 Single-Ended Inputs to OMB-DAQBOARD-3000 Series PCI Boards and OMB-DAQ-3000 Series Personal Daq USB Data Acquisition Modules
- ✓ Any Input Can be a Voltage or a Thermocouple
- ✓ Convenient Removable Screw-Terminal Connections

The OMB-PDQ30 analog input expansion module increases total channel capacity of an OMB-DAQBOARD-3000 Series PCI bus data acquisition board or OMB-DAQ-3000 Series Personal Daq USB data acquisition module to a total of 32 differential or 64 single-ended analog inputs.

The OMB-PDQ30 attaches to an OMB-DAQBOARD-3000 Series board via an optional OMB-CA-266-3 cable, and to the OMB-DAQ-3000 Series either by plugging directly into the Personal Daq module with included clips, or via an optional OMB-CA-96 cable if it is necessary to have some distance between devices. Voltage measurements via the OMB-PDQ30 have the same ranges as the host OMB-DAQBOARD-3000 Series PCI board or OMB-DAQ-3000 Series Personal Daq USB module.

When used with either host, the OMB-PDQ30 also adds thermocouple measurement capability, in which the A/D operates in a programmable, over-sample/digital filtering mode to provide low-noise and stable temperature measurements.



OMB-CA-266-3 cable, \$49, shown smaller than actual size

TC TYPES AND ACCURACY ¹

Thermocouple	Temperature Range °C	Accuracy (±°C)	Noise (±°C)
J	-200 to 760	1.1	0.2
K	-200 to 1200	1.2	0.2
T	-200 to 400	1.1	0.2
E	-270 to 650	1.0	0.2
R	-50 to 1768	2.5	0.2
S	-50 to 1768	2.6	0.2
B	50 to 1780	3.3	0.2
N	-270 to 1300	1.5	0.2

¹ Assumes 256 average mode applied, CMV = 0.0V, 30 minute warm-up and 25°C ambient temperature. Excludes thermocouple errors.

Voltage Range*	Accuracy ± (% of Reading + % Range) 23°C ± 10°C, 1 year	Temperature Coefficient ± (ppm of Reading + ppm Range) /°C 0 to 13°C and 33 to 60°C	Noise** (cts RMS)
10 V	0.031% + 0.008%	14 + 8	2
5 V	0.031% + 0.009%	14 + 9	2
2 V	0.031% + 0.010%	14 + 10	2
1 V	0.031% + 0.012%	14 + 12	3
500 mV	0.031% + 0.018%	14 + 18	5
200 mV	0.036% + 0.012%	14 + 12	9
100 mV	0.042% + 0.018%	14 + 18	17

* Specifications assume differential input single channel scan, 1-MHz scan rate, unfiltered, CMV = 0.0V, 30 minute warm-up.

** Noise reflects 10,000 samples at 1-MHz, typical, differential short.

Specifications

GENERAL

Operating Temperature:

-30 to 70°C (-22 to 158°F)

Storage Temperature:

-40 to 80°C (-40 to 176°F)

Warm-Up: 30 min to rated specifications

Relative Humidity:

0 to 95%, non-condensing

Vibration: MIL STD 810E, category 1 and 10

Communications

Connector: 25-pin DSUB

Signal I/O Connector:

6 removable screw-terminal blocks (12 connections each)

Dimensions:

269 W x 92 D x 45 mm H (10.6 x 3.6 x 1.6")

Weight: 400 g (0.88 lb)

Power: Supplied by

OMB-DAQBOARD-3000 Series PCI

board or OMB-DAQ-3000 Series

Personal Daq USB module;

400 mW max

ANALOG INPUTS

Channels: 48 single-ended inputs,

24 channels of differential inputs

Voltage Measurement Speed:

1 µs per channel

Temperature Measurement

Speed: Programmable from

100 µs to 20 ms per channel

Ranges: ±10 V, ±5 V,

±2 V, ±1 V, ±500 mV,

±200 mV, ±100 mV,

universal thermocouple

Total Harmonic

Distortion:

-80 dB typical for

±10 V range,

1 kHz fundamental

Signal to Noise

and Distortion:

72 dB typical for

±10 V range, 1 kHz

Fundamental

Input Impedance: 10 MΩ

(single-ended); 20 MΩ

(differential)

Bias Current:

40 pA typical (0 to 35°C)

Over-Voltage


Protection: ±30 V

Ranges: Software or sequencer

selectable on a per-channel basis

Crosstalk: -90 dB DC to 60 Hz; 86

dB @10 kHz, typical



OMB-DAQBOARD-3000, \$749, attached to an OMB-PDQ30 expansion module, \$599, via an OMB-CA-266-3 cable, \$49, all shown smaller than actual size

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-PDQ30	\$599	Analog input expansion module, adds 24DE/48SE channels to OMB-DAQ-3000 Series acquisition modules and OMB-DAQBOARD-3000 Series PCI bus data acquisition cards
OMB-CA-266-3	49	OMB-DAQBOARD-3000 Series to OMB-PDQ30 cable, 0.9 m (3')

Ordering Example: OMB-PDQ30 analog input expansion module and OMEGACARESM 1-year extended warranty (adds 1-year to standard 1-year warranty) for OMB-PDQ30, \$599 + 59 = \$658.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters