

30 KS/s 12-Bit Analog and Digital I/O Board for the ISA Bus OME-A-8111

\$249
Basic Unit



- 12-Bit A/D Converter
- 8 Single-Ended Input Channels
- 30 KS/s Sampling Rate
- One 12-Bit Analog Output Channel
- Software Programmable Gain: 1, 2, 4, 8, 16
- A/D Trigger Modes: Software Trigger, Pacer Trigger
- A/D Data Transfer Modes: Polling, Interrupt
- 16 Digital Inputs and 16 Digital Outputs



OME-A-8111 shown smaller than actual size

D/A OUTPUTS

Channels: 1 independent
Type: 12-bit double buffers
Linearity: 0.006% FS
Output Range: 0 to 5 V or 0 to 10 V
Internal Reference: +10 V or -10 V
Output Driving: ±5 mA
DIGITAL I/O
Input: 16 (LSTTL)
Input Low: VIL = 0.8 V max
 IIL = -0.4 mA max
Input High: VIH = 2.0 V min
 IIH = 20 µA max
Outputs: 16 channel TTL levels
Outputs Low: VOL = 0.5 V max
 IOL = 8 mA max

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners

Outputs High: VOH = 2.7 V min
 IOH = -400 µA max
General Environmental Power Requirements:
 +5V @ 200 mA (max)
Operating Temperature:
 0 to 50°C (32 to 122°F)
Storage Temperature:
 -20 to 70°C (-4 to 176°F)
Humidity: 0 to 90% RH non-condensing
Dimensions: 157 H x 106 mm W (6.18 x 4.17")

IN STOCK FOR FAST DELIVERY!

The OME-A-8111 is a 12-bit multi-function analog and digital I/O board for PC/AT compatible computers. The OME-A-8111 offers 8 analog input channels, plus one channel of analog output with 12-bit resolution. In addition, the OME-A-8111 has 16 digital inputs and 16 digital outputs. The OME-A-8111 provides gains of 1, 2, 4, 8, 16. It has a maximum sampling rate of 30 KS/s.

Software Development Kit

All boards are supplied with a standard software development kit for Windows 98/NT/2000/XP. The software development kit includes dll files for programming in C, C++ or other high level languages and OCX files for Visual Basic or Active X programming. LabView drivers are also included.

Specifications

Analog Input Channels:
 8 single-ended channels
Input Range: ±5 V, ±2.5 V, ±1.25 V, ±0.625 V, ±0.3125 V
Resolution: 12-bits
Conversion Rate: 30 KS/s
Input Impedance: 10 MΩ/6 pf
Overvoltage Protection: ±35 V
Linearity: ±1 bit
Sample & Hold: on chip
Zero Drift: ±25 ppm/°C of full scale

To Order (Specify Model Number)

Model Number	Price	Description
OME-A-8111	\$249	30 KS/s 12-bit multi-function board
OME-DB-37	69	Direct connect 37-pin screw terminal board for analog I/O
OME-DN-37	79	37-pin D-Sub DIN rail mount I/O connector board (two 37-pin D-Sub connectors, one for expansion) for analog inputs, includes one 1 m (3') cable
OME-DB-889D	359	16-channel analog input multiplexer board, includes 1 m (3') cable
OME-DB-16P	99	16-channel Isolated digital input board, includes 1 m (3') cable
OME-DB-16R	149	16-channel relay output board, includes 1 m (3') cable
OME-DB-24C	209	24-channel open-collector output board, includes 1 m (3') cable
OME-DB-24SSR	649	24-channel SSR output board

All boards include utility software and a complete user's manual on CD-ROM.
Ordering Example: OME-A-8111 12-bit multi-function board and OMEGACARESM 1 year extended warranty for OME-A-8111 (adds 1 year to standard 1 year warranty), \$249 + 25 = \$274.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters