#### **USB-4718** 8-Channel Thermocouple Input **USB Data Acquisition Module** USB-4718, £218,



- 1 YEAR
- ✓ Supports USB 2.0
- Portable
- Bus-Powered
- 8 Differential Analogue Input Channels
- ✓ 16-Bit Resolution
- ₩ 8 DI/8 DO
- Wiring Terminal on Modules
- ✓ Suitable for DIN-Rail Mounting
- Lockable USB Cable for Rigid Connection

The USB-4700 series consists of true Plug & Play data acquisition devices. No more opening up your computer chassis to install boardsjust plug in the module, then get the data. It's easy and efficient.

The USB-4718 offers 8 thermocouple inputs with 16-bit resolution, up to 0.1% input range accuracy, or 4 to 20 mA Inputs. Reliable and rugged enough for industrial applications, yet inexpensive enough for all types of projects, the USB-4718 is the perfect way to add measurement and control capability to any USB capable computer.

The USB-4718 is fully USB plug and play and easy to use. It obtains all required power from the USB port, so no external power connection is ever required.

Data collection is simple. Simply plug the data acquisition module into an available USB port and our easy-to-use Windows software does the rest. The software converts your PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format. It can also be exported to a text or Microsoft Excel file.



Windows software displays data in graphical or tabular format.

### Specifications

ANALOGUE INPUT Accuracy: ±0.1% for voltage input Bandwidth: 13.1 Hz @ 50 Hz, 15.72 Hz @ 60 Hz Channels: Eight differential Ch. Independent Conf: Yes CMR @ 50/60 Hz: 92 dB min Resolution: 16-bits Input Impedance: 20 MΩ Input Range: 0 to 15 mV, 0 to 50 mV, 0 to 100 mV, 0 to 500 mV, 0 to 1V, 0 to 2.5V, 0 to 20 mA, 4 to 20 mA Input Types: Thermocouple, mV, V, mA Sampling Rate: 10 samples/sec (total) Span Drift: ±25 ppm/°C TVS/ESD Protection: Built-in Zero Drift: ±3 µV/° C **ISOLATED DIGITAL INPUT** 

Channels: 8 Input Voltage:

Logic 0: 2V max Logic 1: 5V min (30 V max) Isolation Protection: 2500 Vdc Opto-Isolator Response: 25 µS

shown smaller than actual size.

DE OMEGA

**ISOLATED DIGITAL OUTPUT** Channels: 8 Output Type: Sink (NPN) Isolation Protection: 2500 Vdc Output Voltage: 5 to 30 Vdc, 1.1 Å max/total Sink Current: 200 mA max/channel **Opto-isolator Response:** 25 µS **GENERAL** Bus Type: USB 2.0 Software: Windows 2000/XP I/O Connector: Onboard screw terminal **Dimensions:** 80 H x 132 L x 32 mm D (3.1 x 5.2 x 1.3") **Power Consumption:** 100 mA @ 5V Power Input: 5V from USB line Watchdog Timer: 1.6 sec (system) **Operating Temperature:** 0 to 60°C (32 to 140°F) Storing Temperature: -20 to 70°C (-4 to 158°F) Storing Humidity: 5 to 95% RH non-condensing

4718

C

JSB-

NANANANAN

Thermocouple Ranges and Accuracy			
Thermocouple	Input Range	Typical Accuracy	Maximum Error
J	0 to 760°C (32 to 1400°F)	±1.0°C	±1.5°C
К	0 to 1370°C (32 to 2498°F)	±1.0°C	±1.5°C
Т	-100 to 400°C (-148 to 752°F)	±1.0°C	±1.5°C
Е	0 to 1000°C (32 to 1832°F)	±1.0°C	±1.5°C
R	500 to 1750°C (932 to 3182°F)	±1.2°C	±2.5°C
S	500 to 1750°C (932 to 3182°F)	±1.2°C	±2.5°C
В	500 to 1800°C (932 to 3272°F)	±2.0°C	±3.0°C

Note: Due to the location of the CJC sensor, the measurement will have a 1°C maximum difference in channels. AVAILABLE FOR FAST DELIVERY!

#### **To Order** (Specify Model Number) Model No. **Price Description USB-4718 £218** 8-channel thermocouple input USB module

Comes with Windows Software and complete user manual on CD, a 1.8 m (6') USB 2.0 cable, and DIN rail mounting kit. ordering Example: USB-4718, 8-channel thermocouple input USB module, and OMEGACARE<sup>™</sup> 1-year extended warranty for USB-4718 (adds 1 year to standard 1-year warranty), £218 + 21.50 = £239.50

## omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622

Fax +44(0) 161 777 6622

Sales@omega.co.uk

### www.omega.co.uk



**UNITED STATES** www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

**GERMANY** www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM www.omega.co.uk Manchester, England 0800-488-488

> FRANCE www.omega.fr 088-466-342

**CZECH REPUBLIC** www.omegaeng.cz Karviná, Czech Republic 596-311-899

> **BENELUX** www.omega.nl 0800-099-33-44



# More than 100,000 Products Available!

#### Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

#### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

#### pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

#### Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

#### Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters