



# TRANSIT TIME ULTRASONIC FLOWMETER

FDT-81

**\$6279**



FDT-81, \$6279, shown smaller than actual size.

*Comes with AC and automobile power adaptors, compartmentalized padded carrying case, coupling grease, standard sensors, straps, cables, mounting track, and complete operators manual.*



- ✓ **Automatic Reynolds Number Compensation**
- ✓ **24 Hour Integral Rechargeable Battery**
- ✓ **AC and Automobile Power Adaptors Included**
- ✓ **User-Configurable Rate and Totalizer Units**
- ✓ **Designed for Clean and Ultraclean Liquids**
- ✓ **Non-Invasive Clamp-on Transducers**

The FDT-80 Series of portable transit time flowmeters feature the world's most advanced non-invasive flow measurement technology, providing a measuring system with unsurpassed accuracy, versatility, ease of installation and dependability. Although designed primarily for cleaner liquids, the flowmeter can also reliably measure liquids containing moderate amounts of suspended solids or aeration.


FDT-80 is designed for long or short term flow measurement surveys on full-pipe liquid systems and is ideal for verifying calibration of permanently mounted flowmeters of all types. The flowmeter features a tactile keypad, 24-hour battery (rechargeable), and a 128 x 64 pixel, back-lit

graphics display—all integrated into a rugged, watertight enclosure. The FDT-80 systems utilize proprietary dual time-base time expansion algorithm, advanced DSP and digital cross-correlation. The cost effective and versatile FDT-80 flowmeter comes complete with all accessories necessary for measuring piping systems from 50 to 2540 mm (2 to 100").

FDT-80 Series has a flow measuring range that exceeds 4000:1. This feature allows the instrument to measure normal process flow rates as well as flows resulting from leaks in piping and valves.

User configurable rate and totalizer units include: feet, gallons, ft<sup>3</sup>, million-gal, barrels, acre-feet, lbs, meters, liters, m<sup>3</sup>, million-liters and kg. Non-invasive clamp-on transducers are simple and cost efficient to install. Since the transducers do not contact the liquid, fouling and maintenance are eliminated.

Automatic Reynolds Number compensation assures accurate measurements through the laminar, transition and turbulent system flow regions. An integral 24 hour rechargeable battery allows extended operation when AC power is not available. Both AC and cigarette socket style power adaptors (battery chargers) are included. Compartmentalized and padded carrying case keeps the FDT-80 meter and all of its accessories organized and protected.



FDT-81, \$6279, shown smaller than actual size.



## SPECIFICATIONS

### Transmitter

**Power Requirements:** Internal 12 V lead-acid gel cell battery provides 24 hrs of continuous operation @ 20°C (68°F)

**Charging:** Wall mount power converter, 115 or 230 Vac 50/60 Hz ±15% @ 5 VA max; 12 to 15 Vdc @ 2.5 VA max

**Velocity:** -12 to +12 MPS (-40 to +40 FPS)

**Outputs:** All output modules are optically isolated from earth and system grounds. A maximum of two modules may be installed

**Analog Output:** 4 to 20 mA, 800Ω max; 12-bit resolution; passive or active

**Other Options:** Pulse output MOSFET, dual form C relays, heat flow and high temperature, and small pipe sensors (consult Engineering for details)

**Display:** 128 x 64 pixel graphics LCD, LED back lit. Two user selectable font sizes: 8.9 or 5.0 mm (0.35 or 0.2") 8-digit rate, 8-digit totalizer (resettable)

**Units:** Feet, gallons, ft<sup>3</sup>, mil-gal, barrels, acre-feet, lbs., meters, liters, m<sup>3</sup>, mil-liters, kg (with Heatflow option: BTUs, calories, watts tons) [rate time: sec, min, hr, day]; Totalizer (NET, FWD, REV or BATCH): gallons, ft<sup>3</sup>, barrels, acre-feet, lbs., liters, m<sup>3</sup>, kg (with Heatflow option: BTUs, calories, watts tons) (user configured)

**Ambient Conditions:** -40 to 85°C (-40 to 185°F), 0 to 95% relative humidity, non-condensing

**Enclosure:** NEMA 4X (IP-66) while open, NEMA 6 (IP68) while closed, ABS with SS hardware

**Electronic Enclosure:** 14.8 lbs (6.7 kg), 356 W x 154 H x 268 mm D (14 x 6.06 x 10.56")

**Accuracy Flow Rate:** ±0.5% of reading at rates > 1 FPS

**Sensitivity Flow:** 0.0003 MPS (0.001 FPS)

**Repeatability:** ±0.01% of reading

**Response Time Flow:** 0.3 to 30 seconds, user configured, to 100% of value, step change in flow. Security keypad lockout, 4-digit user selected access code

**Approvals:** Ordinary area

**Cable:** 6.1 m (20')

**Pipe Sizes:** 50 to 2540 mm (2 to 100")

**Pipe Temperature:** -40 to 121°C (-40 to 250°F); NEMA 6 (IP68) housing

**Material Standard Sensor:** CPVC, Ultem® and Nylon

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
FDT-81	\$6279	Transit-time flowmeter

### Accessories

Model No.	Price	Description
FDT-81-STD	\$839	Replacement standard sensor
FDT-GREASE	28	Coupling grease for FDT-30/80 Series
FW-0107	78	Reference Book: Chemical Engineering Fluid Mechanics 2nd Edition

Comes complete with AC and automobile power adaptors, carrying case, coupling grease, standard sensors, straps, cables, mounting track, and operator's manual.

High temp and small pipe transducers are available as an accessory. Consult Flow Engineering for details.

**Ordering Example:** FDT-81, complete transit time ultrasonic flowmeter kit, and FDT-GREASE, coupling grease, \$6279 + 28 = \$6307.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters