

# EASY-VIEW FLOWMETERS

## With Optional Alarm Modules

**FL-93/96/  
97/98/9900**



- ✓ 1½ to 2" Ports
- ✓ No Special Piping or Flow Straighteners Needed
- ✓ Installs in Any Position
- ✓ Direct Reading Indication
- ✓ Accuracy Within ±5% Full Scale
- ✓ Relatively Insensitive to Shock and Vibration
- ✓ Optional Flow Switch Modules



FL-9302



FL-9902

Both models shown smaller than actual size.

The FL-9000 Series flowmeter are rugged, low-cost direct reading industrial class flowmeters that are simple to install. They can be mounted (installed) in any position from vertical to horizontal without costly flow straighteners or other special plumbing. Constructed of high impact polysulfone plastic, the product line offers excellent structural integrity and chemical compatibility with a wide range of industrial chemicals.


### FL-9000-ACL/DCL

The AC and DC powered flow switch modules consist of a latching relay circuit housed in a sealed polypropylene enclosure. The modules have a normally open dry relay contact that can be used to directly control alarms, warning lights, relays or be used to interface to a PLC. The relay will be latched on as the magnet inside the flow meter passes by the module, and remain latched on until the magnet passes in the other direction or power is interrupted. The set-point is adjustable from 0 to 100% of full scale.

### FL-9000-RA/RB/RC

The reed switch modules are housed in a sealed polypropylene enclosure. The reed switch module does not provide the latching function like the AC and DC powered units. When the magnet inside the flowmeter comes within

proximity of the module, the reed switch will change state. The set-point is adjustable from 0 to 100% full scale. Two reed switches providing low flow and high flow set points may be installed on a single flowmeter.



## SPECIFICATIONS

**Materials:** Polysulfone plastic body, piston and cone, T300 stainless spring, buna flow indicator ring and pressure seals, C360 brass or PVC fittings, polypropylene limit indicators

**Fittings/Threads:**

**NPT:** ANSI/ASME B1.20.1

**BSPP:** ISO228 (-BSP)

**Temperature Range:** 0 to 121°C (32 to 250°F)

**PVC Fittings:** 0 to 60°C (32 to 140°F)

**Pressure Rating:** 22.4 bar (325 psi) maximum

**Pressure Drop:** See differential pressure chart on right

**Accuracy:** ±5% of full scale

**Repeatability:** ±1%

**Standard Scaling:** 0.876 specific gravity for oil, 1.0 specific gravity for water

## Switch Specifications

**Power:**

**FL-9000-ACL:** 115 Vac ±10%

**FL-9000-DCL:** 10 to 30 Vdc

**FL-9000-ACL/DCL:** 25 mA maximum current

**Contacts:** 1A @30 Vdc, 0.5A @ 125 Vac (resistive load)

**FL-9000-RA:** 1 A, 200 Vdc maximum, 15 W (resistive load)

**FL-9000-RB/RC:** 0.25 A maximum, 175 Vdc, 5 W (resistive load)


**Temperature:**

**FL-9000-ACL/DCL:** 0 to 70°C

(32 to 158°F)

**FL-9000-RA/RB/RC:** 0 to 121°C

(32 to 250°F)



## To Order

Model No.	Description	Range GPM (LPM)	Weight kg (lb)
FL-9301	Oil flowmeter 1½ FNPT brass	2 to 25 (10 to 95)	1.86 (4.1)
FL-9302	Oil flowmeter 1½ FNPT brass	5 to 50 (20 to 190)	1.86 (4.1)
FL-9303	Oil flowmeter 1½ FNPT brass	7 to 75 (30 to 280)	1.86 (4.1)
FL-9304	Oil flowmeter 1½ FNPT brass	10 to 100 (40 to 380)	1.86 (4.1)
FL-9701	Oil flowmeter 2 FNPT brass	2 to 25 (10 to 95)	1.4 (3.1)
FL-9702	Oil flowmeter 2 FNPT brass	5 to 50 (20 to 190)	1.4 (3.1)
FL-9703	Oil flowmeter 2 FNPT brass	7 to 75 (30 to 280)	1.4 (3.1)
FL-9704	Oil flowmeter 2 FNPT brass	10 to 100 (40 to 380)	1.4 (3.1)
FL-9601	Water flowmeter 1½ FNPT brass	2 to 25 (10 to 95)	1.86 (4.1)
FL-9602	Water flowmeter 1½ FNPT brass	5 to 50 (20 to 190)	1.86 (4.1)
FL-9603	Water flowmeter 1½ FNPT brass	7 to 75 (30 to 280)	1.86 (4.1)
FL-9604	Water flowmeter 1½ FNPT brass	10 to 100 (40 to 380)	1.86 (4.1)
FL-9801	Water flowmeter 2 FNPT brass	2 to 25 (10 to 95)	1.4 (3.1)
FL-9802	Water flowmeter 2 FNPT brass	5 to 50 (20 to 190)	1.4 (3.1)
FL-9803	Water flowmeter 2 FNPT brass	7 to 75 (30 to 280)	1.4 (3.1)
FL-9804	Water flowmeter 2 FNPT brass	10 to 100 (40 to 380)	1.4 (3.1)
FL-9901	Water flowmeter 2 PVC socket	2 to 25 (10 to 95)	0.077 (1.7)
FL-9902	Water flowmeter 2 PVC socket	5 to 50 (20 to 190)	0.077 (1.7)
FL-9903	Water flowmeter 2 PVC socket	7 to 75 (30 to 280)	0.077 (1.7)
FL-9904	Water flowmeter 2 PVC socket	10 to 100 (40 to 380)	0.077 (1.7)

Comes complete with operator's manual.

For units with BSPP threads add “-BSP” to model number, no additional cost.

**Ordering Example:** FL-9302, oil flowmeter 1½ FNPT brass.

FL-9901, water flowmeter 2 PVC socket.

## Switches (Sold Separately)

Model No.	Description
FL-9000-ACL	115 Vac latching relay, with 4-pin connector, no CE, NEMA 12 and 13 (IP65)
FL-9000-DCL	10 to 30 Vdc latching relay, with 4-pin connector, CE, NEMA 12 and 13 (IP65)
FL-9000-RA	Form-A reed switch NO, with 0.92 m (3') long, 2-wire cable, CE, NEMA 12 and 13 (IP65)
FL-9000-RB	Form-B reed switch NC, with 0.92 m (3') long, 2-wire cable, CE, NEMA 12 and 13 (IP65)
FL-9000-RC	Form-C reed switch, with 0.92 m (3') long, 2-wire cable, CE, NEMA 12 and 13 (IP65)

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters