**ECONOMICAL IN-LINE FLOWMETERS** 

CAPACITIES: 0.05 to 2.0 GPM of Water, 0.05 to 2.0 GPM of Oil

> FL-2000A Starts at

**\$156** 









Optional <sup>1</sup>

- Mounts in Any Position
- Good Viscosity Stability
- Direct Readings for Oil or Water
- ✓ 241.3 bar (3500 psig) Pressure Rating
- Vertical Connectors for In-Line Mounting
- ✓ Temperature Rating: 116°C (240°F) Standard, 204°C (400°F) Optional
- For Clear and Opaque Fluids

The FL-2000A Series of general purpose flowmeters is designed to provide economical, accurate flow rate indication for oil and water. These industrial flowmeters utilize a spring-and-piston type assembly, which enables them to be mounted in any position and makes them immune to changes in viscosity. The FL-2000A meters can be used in severe environments, at up to 241.3 bar (3500 psig) and 116°C (240°F).

#### **SPECIFICATIONS**


Accuracy:  $\pm 2\%$  FS Repeatability:  $\pm 1\%$  Dimensions:  $48 \times 43$  mm (1.9 x 1.7") for 116°C (240°F) units Length: 121 mm (4.75") for 116°C (240°F) units; 168 mm (6.6") for 204°C (400°F) units

Maximum Pressure: 241.3 bar (3500 psig) Maximum Temperature: Standard:116°C (240°F)

**Optional:** 204°C (400°F) at 124 bar

(1800 psig) max Shipping Weight:

**Water Meters:** 453 g (1 lb) **Oil Meters:** 227 g (8 oz)



**Pressure Drop:** Approximate pressure losses in flowmeters using oil at normal temperatures. Add 10% to pressure for equal water flows.

Connections: ¼ FNPT Wetted Parts: Polyphenylene sulfide/ceramic magnet and FKM O-rings; FL-2100A has aluminum body and 302 SS spring; FL-2300ABR has brass body and 302 SS spring



For cutaway drawing of this unit, see page B-7. For correlation equations with other fluids, see page B-8.

MOST POPULAR MODELS HIGHLIGHTED!

## To Order (Specify Model Number)

10 Gluer (Checky model Maniber)			
Model No.	Price	Flow Range LPM (GPM)	Medium/Specific Gravity
FL-2100A*	\$156	0.2 to 2 (0.05 to 0.5)	Oil/0.876
FL-2101A	156	0.4 to 4 (0.10 to 1.0)	Oil/0.8760.2 to 2
FL-2102A	156	0.8 to 7.5 (0.20 to 2.0)	Oil/0.876
FL-2300ABR*	189	0.2 to 2 (0.05 to 0.5)	Water/1.0
FL-2301ABR	189	0.4 to 4 (0.10 to 1.0)	Water/1.0
FL-2302ABR	189	0.8 to 7.5 (0.20 to 2.0)	Water/1.0
CH-4617	42.50	Reference Book: Statistics for Petroleum	

Comes complete with operator's manual.

For 204°C (400°F) units, add suffix "-H" to model number and \$150 to price for oil units or \$181 to price for water units.

\* "-H" option not available with these units.

† For NIST certificate, add suffix "-NIST" to model number and \$275 to price.

Ordering Examples: FL-2301ABR, for a brass water flowmeter, 1.0 GPM, \$189.

FL-2102A, aluminum oil flowmeter, 2.0 GPM, \$156.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622

Fax +44(0) 161 777 6622

Sales@omega.co.uk

## www.omega.co.uk



#### **UNITED STATES** www.omega.com

1-800-TC-OMEGA Stamford, CT.

#### **CANADA**

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

#### **GERMANY**

www.omega.de Deckenpfronn, Germany 0800-8266342

#### UNITED KINGDOM

www. omega.co.uk Manchester, England 0800-488-488

#### **FRANCE**

www.omega.fr 088-466-342

#### **CZECH REPUBLIC**

www.omegaeng.cz Karviná, Czech Republic 596-311-899

#### **BENELUX**

www.omega.nl 0800-099-33-44



## More than 100,000 Products Available!

## Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

#### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

## pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

## Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters