# INTRODUCTION TO SCREW PLUG IMMERSION HEATERS



Screw plug immersion heaters consist of hairpin bent tubular elements brazed or welded into a screw plug and provided with wiring boxes for electrical connections. Screw plug immersion heaters are screwed directly through a threaded opening in a tank wall or through matching pipe coupling, half coupling or welding flange. Sizes of screw plug heaters are available with  $\frac{1}{2}$ ,  $\frac{3}{4}$ " 1", 1 $\frac{1}{4}$ ", 2" and 2 $\frac{1}{2}$ " pipe threads. A wide selection of screw plug sizes, kilowatt ratings, voltages, sheath materials, terminal housings, and thermostats makes these compact heaters ideal for all types of applications.

Screw plug immersion heaters are used for heating liquids and gases in a variety of processes. Those heaters are ideal for process water heating and freeze protection. All types of oils and heat transfer solutions can also be heated using these compact easily controlled units. The direct immersion method is energy efficient and well suited for many applications.

	Screw		Screw		
	Plug	Sheath	Plug	Heater	Integral
Application	Size	Material	Material	Type	Thermostat
Clean water	1"	Copper	Brass	ARTM	Ves
Clean water	1 11//"	Copper	Brass	MT	No
	2"	Copper	Brass		No
	2"	Copper	Brass		Vec
	2"	Copper	Brass	MT	No
	2"		Brass		No
	21//"	Copper	Brass		Vec
	21/2	Copper	Brace		No
Process water	∠/2 1"	copper	01035		Voc
FIOCESS Waler	2"	<u> </u>	<u> </u>	ARTIVIS	Voc
	2"	33	33	ARIVITS	No
	2	33	33		INO No
	<u>2</u> "	55	55		INO Maa
	21/2	33	33	AKIVIIS	res
Colution	<b>2</b> <sup>1</sup> /2 <sup>"</sup>	33	33		
Solution water	<u>2"</u>		33		Yes
	<u>2</u> "	incoloy	55		INO
	21/2"	Incoloy	SS	ARMII	Yes
	2½"	Incoloy	SS	MII	No
Light weight oil	1"	Steel	Steel	ARIMO	Yes
	1¼"	Steel	Steel	MIO	No
	2"	Steel	Steel	ARMIO	Yes
	2"	Steel	Steel	MTO	No
	21/2"	Steel	Steel	ARMTO	Yes
	<b>2</b> <sup>1</sup> /2"	Steel	Steel	MTO	No
Medium weight	2"	Steel	Steel	ARTMO	Yes
oil	2"	Steel	Steel	MTO	No
	<b>2</b> <sup>1</sup> /2"	Steel	Steel	ARTMO	Yes
	2½"	Steel	Steel	MTO	Yes
Heavy weight	2"	Steel	Steel	ARTMO	Yes
oil	2"	Steel	Steel	MTO	No
	2½"	Steel	Steel	ARTMO	Yes
	2½"	Steel	Steel	MTO	No
Specialty	1/2"	Incoloy	Steel	RI	No
Heaters-water,	1/2"	SS	Steel	RIO	No
oil & corrosion	1/2"	Incoloy	Brass	RIN	No
fluids	1/2"	SS	Brass	RINO	No
	1/2"	SS	SS	RIS	No
	1/2"	Hasteloy	Hasteloy	RIH	No
	3/4"	Incoloy	Steel	RI	No
	3/4"	SS	Steel	RIO	No
	3/4"	Incolov	Brass	RIN	No
	3/4"	SS	Brass	RINO	No
	1"	Copper	Brass	TMW	No
	1"	SS	SS	TMWS	No
	1"	Steel	Steel	ТМО	No
	1"		Brass	CJ	Yes
	11/4"	Copper	Brass	TMW	No
	2"	Incolov	Brass	DWH	Yes
	-	1 110010 y	2.000		100

SS denotes Stainless Steel

#### **PRODUCT DESCRIPTION**

OMEGALUX® heavy duty tubular elements are welded or brazed to a screw plug. Uniform heat distribution and repressed element bends provide long element life.For heaters with built-in thermostats, a thermowell (hollow tube sealed at one end) is welded or brazed to the screw plug and allows thermostat sensing element replacement without draining the tank.

Screw plug heaters are equipped with a steel enclosure, and are also available with a combination moisture resistant/explosion resistant enclosure.

Screw plug type heaters are screwed directly through a threaded opening in tank wall. Heavy tank walls may be drilled and tapped if thickness is sufficient to engage ¾ of threads. Lighter tank walls should be equipped with suitable pipe halfcoupling attached with proper braze or weld material.



CONSTRUCTION FEATURES

**Material** — copper, steel, Incoloy and stainless steel.

Number of elements in screw plugs — one, two or three depending on screw plug size.

Element diameters — 0.315", 0.375", and 0.475".

Watt densities — 6.5, 15, 23, 45 and 75 watts per square inch typical.

SCREW PLUG

**Material** — carbon steel, brass and stainless steel.

Sizes —  $\frac{1}{2}$ ",  $\frac{3}{4}$ ", 1", 1 $\frac{1}{4}$ ", 2", 2 $\frac{1}{2}$ ", nominal.

#### **TERMINAL ENCLOSURES**

**General Purpose** sheet metal, painted with red enamel.

**Type E-2** Combination moisture resistant/explosion resistant.

Type E-2 explosion resistant enclosure involve the use of a wiring enclosure for use Class I Groups C & D, Division 1 & 2. Class II, Groups E, F & G, Division 1 & 2. Class III, Division 1 & 2. Not intended for use in hazardous areas.

Safe operation of heaters equipped with these enclosures depends upon employment of electrical wiring meeting National Electric Code for hazardous locations and limiting maximum operating temperatures (including temperature on outside of vessel, piping, flanges, screw plugs, enclosures and other heat conducting parts) as directed by flammable liquids, vapors or gases present. Approved pressure and /or temperature limiting controls must be used to assure safe operation in the event of system malfunctions.

#### **TEMPERATURE CONTROL**

Many screw plug type heaters are available with built-in thermostatic controls. In some installations, where there is more than one heater in a tank, you may consider one heater with a built-in control that will control the other heaters by wiring thermostat into the holding coil circuit of a magnetic contactor. If the thermostat is separate from the heater, the thermostat sensing element should be located approximately 4 to 6 inches above the heater.

#### ARTM, ATMO AND ARTMS SERIES

The ARTM, ARTMO and ATTMS automatic thermostat has a temperature range range of 60°-180°F. Also available with alternate

60°F to 240°F thermostat (TH) and 0° to 127°F(TL). the temperature adjustment screw and scale are inside requiring the removal of cover to change temperature setting.

## ARTM, ATMTI ARTMS AND

**ARMTO SERIES** The integral thermostat is available with temperature ranges at 60° to 250°F or 0° to 100°f for ARMT, ARMTI and **ARMTS heaters. ARMTO heaters** are available with three different temperature ranges: 200° to 550°F, 60° to 250°F and 0° to 100°F. This control is wired in as a line thermostat for loads up to 4.2 kW on 240 volts. For high wattage rating, 3 phase operation and 480 Volts, this control is for pilot duty only and should be wired to operate the holding coil of a magnetic contactor by customer.

**Note:** The integral thermostat functions as a temperature control only. this is not a fail safe device so an approved pressure and/or temperature limit control should be used with these heaters to assure safe operation.

**Caution:** Explosion resistant Type E-2 construction refers to heater design features which provide explosion resisting containment of electrical wiring according to National Electric Code. abnormal application or use of heaters which results in excessive temperature can crete hazardous conditions which can lead to fire.

#### **Corrosion Policy**

OMEGALUX cannot warrant any electric immersion heater against failure is the result of operating conditions beyond the control of the heater manufactures. It is the responsibility of the purchaser to make the ultimate choice of sheath material based on his knowledge of the chemical composition of the corrosive solution, character of materials entering the solution, and controls which he maintains on the process.

# SCREW PLUG IMMERSION HEATER FOR PROCESS WATER

1", 2", 2½" Stainless Steel Screwplug
Stainless Steel Sheath
0.75 to 18 kW
With or Without Thermostat

## **APPLICATIONS**

For process water pH 5-9 — Use with industrial or municipal water with mild or alkaline conditions, which require heater sheath more resistant to corrosive influences or where a pH factor range of pH 5 to 9 exits.

For very weak 2-3% corrosive solutions — For very weak solutions with alkaline or acid content of up to 3% by volume, such as soap and detergent solutions, soluble cutting oils and rinsing applications where carryover from prior chemical processes causes solution contamination buildup.

For temperature ranges to 180°F — Dependable operation at those temperatures normal to the plating or other chemical treating or severe process cleaning applications.

For industrial tanks, vessels, & process piping — Or any application where a screw plug heater can be used or is necessary for a physical connection to an industrial process.

### **FEATURES**

**Rugged construction** — Sturdy elements welded to stainless steel screwplugs provide superior rigidity and strength. Heavy duty jumper straps and terminal posts assure permanent tightness of connection's carrying capacity.

Long life metal sheath — High grade 300 Series stainless steel outer sheath provides the benefits of strength and durability in those applications where stainless performance is required.

### High conductivity elements -

Filled with highest purity blends of magnesium oxide refractory (MgO) compacted to a rock hard density to insure maximum electrical resistance, and assure long life.

Heavy coil construction — Watt density on the heating coil is designed for low watt density operation by increasing the coil diameter and length to give maximum coil surface area and limit coil surface temperature, providing longer coil life.

#### Liberal electrical clearances —

are provided in all terminal enclosures in accordance with the NEC insuring that proper arcing and creepage clearances are maintained. Termination insulators provide electrical isolation between terminations and grounded metal sheaths — all to insure personnel safety and equipment service life.

Easy access to terminal wiring — Superior performances at element bends — with all bent elements repressed in hydraulic presses after bending to assure recompaction of refractory material to eliminate hot spots and electrical insulation voids.

**Grounding connector standard** — A solid terminal connector is standard on all OMEGALUX<sup>®</sup> immersion heaters insuring positive ground and personal safety.

**Precise temperature** — Standard heaters provided with built-in temperature controls. for those units not provided with controls, see OMEGA<sup>®</sup> controllers. Standard temperature ranges are:

Туре	Temp. Range ° F	Туре	Temp. Range ° F	
1" NPT Scr	ew Plug		2 & 2½" NPT Screw Plug	
TL	0-127	T1	0-100	
тн	60-240	T2	60-250	
Standard	60-180	Т3	200-550	

**Note:** The integral thermostat functions as a temperature control only. This is not a fail-safe device so an approved pressure and/or temperature limit control should be used with these heaters to assure safe operation.

To set the control temperature of heaters equipped with the standard general purpose enclosure, adjust the knob on the outside of the terminal enclosure. For those heaters equipped with E-2 enclosures, (explosion resistant/moisture tight)\* remove the terminal enclosure lid to expose the temperature adjusting knob. For safety reasons, power to heater and pilot duty power must be turned off before removing enclosure lid.

This control is wired in as a line thermostat for loads up to 4.2 kW on 120 Volts and up to 6 kW on 240 Volts. For high wattage rating, 3 phase operation and 480 Volts, this control is for pilot duty only and should be wired to operate the holding coil of a magnetic contractor by customer.

### **Terminal Enclosures**

Specify type enclosure required when ordering.

**General purpose --** Sheet metal, NEMA 1.

**E-2** -- Combination moisture tight explosion resistant\*

**Caution:** Explosion resistant type E-2 construction refers to heater design features which provide explosion resisting containment of electrical wiring according to National Electric Code. Abnormal application or use of heaters which results in excessive temperatures can create hazardous conditions which can lead to fire.

\*Not intended for use in hazardous areas.

# SCREW PLUG IMMERSION HEATER FOR SOLUTION WATER

2", 2½" Stainless Steel
Incoloy Sheath
2 to 18 kW
With or Without Thermostat

### **APPLICATIONS**

For severe hard water pH5 to 9 — For use with industrial severe hard water containing minerals, scale and salts or with acid or alkaline conditions where the highest quality, high nickel bearing Incoloy sheath or more durability than copper or stainless is required.

For weak 5 to 6% corrosive solution — For weak and reclaimed water solutions with an alkaline or acid contents up to 6% by volume; or solutions with high mineral content containing heavy detergents; soluble cutting oils or caustic cleaning applications.

## For temperature ranges at 180°F

— This type Screw Plug Immersion Heater will provide dependable operation at the normal temperatures commonly encountered in the plating, chemical treating, or severe process cleaning applications.

For industrial tanks, vessels, & process piping — Or any applications where a screw plug heater can be used or is necessary for a physical connection to an industrial process.

### **FEATURES**

**Rugged construction** — Sturdy 0.475" diameter elements welded to stainless steel screw plugs provide superior rigidity and strength. Heavy duty jumper straps and terminal posts assure permanent tightness of connection's carrying capacity.

Long life metal sheath — Superior grade Incoloy outer sheath provides the highest practical protection available against most corrosive chemical solutions. It resists stress corrosion, cracking, sulfur attack, scaling, oxidation, and carburization at elevated temperatures.

#### High conductivity elements -

Filled with highest purity blend of magnesium oxide refractory (MgO) compacted to a rock hard density to insure maximum thermal conductivity, maximum electrical resistance, and assure long element life.

Heavy coil construction — Watt density on the heating coil is designated for low watt density operation by increasing the coil diameter and length to give maximum coil surface area and limit coil surface temperature, providing longer coil life.

#### Liberal electrical clearances —

are provided in all terminal enclosures in accordance with the NEC insuring that proper arcing and creepage clearances are maintained. Termination insulators provide electrical isolation between terminations and grounded metal sheaths — all to insure personnel safety and equipment service life.

Superior performance at element bends — with all bent elements repressed in hydraulic presses after bending to assure recompaction of refractory material to eliminate hot spots and electrical insulation voids.

Easy access to terminal wiring with a large terminal enclosure providing ample wiring and termination space insuring cool terminations and making installation easy.

**Precise Temperature Control** — Standard heaters provided with built-in temperature controls. For those units not provided with control, see section P of catalog. Standard temperature ranges are:

2 and 2½" NPT	Temp.
Screw Plug Type	Range°F
T1	0-100
T2	60-250

**Note:** The integral thermostat functions as a temperature control only. This is not a fail-safe device so an approved pressure and/or temperature limit control should be used with these heaters to assure safe operation.

To set the control temperature of heaters equipped with the standard general purpose enclosure adjust the knob on the outside of the terminal enclosure. For those heaters equipped with an E-2 enclosure (explosion resistant/ moisture resistant)\* remove the terminal enclosure lid to expose the temperature adjusting knob. For safety reasons, power to heater and pilot duty power must be turned off before removing enclosure lid.

This control is wired in a line thermostat for loads up up to 4.2 kW on 120 Volts and up to 6 kW on 240 Volts. For high wattage ratings and 480 Volts, this control is for pilot duty only and should be wired to operate the holding coil of a magnetic contactor by customer.

**Terminal enclosures** Specify type enclosure required when ordering.

**E1:** General purpose, sheet metal NEMA 1.

**E2:** Combination moisture resistant/ explosion resistant.\*

\* **Caution:** Explosion resistant type E-2 construction refers to heater design features which provide explosion resisting containment of electrical wiring according to National Electrical Code. Abnormal application or use of heaters which results in excessive temperatures can create hazardous conditions which can lead to fire. \* *Not intended for use in hazardous areas.* 

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622

Fax +44(0) 161 777 6622

Sales@omega.co.uk

# www.omega.co.uk



**UNITED STATES** www.omega.com 1-800-TC-OMEGA Stamford, CT.

**CANADA** www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM www.omega.co.uk Manchester, England 0800-488-488

> FRANCE www.omega.fr 088-466-342

**CZECH REPUBLIC** www.omegaeng.cz Karviná, Czech Republic 596-311-899

> BENELUX www.omega.nl 0800-099-33-44



# More than 100,000 Products Available!

## Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

## Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

## pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

## Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

## Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

## Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters