

TUBULAR HEATERS


1.2 cm (0.475") DIAMETER ROUND CROSS-SECTION

TRID-4065/240V,
\$109, shown smaller
than actual size.



TRID and TRIW Series
Starts at

\$84



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Watts	Volts	W/in ²	Dimensions: cm (in)		INCOLOY Sheath		Weight Lb (kg)
			Sheath A	Heated B	Model No.	Price	
TRID — 22 W/in²							
1000	240	22	102 (40)	71 (28 ¹ / ₂)	TRID-4065/240V	\$109	1.3 (0.6)
1000	480	22	102 (40)	71 (28 ¹ / ₂)	TRID-4065/480V	109	1.3 (0.6)
1250	240	22	111 (43 ³ / ₁₆)	80 (31 ¹ / ₁₆)	TRID-4365/240V	113	1.5 (0.7)
1250	480	22	111 (43 ³ / ₁₆)	80 (31 ¹ / ₁₆)	TRID-4365/480V	113	1.5 (0.7)
1500	240	22	138 (54 ¹ / ₄)	108 (42 ³ / ₈)	TRID-5465/240V	134	1.8 (0.8)
1500	480	22	138 (54 ¹ / ₄)	108 (42 ³ / ₈)	TRID-5465/480V	134	1.8 (0.8)
2000	240	22	178 (70)	148 (58 ¹ / ₂)	TRID-7065/240V	160	1.8 (0.8)
2000	480	22	178 (70)	148 (58 ¹ / ₂)	TRID-7065/480V	160	1.8 (0.8)
2500	240	22	216 (85)	186 (73 ³ / ₈)	TRID-8565/240V	185	2.3 (1)
2500	480	22	216 (85)	186 (73 ³ / ₈)	TRID-8565/480V	185	2.3 (1)
3000	240	22	254 (100)	224 (88 ¹ / ₂)	TRID-10065/240V	275	3.3 (1.5)
3000	480	22	254 (100)	224 (88 ¹ / ₂)	TRID-10065/480V	275	3.3 (1.5)
3334	240	22	274 (108)	244 (96 ¹ / ₄)	TRID-10865/240V	285	3.3 (1.5)
4167	240	22	340 (134)	310 (122 ¹ / ₂)	TRID-13465/240V	330	4.3 (2)
5000	240	22	406 (160)	376 (148 ¹ / ₂)	TRID-16065/240V	370	6 (2.7)
TRID — 19 W/in²							
1667	240	19	178 (70)	138 (54 ³ / ₈)	TRID-7085/240V	\$160	1.8 (0.8)
2225	240	19	233 (91 ³ / ₈)	193 (76)	TRID-9285/240V	260	2.3 (1)
2778	240	19	274 (108)	235 (92 ³ / ₈)	TRID-10885/240V	285	3.3 (1.5)
TRIW — 40 W/in²							
1000	120	40	51 (20)	33 (13 ¹ / ₂)	TRIW-2045/120V	\$84	0.5 (0.2)
1000	240	40	51 (20)	33 (13 ¹ / ₂)	TRIW-2045/240V	84	0.5 (0.2)
1250	120	40	58 (23)	41 (16 ¹ / ₂)	TRIW-2345/120V	88	0.5 (0.2)
1250	240	40	58 (23)	41 (16 ¹ / ₂)	TRIW-2345/240V	88	0.5 (0.2)
1500	120	40	71 (28)	56 (21 ¹ / ₂)	TRIW-2845/120V	94	1 (0.5)
1500	240	40	71 (28)	56 (21 ¹ / ₂)	TRIW-2845/240V	94	1 (0.5)
1500	480	40	71 (28)	56 (21 ¹ / ₂)	TRIW-2845/480V	94	1 (0.5)
2000	240	40	102 (40)	71 (28)	TRIW-4065/240V	109	1.3 (0.6)
2000	480	40	102 (40)	71 (28)	TRIW-4065/480V	109	1.3 (0.6)
2500	240	40	110 (43 ¹ / ₂)	80 (31 ¹ / ₂)	TRIW-4365/240V	113	1.3 (0.6)
2500	480	40	110 (43 ¹ / ₂)	80 (31 ¹ / ₂)	TRIW-4365/480V	113	1.3 (0.6)
3000	240	40	138 (54 ¹ / ₄)	108 (42 ³ / ₈)	TRIW-5465/240V	134	1.8 (0.8)
3000	480	40	138 (54 ¹ / ₄)	108 (42 ³ / ₈)	TRIW-5465/480V	134	1.8 (0.8)
3500	240	40	152 (60)	122 (48)	TRIW-6065/240V	144	1.8 (0.8)
4000	240	40	178 (70)	147 (58)	TRIW-7065/240V	160	1.8 (0.8)
4000	480	40	178 (70)	147 (58)	TRIW-7065/480V	160	1.8 (0.8)
5000	240	40	216 (85)	185 (73)	TRIW-8565/240V	185	2.3 (1)
5000	480	40	216 (85)	185 (73)	TRIW-8565/480V	185	2.3 (1)
6000	240	40	254 (100)	224 (88)	TRIW-10065/240V	275	3.3 (1.5)
6000	480	40	254 (100)	224 (88)	TRIW-10065/480V	275	3.3 (1.5)
7500	240	40	284 (112)	254 (100)	TRIW-11265/240V	295	3.3 (1.5)

Ordering Examples: TRID-16065/240V, 5000 Watt, 240V heater, \$370.
TRIW-2045/120V, 1000 Watt, 120V heater, \$84.

- ✓ Incoloy® Sheath
- ✓ 1000 to 7500 Watts
- ✓ 120, 240 and 480V
- ✓ 19 and 22 W/in² (Type TRID)
- ✓ 40 W/in² (Type TRIW)
- ✓ 871°C (1600°F) Max Sheath Temperature

APPLICATIONS

Versatile tubular elements can be designed for use in most applications. See guidelines in the Tubular Heater Overview section at omega.com/heaters

ADVANTAGES

The metal sheath isolates and protects the resistor wire from the environment. At the same time it maximizes heat transfer capability to the work. Tubular elements can be bent to put the heat where it works best.

FEATURES

Type 4 Terminals: Standard. Integral parts of the element are of high strength to resist bending during tightening of the wiring connections. Type 4 is threaded extension of the cold pin. See terminal detail drawing in the Tubular Heater Overview section at omega.com/heaters

Work Temperatures: See Tubular Heater Overview section at omega.com/heaters

Bending: Customer's minimum inside bending radius is 3.8 cm (1¹/₂"). See bending requirements in the Tubular Heater Overview section at omega.com/heaters

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters