# HIGH-PERFORMANCE INDICATOR FOR USE WITH AC-OUTPUT LVDT



- 3 V or 5 Vrms Excitation
- Standard Dual Relays, Analogue Output, and RS232 Serial Output
- Large, 5-Digit Scalable Display
- Maximum, Minimum, and Averaging Functions
- ✓ 2, 4, or 10 Readings per Second Update
- Can be Powered by 90 to 265 Vac
- High-Speed Analogue Output

The DPL53 is a high-performance, high-accuracy, single-channel transducer-conditioning device with a microprocessor-controlled, 5-digit scalable display. Five front-panel pushbuttons allow for simple calibration. All calibration values are stored in non-volatile memory to minimise setup procedures after a power failure. The meter has 2 alarm relays, which can be used for control, voltage and current analogue output for signal retransmission, and RS232 serial output for use with a computer or printer. The 14.7 mm (0.58")

high LED digits are easy to read. Industrial users will find the DPL53 invaluable in automatic processing and testing, which requires a direct readout down to 1/10,000 mm or inch.

#### SPECIFICATIONS

Accuracy:  $\pm 0.2\%$  FS  $\pm 1$  count Input Ranges: 0.05 to 5 Vrms Resolution: 18-bit Input Resistance: >100 k $\Omega$ Excitation: Sine wave 3 or 5 Vrms @ 5.0 or 2.5 kHz, selectable Display Type: Green LED, 14.7 mm (0.58") high digits

Display Digits: 5<sup>1</sup>/<sub>2</sub> digit (±19999) Setpoints: Front-panel programming with high/low and hysteresis selectability RS232 Output: ACSII characters, bidirectional, 300 to 9600 baud rate

Analogue Output: 0 to 10 V @10 mA, 0 to 20 mA or 4 to 20 mA @ 12 Vdc **Operating Temperature:** 0 to 50°C (32 to 122°F) Storage Temperature: -10 to 70°C (14 to 158°F) Span Temperature Coefficient: ±50 ppm/°Ċ Warm-Up Time: 1 hour **Input Connection:** Screw terminal **Power Requirement:** Between 90 and 265 Vac @ 50 to 60 Hz Power Consumption: 120 VA max Dimensions: 48 H x 93 W x 173 mm D (1.89 x 3.66 x 6.8") Panel Cutout: 44.5 H x 93 mm W (1.75 x 3.66") Weight: 0.4 kg (0.88 lb)

# **MOST POPULAR MODELS HIGHLIGHTED! To Order (Specify Model Number)**MODEL NO. PRICE COMPATIBLE TRANSDUCERS

MODEL NO.	PRICE	COMPATIBLE TRANSDUCERS
DPL53	£535	LD200, LD300, LD310, LD320

Comes with complete operator's manual.

Ordering Example: DPL53, LVDT indicator, £535.

#### ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ES-2062	£56	Reference Book: Hazardous Gases and Fumes

### omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622

Fax +44(0) 161 777 6622

Sales@omega.co.uk

### www.omega.co.uk



**UNITED STATES** www.omega.com 1-800-TC-OMEGA Stamford, CT.

**CANADA** www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

**GERMANY** www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM www.omega.co.uk Manchester, England 0800-488-488

> FRANCE www.omega.fr 088-466-342

**CZECH REPUBLIC** www.omegaeng.cz Karviná, Czech Republic 596-311-899

> BENELUX www.omega.nl 0800-099-33-44



## More than 100,000 Products Available!

### Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters