DYNAMIC PRESSURE TRANSDUCERS HIGH FREQUENCY, ACCELERATION COMPENSATED

DPX101 Series 0-250 to 0-5000 psi



- Ideal for Monitoring **Explosion or Pulsation Pressures**
- ✓ 1 µs Rise Time
- Welded Flush Diaphragm
- Pressure Ranges Up to 5000 psi
- High-Level 5 V Output
- Calibration Certificate Supplied

OMEGA's DPX101 dynamic pressure transducers are ideal for measuring pressure transients or dynamic pressure pulsations in liquids or gases. With their wide dynamic range, they can measure pressure events with rise times as fast as 1 µs. frequencies to hundreds of kHz, and pressure levels down to fractions of a psi. Using pure synthetic quartz crystals under high compressive preload, these transducers produce a clean, low-impedance voltage signal compatible with many readout instruments.

SPECIFICATIONS

Excitation: 2 mA nominal @ 18 to 30 Vdc, constant current Rated Output: 5 V nominal FS

Rise Time: 1.0 μs

Resonant Frequency: 500 kHz High Frequency Range: 170 kHz (approx. ½ of resonant frequency) Low Frequency Range (-3 dB): 0.08 Hz (101-250), 0.03 Hz (101-500), 0.02 Hz (101-1K), 0.003 Hz (101-5K)

Acceleration Sensitivity: 0.002 psig

Discharge Time Constant:

2 s (DPX101-250) 5 s (DPX101-500)

10 s (DPX101-1K) 50 s (DPX101-5K)

Proof Pressure:

5000 psi (DPX101-250) 10,000 psi (DPX101-500) 10,000 psi (DPX101-1K)

15,000 psi (DPX101-5K)

NIST 1 YEAR



books1.com

Overload Recovery: 10 µs for 2x range Maximum Shock: ±10,000 g peak Maximum Vibration: ±5000 a

Amplitude Linearity: ±1% FS (BSFL/0)

Temperature Range:

-100 to 250°F (-75 to 120°C) **Temperature Sensitivity Effect:**

0.03% FS/°F

Output Impedance: 100 Ω Bias Voltage: 10 V nominal Noise Floor (Wideband, RMS): 0.004 psi (DPX101-250)


0.007 psi (DPX101-500) 0.014 psi (DPX101-1K) 0.07 psi (DPX101-5K)

Weight: 14 g (0.5 oz) nominal Material: 316L SS diaphragm, 17-4 SS housing

Connector: 10-32 male termination (cable not included; order Model

No. ACC-CB2-10)





MOST POPULAR MODELS HIGHLIGHTED!

To Order <i>(Specify Model Number)</i>		
MODEL NO.	PRICE	RANGE (psig)
DPX101-250	\$495	0 to 250
DPX101-500	495	0 to 500
DPX101-1K	495	0 to 1000
DPX101-5K	495	0 to 5000
ACC-CB2-10	55	3 m (10') coaxial cable (10-32/BNCM) required

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
DPX-NPT	\$65	% NPT flush mount adaptor
DPX-3824	70	%-24 flush mount adaptor
DPX-6600	2	Replacement brass seals
POWER SUPPLIES		
ACC-PS1	\$205	Battery power supply (BNCF connections)
ACC-PS2	530	Battery power supply/amplifier (BNCF connections)
ACC-PS3	475	AC power supply (BNCF connections)
CABLES		
ACC-CB4-15	\$65	4.6 m (15') coaxial cable (BNCM/BNCM)
ACC-CB5-2	25	0.6 m (2') coaxial cable (BNCM/banana plug)
ACC-CB6	15	178 mm (7") coaxial cable (BNCM/pigtail)
ME-1740	160	Reference Book: Diesel Engine Engineering

Notes: Each unit comes with 2 DPX-6600 seals.

See pages K-20 through K-22 for details on the above power supplies and cables.

Ordering Example: DPX101-250, 0 to 250 psig transducer, DPX-NPT, 3.2 mm (½") flush mount adaptor, ACC-CB2-10, 3 m (10") coaxial cable, ACC-PS1, power supply, ACC-CB5-2, banana plug cable, \$495 + 65 + 55 + 205 + 25 = \$845.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

www.omega.co.uk



UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY

www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622

www. omega.co.uk Manchester, England 0800-488-488 +44-(0)161-777-6611

FRANCE

www.omega.fr 0800-466-342

BENELUX

www.omega.nl 0800-099-33-44



Sales@omega.co.uk

More than 100,000 Products Available!

Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ehernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters