# VERY LOW DIFFERENTIAL PRESSURE FOR AIR OR NON-CONDUCTING GAS

PX2670-1DI

4-20 mA Output



PX2670 Series

0-0.1 to ±5 inH20 4-20 mA Output





- ✓ 4-20 mA Output Is Compatible with Most 2-Wire Control Systems
- ✓ Optional 3½-Digit LCD Dispplay
- ✓ IP65/NEMA-4 Enclosure
- ✓ 11-Point Calibration Certificate Standard

#### **SPECIFICATIONS**

Excitation: 24 Vdc nominal

**Max:**  $30.0 + (0.004 \text{ x Loop Resistance } \Omega) \text{ Vdc}$ Min:  $14.0 + (0.02 \text{ x Loop Resistance } \Omega) \text{ Vdc}$ 

**Loop Resistance:** 0 to 800  $\Omega$ Output: 4-20 mA (2-wire) with internal

zero and span adjustments Accuracy: ±0.4% FS at constant

temperature (includes linearity, repeatability, and hysteresis) Linearity: ±0.33% FS

Hysteresis: 0.020% FS Repeatability: 0.10% FS Output Impedance:  $<100 \Omega$ **Operable Temperature Range:** 

0 to 150°F (-18 to 65°C)

**Compensated Temperature Range:** 

40 to 150°F (5 to 65°C)

Thermal Span Effect: ±0.033%FS/°F

Sensor: Capacitance **Position Effects:** 

Range Zero Offset (%FS/G) 0-10 inH2O .03

0-1 inH<sub>2</sub>O 0-0.1 inH2O 4

Maximum Line Pressure: 10 psi

Overpressure:

Negative Direction: 10 psi Positive Direction: 10 psi

Wetted Parts: Air and non-conductive gas


Pressure Port: 36" OD tube fitting

for 1/4" push-on tube **Electrical Connection:** 

Internal Terminal Strip with Strain Relief

Weight: 11 oz (310 g)

OMEGA's PX2670 Series pressure transducers sense either differential or gage pressure and convert this pressure to a highly accurate electrical signal. Used in building energy management systems, these transducers are capable of measuring pressures and flows with a high degree of accuracy to improve overall system efficiency. The units are temperature compensated to better than 0.33% FS/°F over the range of 40 to 150°F and have an IP65/NEMA-4 rated package to withstand environmental effects. A 3½-digit LCD display is optional.



To Order <i>(Specify Model Number)</i>			
RANGE (inH <sub>2</sub> O)	MODEL NO.	PRICE	COMPATIBLE METERS
0 to 0.1	PX2670-0.1DI	\$320	DP41-E, DP25-E, DP-24-E
0 to 0.25	PX2670-0.25DI	320	DP41-E, DP25-E, DP-24-E
0 to 0.5	PX2670-0.5DI	320	DP41-E, DP25-E, DP-24-E
0 to 1	PX2670-1DI	320	DP41-E, DP25-E, DP-24-E
0 to 2.5	PX2670-2.5DI	320	DP41-E, DP25-E, DP-24-E
0 to 5	PX2670-5DI	320	DP41-E, DP25-E, DP-24-E
0 to 10	PX2670-10DI	320	DP41-E, DP25-E, DP-24-E
0 to 25	PX2670-25DI	320	DP41-E, DP25-E, DP-24-E
±0.1	PX2670-0.1BDI	320	DP41-E, DP25-E, DP-24-E
±0.25	PX2670-0.25BDI	320	DP41-E, DP25-E, DP-24-E
±0.5	PX2670-0.5BDI	320	DP41-E, DP25-E, DP-24-E
±1	PX2670-1BDI	320	DP41-E, DP25-E, DP-24-E
±2.5	PX2670-2.5BDI	320	DP41-E, DP25-E, DP-24-E
±5	PX2670-5BDI	320	DP41-E, DP25-E, DP-24-E

All models come with complete operator's manual.

Optional LCD Meter: Add suffix "-M" to model number and add \$100 to list price. Ordering Example: PX2670-0.5BDI-M has a bidirectional range from -0.5 to +0.5 in-H₂O a 4-20 mA output and an LCD Display, \$320+100 = \$420.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

# www.omega.co.uk



# UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

#### **CANADA**

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

#### **GERMANY**

www.omega.de Deckenpfronn, Germany 0800-8266342

## **UNITED KINGDOM**

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622

www. omega.co.uk Manchester, England 0800-488-488 +44-(0)161-777-6611

#### **FRANCE**

www.omega.fr 0800-466-342

#### **BENELUX**

www.omega.nl 0800-099-33-44



Sales@omega.co.uk

# More than 100,000 Products Available!

# Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

# pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

# Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ehernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

## Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters