

Extension Grade  
CHROME<sup>®</sup>/ALOMEGA<sup>®</sup>  
Duplex  
ANSI Type KX

**KX**

ANSI Color Code: Positive Wire, Yellow;  
Negative Wire, Red; Overall, Yellow

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

Insulation	AWG No.	Model Number	Price/1000'	SLE/1000' <sup>††</sup>	Type Wire	Insulation		Max. Temp <sup>*</sup>		Nominal Size mm (in)	Wt.kg/300m (lb/1000') <sup>†</sup>
						Conductor	Overall	°C	°F		
Glass	16	EXGG-K-16	\$685	\$790	Solid	Glass Braid	Glass Braid	200	392	2.2 x 3.3 (0.085 x 0.130)	9 (17)
Neoflon PFA	16	EXTT-K-16	985	1135	Solid	PFA	PFA	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXTT-K-20	480	550	Solid	PFA	PFA	200	392	1.7 x 3.0 (0.068 x 0.116)	4 (9)
	24	EXTT-K-24	360	435	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	14	EXPP-K-14	850	980	Solid	Polyvinyl	Polyvinyl	105	221	3.4 x 7.3 (0.134 x 0.288)	13 (28)
	16	EXPP-K-16	490	565	Solid	Polyvinyl	Polyvinyl	105	221	3.1 x 5.3 (0.123 x 0.207)	10 (22)
	16	EXPP-K-16S	745	895	7 x 24	Polyvinyl	Polyvinyl	105	221	5.5 x 5.7 (0.139 x 0.226)	10 (22)
	18	EXPP-K-18S	770	925	7 x 26	Polyvinyl	Polyvinyl	105	221	3.5 x 5.2 (0.138 x 0.205)	8 (16)
	20	EXPP-K-20	230	265	Solid	Polyvinyl	Polyvinyl	105	221	2.4 x 3.8 (0.095 x 0.151)	6 (12)
	20	EXPP-K-20S	435	520	7 x 28	Polyvinyl	Polyvinyl	105	221	3.1 x 4.4 (0.123 x 0.175)	6 (12)
	24	EXPP-K-24	295	355	Solid	Polyvinyl	Polyvinyl	105	221	1.9 x 3.0 (0.075 x 0.120)	2 (4)
24	EXPP-K-24S	370	445	7 x 32	Polyvinyl	Polyvinyl	105	221	2.1 x 3.4 (0.082 x 0.134)	4 (9)	
Neoflon FEP	16	EXFF-K-16	885	1020	Solid	FEP	FEP	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXFF-K-20	465	535	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-K-24	325	375	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

\* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

†† To order special limits of error wire, add "-SLE" to model number before spool length

Ordering Example: EXTT-K-20-25, 25' spool of extension grade thermocouple wire, Type KX, 20 gage, stranded, Neoflon PFA insulation, \$480 x 0.0625 = \$30.

Extension Grade  
CHROME<sup>®</sup>/Constantan  
Duplex  
ANSI Type EX

**EX**

ANSI Color Code: Positive Wire, Purple;  
Negative Wire, Red; Overall, Purple

Insulation	AWG No.	Model Number	Price/1000'	SLE/1000' <sup>††</sup>	Type Wire	Insulation		Max. Temp <sup>*</sup>		Nominal Size mm (in)	Wt.kg/300m (lb/1000') <sup>†</sup>
						Conductor	Overall	°C	°F		
Neoflon PFA	16	EXTT-E-16	\$985	\$1135	Solid	PFA	PFA	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXTT-E-20	550	635	Solid	PFA	PFA	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXTT-E-24	435	500	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	16	EXPP-E-16	690	795	Solid	Polyvinyl	Polyvinyl	105	221	3.1 x 5.3 (0.123 x 0.207)	10 (22)
	18	EXPP-E-18S	605	725	7 x 26	Polyvinyl	Polyvinyl	105	221	3.5 x 5.2 (0.138 x 0.205)	8 (16)
	20	EXPP-E-20	260	300	Solid	Polyvinyl	Polyvinyl	105	221	2.4 x 3.8 (0.095 x 0.151)	6 (14)
	24	EXPP-E-24S	350	420	7 x 32	Polyvinyl	Polyvinyl	105	221	2.1 x 3.4 (0.82 x 0.134)	4 (9)
Neoflon FEP	16	EXFF-E-16	885	1020	Solid	FEP	FEP	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXFF-E-20	540	655	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-E-24	380	435	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

\* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

†† To order special limits of error wire, add "-SLE" to model number before spool length

Ordering Example: EXPP-E-20-50, 50' spool of extension grade thermocouple wire, Type EX, 20 gage, Polyvinyl over Polyvinyl insulation, \$260 x 0.1 = \$26.

Extension Grade  
Copper/Alloy#11  
Duplex  
ANSI Type RX and SX

**RX/SX**

Compensating Extension Wires for Platinum  
(-)/Platinum-Rhodium (+) Thermocouples.

ANSI Color Code: Positive Wire, Black; Negative Wire, Red; Overall, Green

Insulation	AWG No.	Model Number	Price/1000'	Type Wire	Insulation		Max. Temp <sup>*</sup>		Nominal Size mm (in)	Wt.kg/300m (lb/1000') <sup>†</sup>
					Conductor	Overall	°C	°F		
Glass	20	EXGG-RS-20	\$400	Solid	Glass Braid	Glass Braid	200	392	1.5 x 2.4 (0.060 x 0.095)	3 (6)
	24	EXGG-RS-24	390	Solid	Glass Braid	Glass Braid	200	392	1.3 x 2.0 (0.050 x 0.080)	1.8 (1.4)
Neoflon PFA	20	EXTT-RS-20	510	Solid	PFA	PFA	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXTT-RS-24	480	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	16	EXPP-RS-16	425	Solid	Polyvinyl	Polyvinyl	105	221	3.0 x 5.0 (0.118 x 0.195)	10 (22)
Neoflon FEP	20	EXFF-RS-20	440	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-RS-24	390	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

\* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

Ordering Example: EXTT-RS-20-500, 500' spool of extension grade thermocouple wire, Type RX, 24 gage, Neoflon PFA insulation, \$510 x 0.5 = \$255.



ANSI color code shown  
To order IEC color code see pg. H-9

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters