

Universal DIN Rail Transmitter



TXDIN1600 Series
Starts At
\$195



Free Software*
Download, Visit
omega.com/ftp

✓ Simple Configuration
Via USB Port

✓ Universal Pt100,
Thermocouple, mV,
mA Input

✓ Isolated Input

TXDIN1610

✓ Push Button User Trim

✓ 4 to 20 mA, 2-Wire Output

TXDIN1620

✓ Push Button User Trim

✓ 3-Wire Isolated Voltage
Output

TXDIN1630

✓ Dual Relay Outputs
250 Vac 1 Amp

✓ Relay Isolated From
Each Other

The TXDIN1600 Series is a new generation DIN rail mounted temperature transmitter. It has been designed to accept most common process and temperature sensor inputs and provide the user with a standard two wire 4 to 20 mA output signal. Isolation is provided between input and output and all temperature ranges are linear to temperature.

Designed for ease of use, our latest USB interface is fitted for quick and easy configuration. Just connect a standard USB cable between the TXDIN1600 and your PC. Using our free configuration software, your PC will automatically upload the existing configuration data and guide you through any changes you wish to make. To further help save time, the TXDIN1600 does not need to be wired to a power supply during the configuration process, it is powered via the USB interface from your PC.

The TXDIN1600 is also provided with user push button trim, allowing trim adjustments at both 4 mA and 20 mA. The user trim function can be locked during configuration if not required. The range led indicates out of range input during normal operation, during user trim it is used to indicate the stage of trim.

Specifications

Isolation: Input to output tested at 500 Vdc

Ambient: Operating -20 to 70°C (-4 to 158°F) 10 to 95% RH non-condensing

Storage: -40 to 85°C (-40 to 185°F)

Approvals: CE tested to BS EN 61326

Dimensions: 17.5 W x 56.4 D x 90 mm L (0.7 x 2.2 x 3.5")

Material: Polimide 6.6

Self Extinguishing

Terminals: Screwing terminal

Cable: 2.5 mm (0.1") max

Color: Gray



TXDIN1620, \$219,
shown actual size.



TXDIN1630, \$219,
shown actual size.

Output

TXDIN1610

Type: 2-wire current sink; signal range 4 to 20 mA; full range 3.8 to 24 mA

Supply: 11 to 30 Vdc, 24V nominal giving max loop load of 600 R @ 24V

Response Time: <500 ms to reach 95% of final value; start up time <3 s

Calibration Accuracy: ±5 uA

Loop Effects: Loop ripple 0.03% of FSR; supply sensitivity 0.05 uA/°C; supply ripple rejection <±5 uA error @ 1V rms 50 Hz ripple

Protection: Reverse connection and over-voltage protection, max over voltage current 100 mA

* Requires USB cable, OM-62-USB-CABLE, \$10, sold separately.



TXDIN1620, \$219, shown smaller than actual size.



TXDIN1630, \$219, shown smaller than actual size.

User Trim: Raise and lower buttons, active for offset when output is between 3.8 to 6 mA, span between 18 to 22 mA, trim lock option

TXDIN1620

Type: 3-wire voltage output with programmable ranges: 0 to 10, 0 to 5, 2 to 10, 1 to 5, and 0 to 1V

Supply: 15 to 28 Vdc

Response Time: <500 ms to reach 95% of final value; start up time <3 s

Calibration Accuracy: ±5 mV

Output Drive: 2 mA driving 5 kΩ @ 10V

Protection: Reverse connection and over-voltage protection, max over voltage current 100 mA

User Trim: Raise and lower buttons, active for offset when output is at offset and span, trim lock option

TXDIN1630

Type: Dual form C relay contacts

Supply: 24 Vdc ± 5% @ 40 mA max

Response Time: <500 ms to reach 95% of final value; start up time <3 s

Contact Rating: 250 Vac rms @ 1 A; 30 Vdc @ 1 A resistive load

Trip Type: Individual trips A and B may be set at high or low level, full range setpoint plus adjustable

Ranges: Setpoint programmed on units, covering full range of input

Hysteresis: Set in units

Protection: Reverse connection and over-voltage protection, max over voltage current 100 mA

Inputs

Input	Range	Accuracy*
K	-200 to 1370°C (-328 to 2498°F)	0.1% of FSR ±0.5°C (±33°F) [Type T 0.2% FSR ±0.5°C (±33°F)]
J	-100 to 1200°C (-148 to 2192°F)	
E	-100 to 1000°C (-148 to 1832°F)	
N	-180 to 1300°C (-292 to 2372°F)	
T	-100 to 400°C (-148 to 752°F)	
R	-10 to 1760°C (14 to 3200°F)	±0.5°C (±33°F) ±0.1% of FSR**
S	-10 to 1760°C (14 to 3200°F)	
Pt100	-200 to 850°C (-328 to 1562°F)	±0.1°C (±32°F)/±0.05% of rdg
mV	-40 to 75 mV	±0.04 mV
mA	-10 to 25 mA	±0.008 mA

* Accuracy for Pt100 and T/C do not include sensor and cold junction errors.

** Only over the range 800 to 1600°C (1472 to 2912°F).

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
TXDIN1610	\$195	Universal DIN rail transmitter
TXDIN1620	219	Universal DIN rail transmitter with 3-wire isolated voltage output
TXDIN1630	219	Universal DIN rail trip amplifier
OM-62-USB-CABLE	10	USB cable for software

Comes complete with operator's manual.

Ordering Example: TXDIN1610, universal DIN rail transmitter, \$195.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters